

HIGH SPEED MULTIPOLE CAT 6A CONNECTORS



Cat 6A connector

The high speed connectors complete the line of 2B series connector. These new contact

Specifications:

- Transmission performance meets Category 6A specification up to 500 MHz for 10 GigaBit Ethernet transmission according IEEE802.3an.
- Push-Pull connector
- IP50 or IP68 solution
- For cable diameter from 3.2 to 9.9 mm
- Designed for AWG 26 AWG 22, AWG 24 and AWG 26* (* recommended cable length 60 meters)

configuration can be used in the LEMO B, K or T series and are suitable for Category 6A.



Applications:

- Industry, food processing, industrial automation
- Technical equipment in buildings
- Broadcast networks
- Data communication

These products are specifically designed to work in harsh environments of temperature extremes, humidity, and vibration





Models





FGG.2B.514 Straight plug, key (G) or keys (A...M and R), cable collet

Part Number Example:
FGG.2B.514.CYCD62





FGG.2B.514 Straight plug, key (G) or keys (A...M), cable collet and nut for fitting a bend relief

Part Number Example:
FGG.2B.514.CYCD62Z





PHG.2B.514 Free socket, key (G) or keys (A...M and R), cable collet

Part Number Example:
PHG.2B.514.CYMD62



PHG.2B.514 Free socket, key (G) or keys (A...M), cable collet and nut for fitting a bend relief

Part Number Example:
PHG.2B.514.CYMD62Z



PKG.2B.514 Fixed socket, nut fixing, key (G) or keys (A...M and R), cable collet

Part Number Example:
PKG.2B.514.CYMD62

Insert configuration and electrical characteristics

Male crimp contacts	Female crimp contacts	Reference	Number of contacts	ø A (mm)	Crimp	Test voltage (kV rms) Contact-contact	Test voltage (kV rms) Contact-shell	Rated current (A)
		514	8	0.7	•	1.6	1.5	10

Note: CAT 6A insulators can be built into the 2B, 2K (IP68) and 2T (IP68) series.


D type collets for 2B series

Reference		Collet ø		Cable ø		Nut for fitting a bend relief	Bend relief
Type	••	ø A	ø B	max.	min.		
D	42	4.2	–	4.2	> 3.2	FFM.2B.130.LC	GMA.2B.040.DG
D	52	5.2	–	5.2	> 4.2		GMA.2B.045.DG
D	62	6.2	–	6.2	> 5.2		GMA.2B.050.DG
D	72	7.2	–	7.2	> 6.2		GMA.2B.060.DG
D	82	8.2	–	8.2	> 7.2		GMA.2B.070.DG
D	92	9.2	8.6	9.2	> 8.2		GMA.2B.080.DG
D	99	9.9	8.6	9.9	> 9.2	1)	–

Note: all dimensions are in millimetres.

1) these collets cannot be used for connector models with nut for fitting a bend relief.

Accessories



Note:
Material: Polyurethane elastomer
Temperature range in dry atmosphere: -40°C +80°C

GMA Bend relief for FGG and PHG models with nut for fitting a bend relief

Part Number	Dimensions (mm)			
	Bend relief		Cable ø	
	A	L	max.	min.
GMA.2B.040.DG	4.0	36	4.5	4.0
GMA.2B.045.DG	4.5	36	5.0	4.5
GMA.2B.050.DG	5.0	36	5.5	5.0
GMA.2B.060.DG	6.0	36	6.5	6.0
GMA.2B.070.DG	7.0	36	7.7	7.0
GMA.2B.080.DG	7.8	36	8.8	7.8


Ref.	Colour
A	blue
B	white
G	grey

Ref.	Colour
J	yellow
M	brown
N	black

Ref.	Colour
R	red
S	orange
V	green

Note: The last letter «G» of the part number indicates the colour grey of the bend relief. For others colour, refer to the above table and replace letter «G» by the letter of the colour required.

Panel cut-out





Cable stripping lengths

Connector	Type	ø contact (mm)	Cable stripping lengths (mm)		
			Crimp		
			L	S	T
514		0.7	14	7	4

Note: all dimensions are in millimetres. Mounting nut torque: 6.0 Nm.

Refer to B series catalog for general characteristics.





LEMO HEADQUARTERS

SWITZERLAND

LEMO SA

Chemin des Champs-Courbes 28 - P.O. Box 194 - CH-1024 Ecublens
Tel. (+41 21) 695 16 00 - Fax (+41 21) 695 16 02 - e-mail: info@lemo.com

www.lemo.com