

3-conductor through terminal block; 2.5 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®

Item no.	2002-63011	GTIN / EAN	4044918964920
Content	1 piece	Order unit	piece
Order quantity	100	Increase in order quantity	(100, 200, 300, 400, ...)
Customer item no.		Customs Tariff no.	85369010000
Customs duty for the country of origin	CN	Available	-
List price	On request	Net price	On request
Availability	On request		

Note: Some items may not be available from your local WAGO company. Please note that the quantities ordered in the shopping cart are rounded up to the PU (SPU).

RoHS ✓
Compliant

Article details

Approvals

Downloads/Certificates

Accessories

Description

Remarks

3-conductor through terminal block; 2.5 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®

Safety information 1: An end plate must be applied when changing from a 3-conductor terminal block to a 4-conductor terminal block and vice versa.

Item properties

Miscellaneous

Name	Value	Unit
Rated voltage EN (Ex e II) [V]	500	V
Rated current (Ex e II) [A]	22	A
Rated current (Ex e II) with jumper [A]	20	A
Connection technology	Push-in CAGE CLAMP®	
Actuation type	Push-in	
Connectable conductor materials	Copper	
Nominal cross section	2.5 mm²	
Solid conductor	0.25 ... 4 mm² / 22 ... 12 AWG	
Solid conductor, push-in termination	0.75 ... 4 mm² / 18 ... 12 AWG	
Fine-stranded conductor	0.25 ... 4 mm² / 22 ... 12 AWG	
Fine-stranded conductor with ferrule, push-in termination, l	0.75 mm² / 18 AWG	
Strip length	10 ... 12 mm / 0.39 ... 0.47 inch	
Total number of connection points	3	
Total number of potentials	1	
Number of levels	1	
Type of wiring	Front-entry wiring	
Width	5.2 mm / 0.205 in	
Height from upper-edge of DIN-35 rail	38.9 mm / 1.531 in	
Depth	51.3 mm / 2.031 in	
Design	angled	
Type of mounting	Carrier rail 35 x 15	
Marking level	Center/side marking	
Color	gray	
Insulating material	Polyamide 66 (PA 66)	
Fire load [MJ]	0.123	MJ
Weight [g]	5.61	g
Packaging type	BOX	
[mm]	5.2	mm
Product Family	TQFUCBB S	
Main product function	Through term. block	
Product type	Through rail-mount term. blocks	

Upwards