

# EVVOSEMI<sup>®</sup>

THINK CHANGE DO



ESD



TVS



MOS



LDO



Diode



Sensor



DC-DC

## Product Specification

▶ Domestic	Part Number	LM324ADR
▶ Overseas	Part Number	LM324ADR
▶ Equivalent	Part Number	LM324ADR

EV is the abbreviation of name EVVO

## Quadruple Operational Amplifiers



### DESCRIPTION

The LM324ADR consists of four independent, high gain, internally frequency compensated operational amplifiers which were designed specifically to operate from a single power supply over a wide range of voltages. Operation from split power supplies is also possible and the low power supply current drain is independent of the magnitude of the power supply voltage. Application areas include transducer amplifiers, DC gain blocks and all the conventional op amp circuits.

### FEATURES


- Wide range of supply voltages
- Low supply current drain independent of supply voltage
- Low input biasing current
- Low input offset voltage and offset current
- Input common-mode voltage range includes ground
- Differential input voltage range equal to the power supply voltage
- DC voltage gain 100 V/ mV Typ
- Internally frequency compensation

### PACKAGE INFORMATION



PIN1

SOP14



PIN1

DIP14

## ELECTRICAL CHARACTERISTICS



PARAMETER	TEST CONDITIONS*		LM324ADR			UNIT
			MIN	TYP	MAX	
V <sub>IO</sub> Input offset voltage	V <sub>CC</sub> =5V to MAX, V <sub>IC</sub> = V <sub>ICR</sub> min, V <sub>O</sub> =1.4V	25 °C Full temperature range		3	7 9	mV
αV <sub>IO</sub> Average temperature coefficient of input offset voltage		Full temperature range		7		μV/°C
I <sub>IO</sub> Input offset current	V <sub>O</sub> =1.4V	25 ° C Full temperature range		2	50 150	nA
αI <sub>IO</sub> Average temperature coefficient of input offset current		Full temperature range		10		pA/°C
I <sub>IB</sub> Input bias current	V <sub>O</sub> =1.4V	25 °C Full temperature range		-20	-250 -500	nA
V <sub>ICR</sub> Common-mode input voltage range	V <sub>CC</sub> = 5V to MAX	25 °C Full temperature range	0 to V <sub>CC</sub> -1.5 0 to V <sub>CC</sub> - 2			V
V <sub>OH</sub> High-level output voltage	R <sub>L</sub> = 2 kΩ V <sub>CC</sub> = MAX, R <sub>L</sub> =2kΩ V <sub>CC</sub> = MAX, R <sub>L</sub> = 10 kΩ	25 °C Full temperature range Full temperature range	V <sub>CC</sub> -1.5 26 27			V
V <sub>OL</sub> Low-level output voltage	R <sub>L</sub> = 10 kΩ	Full temperature range		5	20	mV
A <sub>VD</sub> Large-signal differential voltage amplification	V <sub>CC</sub> = 15 V, V <sub>O</sub> =1V to 11 V, R <sub>L</sub> ≥ 2 kΩ	25 °C Full temperature range	25 15	100		V/mV
CMRR Common-mode rejection ratio	V <sub>CC</sub> = 5V to MAX, V <sub>IC</sub> = V <sub>ICR</sub> min	25 °C	65	80		dB
k <sub>SVR</sub> Supply voltage rejection ratio (ΔV <sub>CC</sub> /ΔV <sub>IO</sub> )	V <sub>CC</sub> = 5V to MAX	25 °C	65	100		dB
Vo1/Vo2 Crosstalk attenuation	f=1kHz to 20 kHz	25 °C		120		dB
I <sub>O</sub> Output current	V <sub>CC</sub> = 15 V, V <sub>ID</sub> =1V,V <sub>O</sub> = 0 V <sub>CC</sub> = 15 V, V <sub>ID</sub> = -1V, V <sub>O</sub> =15V V <sub>ID</sub> = -1V, V <sub>O</sub> = 200 mV	25 °C Full temperature range 25 °C Full temperature range 25 °C	-20 -10 10 5 12	-30  20		mA    μA
I <sub>OS</sub> Short-circuit output current	V <sub>CC</sub> at 5 V, GND at -5V,V <sub>O</sub> =0	25 °C		±40	±60	mA
I <sub>CC</sub> Supply current (four amplifiers)	V <sub>O</sub> = 2.5 V, No load V <sub>CC</sub> = MAX, V <sub>O</sub> = 0.5V <sub>CC</sub> , No load	Full temperature range Full temperature range		1.5 1.1	2.4 3	mA

"MAX" Vcc for testing purposes is 30 V. Operating temperature -40 - 85° C.

Quadruple Operational Amplifiers



PACKAGE

SOP14



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	—	1.750	—	0.069
A1	0.100	0.250	0.004	0.010
A2	1.250	—	0.049	—
b	0.310	0.510	0.012	0.020
c	0.100	0.250	0.004	0.010
D	8.450	8.850	0.333	0.348
E	5.800	6.200	0.228	0.244
E1	3.800	4.000	0.150	0.157
e	1.270(BSC)		0.050(BSC)	
L	0.400	1.270	0.016	0.050
θ	0°	8°	0°	8°

DIP14



UNIT: mm							
DIM.	MIN	TYP	MAX	DIM.	MIN	TYP	MAX
A	6.100	6.300	6.680	a	1.504	1.524	1.544
B	18.940	19.200	19.560	c	0.437	0.457	0.477
D	8.200	8.700	9.200	d	2.530	2.540	2.550
D1	7.42	7.62	7.82	L	0.500	—	0.800
E	3.100	3.300	3.550	L1	3.000	3.200	3.600

## Disclaimer

EVVOSEMI ("EVVO") reserves the right to make corrections, enhancements, improvements, and other changes to its products and services at any time, and to discontinue any product or service without notice.

EVVO warrants the performance of its hardware products to the specifications applicable at the time of sale in accordance with its standard warranty. Testing and other quality control techniques are used as deemed necessary by EVVO to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

Customers should obtain and confirm the latest product information and specifications before final design, purchase, or use. EVVO makes no warranty, representation, or guarantee regarding the suitability of its products for any particular purpose, nor does EVVO assume any liability for application assistance or customer product design. EVVO does not warrant or accept any liability for products that are purchased or used for any unintended or unauthorized application.

EVVO products are not authorized for use as critical components in life support devices or systems without the express written approval of EVVOSEMI.

The EVVO logo and EVVOSEMI are trademarks of EVVOSEMI or its subsidiaries in relevant jurisdictions. EVVO reserves the right to make changes without further notice to any products herein.