


## Coaxial Cable Connector 16\_MMCX-50-1-7/111\_O

### Description

Right angle cable plug

Interface standards  
SUHNER-MMCX



### Technical Data

#### Electrical Data

|                          |             |
|--------------------------|-------------|
| Impedance                | 50 $\Omega$ |
| Interface frequency max. | 6 GHz       |

#### Mechanical Data

|                |           |
|----------------|-----------|
| Centre contact | soldered  |
| Outer contact  | crimped   |
| Weight         | 0.0008 kg |

#### Environmental Data

|                                                      |                  |
|------------------------------------------------------|------------------|
| Operating temperature                                | -55 °C to 155 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant        |

#### Material Data

| Piece Parts    | Material               | Surface Plating                            |
|----------------|------------------------|--------------------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated)          |
| Outer contact  | Brass                  | Gold Plating (without Nickel underplating) |
| Body           | Brass                  | Gold Plating (without Nickel underplating) |
| Insulator      | PFA / PTFE             |                                            |
| Crimp ferrule  | Copper                 | Gold Plating (without Nickel underplating) |

### Related Documents

|                      |                |
|----------------------|----------------|
| Outline drawing      | DOU-00007520   |
| Catalogue drawing    | DOU-00006005   |
| Assembly instruction | DOC-0000241532 |

### Ordering Information

|                      |                       |
|----------------------|-----------------------|
| Single package       | 16_MMCX-50-1-7/111_OE |
| Bulk 100 pcs package | 16_MMCX-50-1-7/111_OH |

### Additional Information

|                 |                             |
|-----------------|-----------------------------|
| Suitable cables | ENVIROFLEX_178_D, K_01252_D |
|-----------------|-----------------------------|