








RECOMMENDED PANEL CUTOUT, TOLERANCE +/-0.05
THICKNESS: 1.25~1.60MM.


NOTES:

1. MATERIAL: NYLON, 94V-0.
2. PRODUCT SPECIFICATION 2192681000-PS.
3. PACKING SPECIFICATION 2192681000-PK.
4. USE WITH MOLEX TERMINAL 105300****.
5. MATING WITH MOLEX HEADER 219637****.
6. PART CONFORM TO CLASS "B" REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex							
mm		4:1													
GENERAL TOLERANCES (UNLESS SPECIFIED)				SALES DRAWING FOR NANO-FIT BMI RECEP											
ANGULAR TOL ± 3.0°															
4 PLACES		±													
3 PLACES		±													
2 PLACES		± 0.4		EC NO: 761370 DRWN: GLLI 2023/08/31 CHK'D: XQZHANG 2023/09/11 APPR: XQZHANG 2023/09/11				PRODUCT CUSTOMER DRAWING							
1 PLACE		± 0.5													
0 PLACES		±													
INITIAL REVISION: DRWN: GLLI 2023/03/03 APPR: XQZHANG 2023/09/11				DOCUMENT NUMBER				DOC TYPE		DOC PART		REVISION			
				2192681000-SD				PSD		000		A			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A3-SIZE		219268		SEE TABLE IN SHEET 2		GENERAL MARKET		1 OF 3	




4 CKT




6 CKT




8 CKT




10 CKT



12 CKT



14 CKT



16 CKT

PART NUMBER	DIM'A'	DIM'B'	CKT	COLOR
219268-1204	23.82	8.86	4	BLACK
219268-1206	26.32	11.36	6	
219268-1208	28.82	13.86	8	
219268-1210	31.32	16.36	10	
219268-1212	33.82	18.86	12	
219268-1214	36.32	21.36	14	
219268-1216	38.82	23.86	16	NATURAL
219268-2204	23.82	8.86	4	
219268-2206	26.32	11.36	6	
219268-2208	28.82	13.86	8	
219268-2210	31.32	16.36	10	
219268-2212	33.82	18.86	12	
219268-2214	36.32	21.36	14	
219268-2216	38.82	23.86	16	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE	CURRENT REV DESC:		molex SALES DRAWING FOR NANO-FIT BMI RECEP					
mm	4:1								
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 761370 DRWN: GLLI CHK'D: XQZHANG APPR: XQZHANG INITIAL REVISION: DRWN: GLLI APPR: XQZHANG		DOCUMENT NUMBER					
ANGULAR TOL ± 3.0 °				2192681000-SD					
4 PLACES ±				PSD					
3 PLACES ±				000					
2 PLACES ± 0.4				A					
1 PLACE ± 0.5									
0 PLACES ±		2023/03/03		SHEET NUMBER					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER	
				A3-SIZE	219268	SEE TABLE IN SHEET 2	GENERAL MARKET	2 OF 3	




2023/08/31

2023/09/11

2023/09/11

2023/03/03

2023/09/11



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex			
mm		1:1								
GENERAL TOLERANCES (UNLESS SPECIFIED)				SALES DRAWING FOR NANO-FIT BMI RECEP						
ANGULAR TOL ± 3.0 °										
4 PLACES		±		EC NO: 761370			PRODUCT CUSTOMER DRAWING			
3 PLACES		±		DRWN: GLLI 2023/08/31						
2 PLACES		± 0.4		CHK'D: XQZZHANG 2023/09/11						
1 PLACE		± 0.5		APPR: XQZZHANG 2023/09/11			DOCUMENT NUMBER			
0 PLACES		±		INITIAL REVISION:			2192681000-SD			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION			DOC TYPE		DOC PART	
				DRAWING			SERIES		REVISION	
				A3-SIZE		219268		MATERIAL NUMBER		
								CUSTOMER		
								SHEET NUMBER		
								3 OF 3		