

Description


μClamp0551ZV diodes are designed to protect sensitive electronics from damage or latch-up due to ESD. They feature large cross-sectional area junctions for conducting high transient currents.

μClamp0551ZV is in a DFN 1.0 x 0.6 x 0.25mm 2-lead package. Leads are spaced at a pitch of 0.65mm. Each device will protect one unidirectional line operating at 5.5 volts. They offer desirable characteristics for board level protection including fast response time, low operating and clamping voltage, and no device degradation.

Applications

- Cellular Handsets & Accessories
- Battery Protection
- Notebooks & Handhelds
- Voltage Bus Protection

Package Dimension



Nominal Dimensions in mm


Features

- High ESD withstand Voltage
 - IEC 61000-4-2 (ESD): 30kV (Contact), 30kV (Air)
- Protects one I/O or power line
- High peak pulse current capability: 100A (tp = 8/20μs)
- Working voltage: 5.5V
- Low ESD clamping voltage
- Solid-state silicon-avalanche technology

Mechanical Characteristics

- Package : DFN 1.0 x 0.6 x 0.25mm 2-Lead
- Pb-Free, Halogen Free, RoHS/WEEE Compliant
- Lead Finish : Pb-Free
- Molding compound flammability rating: UL 94V-0
- Marking : Marking Code + Date Code
- Packaging : Tape and Reel

Functional Schematic



DFN 1.00 x 0.60 x 0.25 mm 2-Lead (Bottom View)

Absolute Maximum Rating

RATING	SYMBOL	VALUE	UNITS
Peak Pulse Power (tp = 8/20μs)	P _{PK}	1200	W
Peak Pulse Current (tp = 8/20μs)	I _{PP}	100	A
ESD per IEC 61000-4-2 (Contact) ⁽¹⁾	V _{ESD}	±30	kV
ESD per IEC 61000-4-2 (Air) ⁽¹⁾		±30	
Operating Temperature	T _{OP}	-40 to +85	°C
Storage Temperature	T _{STG}	-55 to +150	°C

Electrical Characteristics

T=25°C unless otherwise specified

All data taken from Pin 1 to 2 unless otherwise specified

PARAMETER	SYMBOL	CONDITIONS	MIN.	TYP.	MAX.	UNITS
Reverse Stand-Off Voltage	V _{RWM}				5.5	V
Reverse Breakdown Voltage	V _{BR}	I _t = 1mA	5.8	7.0	7.5	V
Reverse Leakage Current	I _R	V _{RWM} = 5.5V		10	100	nA
Clamping Voltage	V _C	I _{PP} = 40A, t _p = 8/20 μs		8.3	9.5	V
		I _{PP} = 100A, t _p = 8/20 μs		10.5	12.0	
ESD Clamping Voltage ⁽²⁾	V _C	I _{TLP} = 4A, t _p = 0.2/100ns (TLP)		7		V
		I _{TLP} = 16A, t _p = 0.2/100ns (TLP)		7.5		
Dynamic Resistance ^{(2),(3)}	R _{DYN}	t _p = 0.2/100ns (TLP)		0.03		Ω
Junction Capacitance	C _J	V _R = 0V, f = 1MHz		400	500	pF

Notes:


(1): ESD Gun return path to Ground Reference Plane (GRP)

(2): Transmission Line Pulse Test (TLP) Settings: tp = 100ns, tr = 0.2ns, I_{TLP} and V_{TLP} averaging window: t₁ = 70ns to t₂ = 90ns.


(3): Dynamic resistance calculated from I_{TLP} = 4A to I_{TLP} = 16A

Typical Characteristics


ESD Clamping (+8kV Contact per IEC 61000-4-2)




ESD Clamping (-8kV Contact per IEC 61000-4-2)




TLP Characteristics (Positive Pulse)




TLP Characteristics (Negative Pulse)



Surge Clamping Characteristic ($t_p = 8/20\mu\text{s}$)



Capacitance vs. Reverse Voltage



Applications Information

Assembly Guidelines

The figure at the right details Semtech's recommended mounting pattern. Recommended assembly guidelines are shown in Table 1. Note that these are only recommendations and should serve only as a starting point for design since there are many factors that affect the assembly process. Exact manufacturing parameters will require some experimentation to get the desired solder application.

Solder Stencil

Stencil design is one of the key factors determining the volume of solder paste which is deposited onto the land pad. The area ratio of the stencil aperture will determine how well the stencil will print. The area ratio takes into account the aperture shape, aperture size, and stencil thickness. A minimum area ratio of 0.66 is preferred for the subject package. The area ratio of a rectangular aperture is given as:

$$\text{Area Ratio} = (L * W) / (2 * (L + W) * T)$$

Where:

L = Aperture Length

W = Aperture Width

T = Stencil Thickness

Semtech recommends a stencil with square aperture and rounded corners for consistent solder release. The stencil should be laser cut with electro-polished finish. A stencil thickness of 0.100mm (0.004") or 0.125mm (0.005") stencil may be used, however the stencil opening may need to be increased slightly to achieve the desired area ratio to ensure proper solder coverage on the pad.






Figure 1 - Assembly Guidelines

Assembly Parameter	Recommendation
Solder Stencil Design	Laser Cut, Electro-Polished
Aperture Shape	Rectangular with Rounded Corners
Solder Stencil Thickness	0.100mm (0.004") or 0.125mm (0.005")
Solder Paste Type	Type 4 or Type 5
Solder Reflow Profile	Per JEDEC J-STD-020
PCB Solder Pad Design	SMD or NSMD
PCB Pad Finish	OSP or NiAu


Outline Drawing - DFN 1.00 x 0.60 x 0.25mm 2-Lead



Landing Pattern - DFN 1.00 x 0.60 x 0.25mm 2-Lead




Marking Code



Notes:

- (1) Marking will also include line matrix date code
- (2) Bar indicates Pin 1 location

Tape and Reel Specification



Order Information

PART NUMBER	QTY PER REEL	REEL SIZE
μClamp0551ZV.F	15,000	7"

MicroClamp, μClamp and uClamp are registered trademarks of Semtech Corporation.



SEMTECH®

Important Notice

Information relating to this product and the application or design described herein is believed to be reliable, however such information is provided as a guide only and Semtech assumes no liability for any errors in this document, or for the application or design described herein. Semtech reserves the right to make changes to the product or this document at any time without notice. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. Semtech warrants performance of its products to the specifications applicable at the time of sale, and all sales are made in accordance with Semtech's standard terms and conditions of sale.

Product features listed in this datasheet may be suitable for "non-safety" applications in Automotive use cases. Information in this datasheet for such applications is provided as a guide only. No safety claim is made in respect of the product described in this datasheet when used in Automotive safety systems or security devices, including systems for controlling vehicles and other transportation equipment; responsibility for achieving safety goals belongs solely to the buyer and/or integrators. Semtech is under no obligation to provide any data regarding safety integration to the buyer or any integrator.

SEMTECH PRODUCTS ARE NOT DESIGNED, INTENDED, AUTHORIZED OR WARRANTED TO BE SUITABLE FOR USE IN AUTOMOTIVE SAFETY OR SECURITY DEVICES, INCLUDING SYSTEMS FOR CONTROLLING VEHICLES AND OTHER TRANSPORTATION EQUIPMENT, LIFE-SUPPORT APPLICATIONS, DEVICES OR SYSTEMS, OR IN NUCLEAR APPLICATIONS IN WHICH THE FAILURE COULD BE REASONABLY EXPECTED TO RESULT IN PERSONAL INJURY, LOSS OF LIFE OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. INCLUSION OF SEMTECH PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE UNDERTAKEN SOLELY AT THE CUSTOMER'S OWN RISK. Should a customer purchase or use Semtech products for any such unauthorized application, the customer shall indemnify and hold Semtech and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs damages and attorney fees which could arise.

The Semtech name and logo are registered trademarks of the Semtech Corporation. All other trademarks and trade names mentioned may be marks and names of Semtech or their respective companies. Semtech reserves the right to make changes to, or discontinue any products described in this document without further notice. Semtech makes no warranty, representation or guarantee, express or implied, regarding the suitability of its products for any particular purpose. All rights reserved.

© Semtech 2024