


19083000	DATA SHEET	
Valid from: 26.07.2024	EPIC® H-B 16 TSB	

Description

- The housing standard.
- Wide choice for all applications.



General Characteristics

Series	H-B 16
Version	Hood M 25
Locking	Double lever
Gland body	Yes
Cable entry	Side
Protection (DIN EN 60529)	IP 65 (latched)
Protection (NEMA 250, UL50E)	4, 12 (latched)
Temperature Range	-40°C to +100°C, short term up to +125°C


Materials and Surfaces

Housing	Aluminium alloy, powder-coated, grey
Bolt	Heat-treatable steel, zinc-plated
Lever	Steel, zinc-plated
Gland body	Brass, nickel plated



Standard

Safety Standard	IEC 61984
-----------------	-----------

Creator: THB01/BU-EPIC Released: IVSE1/BU-EPIC	Document: DB19083000EN Version: 02	Page 1 of 3
---	---------------------------------------	-------------

19083000	DATA SHEET	
Valid from: 26.07.2024	EPIC® H-B 16 TSB	

Technical Drawings



Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Universal, robust metal housings size H-B 16


Application range

Plant engineering
Light & sound technology
Plastics industry

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: THB01/BU-EPIC Released: IVSE1/BU-EPIC	Document: DB19083000EN Version: 02	Page 2 of 3
---	---------------------------------------	-------------

19083000	DATA SHEET	
Valid from: 26.07.2024	EPIC® H-B 16 TSB	