






PART NO.	NO OF TERMINALS	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'
10139522-108LF	8	97.0	85.5	66.5	Ø 4.5
10139522-112LF	12	135.0	123.5	104.5	Ø 3.8

NOTES :

RATED CURRENT & VOLTAGE : 30A, 300V
WITHSTAND VOLTAGE : 3400V AC/Min
INSULATION RESISTANCE : 1000MΩ or More at DC 500V
OPERATING TEMPERATURE : -40°C MIN TO 105°C MAX
SCREW TORQUE : 9 Lb-in
WIRE RANGE : 12-22 AWG
MATERIAL
HOUSING : THERMOPLASTIC, UL 94 V-0 BLACK
TERMINAL : BRASS, 0.8T, TIN PLATED (3µ MIN)
SCREW : STEEL M3.5, Zn PLATED (2µ MIN)
APPROVAL : UL & CSA (PENDING)



spec ref				dr		Binesh C		2017/08/01		projection		MM		size		A3		scale		1:1			
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED				eng		Binesh C		2017/08/02						ecn no						-	
chr						-		-															
appr						K-Paul Biju		2017/08/02		product family		TERMINAL BLOCK		rel level						Released			
surface		linear		0.X		±0.3		Amphenol FCi		title		BARRIER TERMINAL BLOCK		dwg no		10139522		rev		A			
				0.XX		±0.20																	
				0.XXX		±0.10																	
		angular		0°		±2°																cat. no.	