


LEAD-FREE P/N	CABLES	ød1	ød2	ød3	ød4	d5	d6	Remarks
85861-X01LF	RG 178B/U, RG196A/U TZC_50126	1.10	1.70	2.20	3.20	7.8	21.00	
85861-X02LF	RG188A/U, RG174A/U, RG316/U	1.70	2.50	2.90	3.60	9.0	22.20	
85861-X04LF	TZC_75106 (GORE CABLE) 75ohm	1.30	2.00	2.50	3.20	7.8	21.00	see note 2
85861-X05LF	RG 179 75ohm	1.70	2.50	2.90	3.60	9.0	22.20	see note 2
85861-X06LF	FILOTEX CABLE ALCATEL	1.30	2.00	2.50	3.20	7.8	21.00	see note 2

1,27um Min. Au.
Positions 1&2
Plating on contact area



- This product 85861-X0ZLF will be packed in a plastic bag containing three loose parts, as follows.
 - Crimp Ferrule
 - Outer Contact
 - Inner Contact
- All dimensions shown are reference.
- Assemble product with tool HT430, use insert EPL 193460 or EPL 193428
- This product is made for a PCB thickness of 3.2mm.
- Dash numbers -00ZLF is for crimp inner center contact
- THIS PRODUCT WITH "LF" SUFFIX MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS -22-008.
- THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.
- PACKAGING SPEC: SEE GS-14-920

rev	ecn no	dr	date
D	LS06-0022	LGO	2006/06/03
E	LS07-0214	LGO	2007/08/20
F	LS08-0057	LGO	2008/02/18
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	GOISNARD	2006/03/06	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 5			
Eng	GOISNARD	2006/03/06			0.XX	±0.1					
Chr	LEGARE	2006/03/06			0.XX' ±2°	0.XXX					±0.1
Appr	LEGARE	2006/03/06	Product family				METRAL	Spec ref -			
			title CRIMP TO CABLE 50ohm MALE MINI COAX				dwg no 85861		Rev. F		
catalog no			-				CUSTOMER		sheet	of	