






PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)

SECTION HH



Part Number & Date Code Printing

						PART NUMBER
SHELL	A $\pm$ 0.38	B $\pm$ 0.12	C $\pm$ 0.10	D $\pm$ 0.25	G $\pm$ 0.25	Plating: 0.76» AU
09	30.81	24.99	16.96	16.79	5.90	D09P23B6GL4A*
15	39.14	33.32	25.18	25.12	5.90	D15P23B6GL4A**
25	53.03	47.04	39.12	38.84	5.70	D25P23B6GL4A**
37	69.32	63.50	55.68	55.30	5.70	D37P23B6GL4A**

REQUIREMENTS

Technical characteristics:

Shell: steel tin /Zinc Cr3 plated

Insulators: self-extinguishing black polyster, ULclass94V0

Contacts size 20:brass,gold on mating end,bright tin on termination end over nickel on entire contact

Cycles : 500 for protection 6

Harpoons: phosphor bronze, tin plated

Metal plate for electrical continuity:brass,tin/Zinc Cr3 plated

Nuts: brass, tin/Zinc Cr3 plated torque: 0.7N/m

Electrical characteristics:

max.current rating: 5A

Test voltage: 1000V

Rated voltage: 300V

Contact resistance: $\leq 15\text{m}\Omega$

Shell resistance: $\leq 5\text{m}\Omega$

Insulation resistance: $\geq 5000M\Omega$

Climatic characteristics:

Operating temperature range: -55°C $+125^{\circ}\text{C}$

Dimensions:

in accordance with MIL-C-24308

LF FOR LEAD FREE

SPECIAL CODE 4A—SPECIAL CLINCH NUT

FOR ROHS DETAILS REFER DWG.NO: C01-8646-0000

[illegible]