



Features

HIGH CURRENT CARRY AND HIGH VOLTAGE

Inert gas filled arc chamber suitable for high voltage switching

COMPACT STRUCTURE, LOW NOISE

Small, low-profile design with low noise while carrying or switching loads

SAFE FOR EXPLOSIVE ENVIRONMENTS

No arc leakage due to a hermetically sealed design

HIGH RELIABILITY DESIGN

Hermetic sealing creates a stable environment for high voltage switching

NO SPECIFIC MOUNTING ARRANGEMENT

Mountable in any orientation without reduction of performance

VARIOUS APPLICATIONS

Battery disconnect, EV charging, energy storage systems, photovoltaics, power control, circuit protection and much more

Sealing Type: Epoxy/Resin

- Compact design, optional auxiliary contacts available
- ✓ Bi-directional options




Certification Information

- 1. Meet RoHS (2011/65/EU)
- 2. CE certified
- 3. UL approved



Page |1 Rev K - 05-Feb-2025





Performance Data for 900V Switching Option

MAIN CONTACT			
Contact Arrangement		1 Form X (SPST-NO)	
Rated Operatin	g Voltage	12-900 VDC	
Continuous (Ca	rry) Current	100A*1	
Short Time Ove	r current	200A (3 minutes) *2	
Short Circuit Current		1,250A (1/2 cycle, 60Hz)	
Dielectric Withstanding Voltage (initial)	Between Open Contacts	2500VDC, ≤1mA	
	Between Contacts to Coil	2,200Vrms, ≤1mA	
Insulation Resistance	Terminal to Terminal	New: Min 100 MΩ@500VDC	
(Initial)	Terminals to Coil	End of Life: 50 MΩ@500VDC	
Voltage Drop (@100A)		≤80mV	

EXPECTED LIFE			
Electrical Life	See table below		
Mechanical Life	200,000 Cycles		

Polarized Load

Voltage (VDC)	650	450
Current(A)	100	100
Electrical Life (cycles)	2,000	10,000

Note:

- 1. Do not meet dielectric & IR after the test.
- 2. ON:OFF= 1s:9s.
- 3. The ambient environment of the application should not cause any dewing or icing inside the relay. Otherwise, the relay may fail to work consequently.

OPERATE / RELEASE TIME		
Operate Time Close (includes bounce)	25ms, Max.	
Release Time	10ms, Max.	


ENVIRONMENTAL DATA		
Shock	Functional	196m/s² Sine half-wave pulse
	Destructive	490m/s² Sine half-wave pulse
Operating Temperature		-40 to +85 °C
Vibration, Sine, Peak, 20G		80 to 2,000Hz
Weight		0.42Lb (0.19kg)


COIL DATA				
Nominal Voltage	12VDC	24VDC	48VDC	
Pickup voltage (20 °C)	9.6VDC	19.2VDC	38.4VDC	
Dropout voltage (20 °C)	0.8VDC	1.6VDC	3.3VDC	
Coil current (20°C, voltage rating, nominal)	461mA	250mA	122mA	
Coil wattage (20°C, voltage rating, nominal)	5.5W	6W	6W	
Rated coil resistance ±5% (20°C)	26 Ω	96 Ω	392 Ω	

AUX. CONTACT			
Aux. Contact Arrangement	1 Form A		
Aux. Contact/Current Max.	2A@30VDC/3A@125VAC		
Aux. Contact Current Min.	100mA@8V		
Aux. Contact Resistance Max.	0.417ohms@30VDC/ 0.150ohms@125VAC		

Page | 2 Rev K - 05-Feb-2025








Performance Data for ALEV100-H /1000V Switching Option

MAIN CONTACT			
Contact Arrangement		1 Form X (SPST-NO)	
Rated Operatin	g Voltage	1000 VDC	
Rated Current		100A	
Max. Short Circu	uit Current	1250A (1s)	
Short Term Current		200A (3min)	
Dielectric Withstanding Voltage (initial)	Between Open Contacts	4000VDC 1mA 1min	
	Between Contacts to Coil	2200VAC 1mA 1min	
Insulation Resistance	Terminal to Terminal	Min 1000 MΩ @1000VDC	
(Initial)	Terminals to Coil		
Contact Voltage Drop		Max. 5mV @10A	
Limit breaking		1500A@450VDC,1 Cycle	

EXPECTED LIFE		
Electrical Endurance (Make/ Break)	100A@750V 500 Cycles	
Electrical Endurance (Break only)	63A@1000V 500 Cycles	
Mechanical Life	200,000 Cycles	

Current Carry Curve



Note:

- 1. Do not meet dielectric & IR after the test.
- 2. ON:OFF= 0.6s:5.4s.
- 3. The ambient environment of the application should not cause any dewing or icing inside the relay. Otherwise, the relay may fail to work consequently.

OPERATE / RELEASE TIME		
Operate Time Close (includes bounce)	25ms, Max. @20°C	
Release Time	10ms, Max. @20°C	


ENVIRONMENTAL DATA			
Shock	Functional	196m/s² Sine half-wave pulse	
SHOCK	Destructive	490m/s² Sine half-wave pulse	
Operating Temperature		-40 to +85 °C	
Humidity		5% to 85%RH	
Weight		0.42Lb (0.19kg)	

COIL DATA				
Nominal Voltage	12VDC	24VDC	48VDC	
Pickup voltage (20 °C)	9.6VDC	19.2VDC	38.4VDC	
Dropout voltage (20 °C)	0.8VDC	1.6VDC	3.3VDC	
Coil current (20°C, voltage rating, nominal)	461mA	250mA	122mA	
Coil wattage (20°C, voltage rating, nominal)	5.5W	6W	6W	
Rated coil resistance ±5% (20°C)	26 Ω	96 Ω	392 Ω	

AUX. CONTACT	
Aux. Contact Arrangement	1 Form A
Aux. Contact Current Max.	2A@30VDC/3A@125VAC
Aux. Contact Current Min.	100mA@8V
Aux. Contact Resistance Max.	0.417ohms@30VDC/ 0.150ohms@125VAC

Page |3 Rev K - 05-Feb-2025









Outline Dimensions: inches (mm)

A. Bottom mount-Polar:



B. Side mount-Polar:




Notes:

- 1. The polarity of the product has the polarity of "+A1" and "-A2" on the outer cover, and the non-polar product has no polarity mark.
- 2. The wire size is 22 AWG.

Page |4 Rev K - 05-Feb-2025










Outline Dimensions: inches (mm)

A. Bottom mount-Non-polar:





B. Side mount-Non-polar:




Notes:

- 1. The polarity of the product has the polarity of "+A1" and "-A2" on the outer cover, and the non-polar product has no polarity mark.
- 2. The wire size is 22 AWG.

Page |5 Rev K - G0-Exti-2025







Application Notes

- 1. Be sure to use split washers to prevent nuts from loosening, all the terminals or conductors must be in direct contact with the contactor's terminals. Nut tightening torque is specified below. Exceeding the maximum torque can lead to product failure.
 - a. Contact torque: 30 40 lb.in (3.4 4.5 N.m) Max.
 - b. Mounting torque: 20 lb.in (2.3 N.m)
- 2. Contact terminals are polarized so refer to drawing during connecting. We suggest using a varistor rather than diode as a surge protector.
- 3. Do not use if dropped.
- 4. Avoid installing in a strong magnetic field (close to a transformer or magnet), or near a heat source.
- 5. Electrical life:
 - Use per load capability and life cycle limits so as not to cause a function failure (treat the contactor as a product with specified life and replace it when necessary). It is possible to make parts burn around the contactor once operating failure occurs. It is necessary to take layout into account and to make sure power shall be cut off within 1 second.
- 6. Lifetime of internal gas diffusion: The contactor is sealed and filled with gas, lifetime of gas diffusion is determined by temperature in contact chamber (ambient temperature + temperature generated by contact operation). Operate only in an ambient temperature from -40 to +85 °C.
- 7. Coil drive power must be greater than coil power or it will reduce performance capability.
- 8. Avoid debris or oil contamination on the main terminals to optimize contact and avoid excess heat generation.

Page |6 Rev K - 05-Feb-2025







Quality Revision History

Revision	Date	Description of Changes
Α	12/27/2022	Added "B" to the nomenclature with Aux. contact.
В	03/15/2023	Added current carry graph.
С	06/07/2023	Fixed title name in the operate release time section.
D	09/20/2023	Added 1000V version.
Е	12/13/2023	Added notes under the non-polarized load table, fixed.
F	03/06/2024	Added resistance specifications.
G	06/12/2024	Added side mount version.
Н	09/04/2024	Moved current carry graph to second page.
1	12/18/2024	Updated drawings for bottom mount polar and non-polar / side mount polar and non-polar.
	02/12/2024	·
J	02/12/2024	Removed "B" NC normally close from the nomenclature.
K	10/30/2024	Changed the wire direction in the ALEV100.

Page | 7 Rev K - 05-Feb-2025