




Housing Material: Polyester, Black UL94V-0
 Contacts: Phosphor Bronze 30µin Au plating over Ni
 Leads: Matte Sn over Ni plating
 Shield: Cu Alloy with Ni plating 40µin min
 Durability: 1000 mating cycles
 Dimensions: Inch [mm]
 Tolerances: ±0.008 inch if not specified



PART NO. : HFJ12-1G06ERL

2 PORT FASTJACK™ WITH 1000BASE-T MAGNETICS
 DESIGNED FOR IEEE802.3ab GIGABIT APPLICATIONS
 LEAD-FREE/ROHS COMPLAINT
 COMPATIBLE TO LEAD-FREE WAVE SOLDERING PROCESS
 FOR THROUGH HOLE COMPONENTS
 OPERATING TEMPERATURE 0/70°C




ELECTRICAL SPECIFICATIONS @ 25° C

URNS RATIO	1:1 ±3%
OCL (100KHz,0.1V,8mA)	350µH min
INSERTION LOSS	
1-100MHz	-1.1dB max
RETURN LOSS	
1-40MHz	-18dB min
60MHz	-14dB min
80MHz	-12dB min
100MHz	-10dB min
CROSSTALK 1-100MHz	-35dB typ
CMR 1-30MHz	-38dB typ
30-60MHz	-35dB typ
60-100MHz	-30dB typ
ISOLATION	1,500Vrms


HALO/PBL

CALIFORNIA, USA
 KOWLOON, HONG KONG
 SINGAPORE

TITLE	FastJack™ 1X2	SIGNATURES	DATE	REV.	DESC.	DATE
FOR	GIGABIT ETHERNET	DRAWN	PETER LU	5/18/06	A	
PART NO.	HFJ12-1G06ERL	CHECKED				
SCALE	NONE	APPROVED				
PAGE	1 OF 2	FILE	FJ121G06ERL.DWG			



RECOMMENDED P.C. BOARD PATTERN (COMP. SIDE)
DIMENSIONS: INCH [mm]



RECOMMENDED PANEL CUTOUT

HALO/PBL CALIFORNIA, USA KOWLOON, HONG KONG SINGAPORE	TITLE FastJack™ 1X2		SIGNATURES		DATE	REV.	DESC.	DATE
	FOR GIGABIT ETHERNET		DRAWN PETER LU		5/18/06	A		
	PART NO. HFJ12-1G06ERL		CHECKED					
	SCALE NONE		APPROVED					
	PAGE 2 OF 2		FILE FJ121G06ERL.DWG					