

PART NO. : HFJT1-RP22-L12RL




FASTJACK™ (TAB-UP) WITH 10/100BASE-TX MAGNETICS
DESIGNED FOR FAST ETHERNET IEEE802.3af APPLICATIONS
POWER ON USED OR UNUSED PAIRS FOR UP TO 350mADC
RoHS COMPLIANT

COMPATIBLE TO LEAD-FREE WAVE SOLDERING PROCESS
FOR THROUGH HOLE COMPONENTS

OPERATING TEMPERATURE 0 TO 55°C

ELECTRICAL SPECIFICATIONS @ 25° C

Turns Ratio	1CT:1 ±3%
OCL (100KHz,0.1Vrms,8mA)	350µH min
DCR P1-P2,P3-P6	0.9Ω max
Insertion Loss 0.1-100MHz	-1.1dB max
Return Loss 0.5-30MHz	-18dB min
40MHz	-15.5dB min
50MHz	-13.6dB min
60-80MHz	-12dB min
Crosstalk 0.1-100MHz	-38dB typ
CMR 0.1-30MHz	-50dB typ
30-60MHz	-40dB typ
60-100MHz	-30dB typ
Isolation	1,500Vrms






HALO/PBL

CALIFORNIA, USA
KOWLOON, HONG KONG
SINGAPORE

TITLE	FastJack™ SINGLE
FOR	FAST ETHERNET IEEE802.3af
PART NO.	HFJT1-RP22-L12RL
SCALE	NONE
PAGE	1 OF 2

SIGNATURES	DATE	REV.	DESC.	DATE
DRAWN PETER LU	5/27/09	A	FIRST ISSUE	5/27/09
CHECKED LEI KEONG	5/27/09			
APPROVED PETER LU	5/27/09			
FILE HFJT1-RP22-L12RL.DWG				

c7us



RECOMMENDED P.C. BOARD PATTERN (COMP. SIDE)

Housing Material: Polyester, Black UL94V-0
 Contacts: Phosphor Bronze 30µin Au plating over Ni
 Leads: Matte Sn over Ni
 Shield: Cu Alloy with Ni plating 40µin min
 Durability: 1000 mating cycles
 Dimensions: Inch [mm]
 Tolerances: ±0.008 inch if not specified

HALO/PBL

CALIFORNIA, USA
 KOWLOON, HONG KONG
 SINGAPORE

TITLE	FastJack™ SINGLE	
FOR	FAST ETHERNET IEEE802.3af	
PART NO.	HFJT1-RP22-L12RL	
SCALE	NONE	PAGE 2 OF 2

SIGNATURES	DATE	REV.	DESC.	DATE
DRAWN PETER LU	5/27/09	A	FIRST ISSUE	5/27/09
CHECKED LEI KEONG	5/27/09			
APPROVED PETER LU	5/27/09			
FILE HFJT1-RP22-L12RL.DWG				