


Bluetooth LE Module

ME54BS61



Datasheet

V 1.0.0



ME54BS61-nRF54L15

Ultra-Small Size, Ultra-Low Power Consumption, BLE 6.0 Supported Bluetooth Module

The ME54BS61 is a highly flexible, ultra-low power consumption, cost-effective, and compact-sized Bluetooth module based on the nRF54L15 WLCSP. It features a powerful Arm® Cortex®-M33 CPU with a core operating speed of up to 128MHz, along with 1.5MB of NVM space and 256 KB of RAM. The module comes with an onboard antenna, highlighting the superior performance of the nRF54 series, and provides more GPIOs for development. Its ultra-low system power consumption, excellent RF performance, and powerful supporting resources make it an ideal solution for Bluetooth connectivity.

FEATURES



Bluetooth 6.0



Ultra-small size



Ultra-low Power




Multi-Protocol supports:
Bluetooth LE 6.0 Channel Sounding, Bluetooth Mesh, Thread, Matter, and proprietary 2.4 GHz protocols


KEY PARAMETER

ME54BS61			
Chip Model	nRF54L15	Antenna	Antenna-free
Module Size	6.0×6.0×1.8mm	GPIO	30
Flash	1.5MB	RAM	256 KB
Receiving Sensitivity	-96dBm	Transmission Power	-8 ~ +7dBm
Current(TX)	0dBm-5mA	Current(RX)	3.2mA


APPLICATION




Smart Home




Computer Accessories




Virtual reality and Augmented reality



Game controllers and Remotes



Medical Devices



Industrial IoT

STORAGE CONDITIONS

- **Please use this product within 6 months after signing the receipt.**
 - This product should be stored without opening the package at an ambient temperature of 5~35°C and a humidity of 20~70%RH.
 - This product should be left for more than 6 months after receipt and should be confirmed before use.
 - The product must be stored in a non-corrosive gas (Cl₂, NH₃, SO₂, NO_x, etc.).
 - To avoid damaging the packaging material, do not apply any excessive mechanical shocks, including but not limited to sharp objects adhering to the packaging material and product dropping.
- **This product is suitable for MSL2 (based on JEDEC standard J-STD-020).**
 - After opening the package, the product must be stored at ≤30°C/<60%RH. It is recommended to use the product within 3-6 months after opening the package.
 - When the color of the indicator in the package changes, the product should be baked before welding.
- **Baking is not required for one year if exposure is limited to <30°C and 60%RH. Refer to MSL2 for exposure criteria for moisture sensitivity level. If exposed to (≥168h@85°C/60%RH) conditions or stored for more than one year, recommended baking conditions.**
 1. 120 ±5/-5°C, 8 hours, 1 time
Products must be baked individually on heat-resistant trays because the materials (base tape, reel tape, and cover tape) are not heat-resistant, and the packaging material may be deformed at temperatures of 120 °C;
 2. 90 °C ±8/-0 °C, 24hours, 1times
The base tape can be baked together with the product at this temperature. Please pay attention to the uniformity of heat.

HANDLING CONDITIONS

- Be careful in handling or transporting products because excessive stress or mechanical shock may break products.
- Handle with care if products may have cracks or damages on their terminals. If there is any such damage, the characteristics of products may change. Do not touch products with bare hands that may result in poor solder ability and destroy by static electrical charge.

QUALITY

Cognizant of our commitment to quality, we operate our own factory equipped with state-of-the-art production facilities and a meticulous quality management system. We hold certifications for ISO9001, ISO14001, ISO27001, OHSAS18001, BSCI.

Every product undergoes stringent testing, including transmit power, sensitivity, power consumption, stability, and aging tests. Our fully automated module production line is now in full operation, boasting a production capacity in the millions, capable of meeting high-volume production demands.

COPYRIGHT STATEMENT

This manual and all the contents contained in it are owned by Shenzhen Minewsemi Co., Ltd. and are protected by Chinese laws and applicable international conventions related to copyright laws.

The certified trademarks included in this product and related documents have been licensed for use by MinewSemi. This includes but is not limited to certifications such as BQB, RoHS, REACH, CE, FCC, BQB, IC, SRRC, TELECOM, WPC, RCM, WEEE, etc. The respective textual trademarks and logos belong to their respective owners. For example, the Bluetooth® textual trademark and logo are owned by Bluetooth SIG, Inc. Other trademarks and trade names are those of their respective owners. Due to the small size of the module product, the "®" symbol is omitted from the Bluetooth Primary Trademarks information in compliance with regulations.

The company has the right to change the content of this manual according to the technological development, and the revised version will not be notified otherwise. Without the written permission and authorization of the company, any individual, company, or organization shall not modify the contents of this manual or use part or all of the contents of this manual in other ways. Violators will be held accountable in accordance with the law.

RELATED DOCUMENTS

- [MinewSemi_Product_Naming_Reference_Manual](https://en.minewsemi.com/file/MinewSemi_Product_Naming_Reference_Manual_EN.pdf)
https://en.minewsemi.com/file/MinewSemi_Product_Naming_Reference_Manual_EN.pdf
- [MinewSemi_Connectivity_Module_Catalogue](https://en.minewsemi.com/file/MinewSemi_Connectivity_Module_Catalogue_EN.pdf)
https://en.minewsemi.com/file/MinewSemi_Connectivity_Module_Catalogue_EN.pdf



For product change notifications and regular updates of Minewsemi documentation, please register on our website: www.minewsemi.com

MINESEMI

SHENZHEN MINEWSEMI CO., LTD.



0086-755-2801 0353

<https://minewsemi.com>minewsemi@minew.com<https://store.minewsemi.com>

No.8, Qinglong Road, Longhua District, Shenzhen, China