

# SAC-4P-M12FSS PE SH US/.../... - Power cable



1292086

<https://www.phoenixcontact.com/ca/products/1292086>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power cable, 4-position, PVC, black, shielded (Advanced Shielding Technology), free cable end, on Socket straight M12, coding: S, cable length: Free input (0.2 ... 40.0 m)

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Protection against incorrect connection using special S-coding
- Shield power reliably – 360° shielding to reduce electromagnetic loads

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1292086                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | XX                             |
| Product key                          | AF1IKH                         |
| Weight per piece (including packing) | 22.22 g                        |
| Weight per piece (excluding packing) | 22.22 g                        |
| Country of origin                    | US                             |

# SAC-4P-M12FSS PE SH US/.../... - Power cable



1292086

<https://www.phoenixcontact.com/ca/products/1292086>

## Technical data

### Product properties

|                      |              |
|----------------------|--------------|
| Product type         | Power cable  |
| Application          | Power supply |
| Number of positions  | 4            |
| No. of cable outlets | 1            |
| Shielded             | yes          |
| Coding               | S            |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Material specifications

|                                        |                              |
|----------------------------------------|------------------------------|
| Flammability rating according to UL 94 | V0                           |
| Material of grip body                  | PP                           |
| Contact material                       | CuZn                         |
| Contact surface material               | Ni/Au                        |
| Contact carrier material               | PA                           |
| Material for screw connection          | Zinc die-cast, nickel-plated |

### Electrical properties

|                       |                                          |
|-----------------------|------------------------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$               |
| Nominal voltage $U_N$ | 600 V AC (Dielectric withstand 2.2KV AC) |
| Nominal current $I_N$ | 16 A                                     |

### Mechanical properties

#### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | > 100 |
|-----------------------------|-------|

### Connector

#### Connection 1

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

#### Connection 2

|             |                     |
|-------------|---------------------|
| Type        | Socket straight M12 |
| Coding type | S (Power)           |

### Cable/line

|              |                             |
|--------------|-----------------------------|
| Cable length | Free input (0.2 ... 40.0 m) |
|--------------|-----------------------------|

#### TC-ER 600V [PVC]

|                     |   |
|---------------------|---|
| Number of positions | 4 |
|---------------------|---|

# SAC-4P-M12FSS PE SH US/.../... - Power cable



1292086

<https://www.phoenixcontact.com/ca/products/1292086>

|                                               |                                                 |
|-----------------------------------------------|-------------------------------------------------|
| Shielded                                      | yes                                             |
| Cable type                                    | TC-ER 600V [PVC]                                |
| Conductor structure, voltage supply           | 41/30                                           |
| AWG power supply                              | 14                                              |
| Wire diameter incl. insulation                | 2.87 mm ±0.05 mm                                |
| External cable diameter                       | 10.54 mm                                        |
| Outer sheath, material                        | PVC                                             |
| External sheath, color                        | black                                           |
| Conductor material                            | Bare Cu litz wires                              |
| Material wire insulation                      | PVC, nylon covering                             |
| Single wire, color                            | black, white, red, green                        |
| Thickness, insulation                         | approx. 0.50 mm (20 mil)                        |
| Thickness, outer sheath                       | approx. 1.40 mm (55 mil)                        |
| Nominal voltage, cable                        | 600 V                                           |
| Minimum bending radius, fixed installation    | 10 x D                                          |
| Minimum bending radius, flexible installation | 15 x D                                          |
| Dynamic load capacity (bending)               | Max. bending cycles: 1000000                    |
| Flame resistance                              | FT4                                             |
| Fire protection in rail vehicles              | UL TC-ER                                        |
| Other resistance                              | oil resistant                                   |
|                                               | sunlight resistant                              |
|                                               | direct burial                                   |
|                                               | water resistant                                 |
| Ambient temperature (operation)               | -40 °C ... 90 °C (cable, fixed installation)    |
|                                               | -40 °C ... 90 °C (Cable, flexible installation) |

## Environmental and real-life conditions

### Ambient conditions


|                                 |                                  |
|---------------------------------|----------------------------------|
| Degree of protection            | IP65                             |
|                                 | IP67                             |
| Ambient temperature (operation) | -25 °C ... 85 °C (Plug / socket) |

## Standards and regulations

|                          |                   |
|--------------------------|-------------------|
| Standard designation     | M12 connector     |
| Standards/specifications | IEC 61076-2-111   |
| Standards/specifications | UL 2237           |
| Note                     | Type 4 indoor, 12 |


## Drawings

Dimensional drawing



M12 x 1 socket, straight

Schematic diagram



Pin assignment of M12 socket, 4-pos., S-coded, socket side view


# SAC-4P-M12FSS PE SH US/.../... - Power cable



1292086

<https://www.phoenixcontact.com/ca/products/1292086>

Circuit diagram



# SAC-4P-M12FSS PE SH US/.../... - Power cable



1292086

<https://www.phoenixcontact.com/ca/products/1292086>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27060311 |
| ECLASS-12.0 | 27060311 |
| ECLASS-13.0 | 27060327 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

# SAC-4P-M12FSS PE SH US/.../... - Power cable



1292086

<https://www.phoenixcontact.com/ca/products/1292086>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
8240 Parkhill Drive  
Milton, Ontario L9T 5V7  
1-800-890-2820  
[cdinfo@phoenixcontact.ca](mailto:cdinfo@phoenixcontact.ca)