


Silicone Rubber Insulated Thermocouple Cable / Wire (IEC) Type K

XE-2164-010



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Specifications

| | |
|----------------------------|--|
| General Description | Good electrical and mechanical properties, highly flexible, resistant to oils, acids and other adverse fluids. Good heat resistance to 200°C although not suitable for direct use in high pressure steam applications. |
| Cable Length | 10m |
| Core / Strands | 7/0.2mm |
| Outer Colour | Green |
| + Colour | Green |
| - Colour | White |
| Drain Wire | No |
| Insulation Material | Silicone rubber insulated 7/0.2mm conductors, twisted together with silicone rubber outer jacket |
| Max. Temperature | +200°C |
| Min. Temperature | -40°C |
| Screen | No |
| Standards Met | Colour code (cores & jacket) to IEC-584-3 |
| Thermocouple Type | K |
| Tolerance | Class 2 to IEC-584 |

Ordering Information

| Type | Style | Material | Core/Strands | Length | Manufacturers Number |
|------|-----------|-----------------|--------------|--------------|----------------------|
| K | Flat Pair | Silicone rubber | 7/0.2mm | 10m (32.8ft) | XE-2164-010 |