


## **Type T PVC Insulated Flat Pair Thermocouple Cable / Wire (IEC)**

**XE-2303-010**



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

## Specifications

<b>General Description</b>	Good general purpose insulation for 'light' environments. Waterproof and very flexible.
<b>Cable Length</b>	10m
<b>Cable Type</b>	Flat pair construction
<b>Core / Strands</b>	13/0.2mm
<b>Conductor Cross Section 13/0.2 (mm<sup>2</sup>)</b>	0.408
<b>Outer Colour</b>	Brown
<b>+ Colour</b>	Brown
<b>- Colour</b>	White
<b>Drain Wire</b>	No
<b>Insulation Material</b>	PVC Insulated
<b>Loop Resistance 13/0.2 (Ohms per combined metre)</b>	1.2
<b>Max. Temperature</b>	+105°C
<b>Min. Temperature</b>	-10°C
<b>+ Conductor</b>	Copper
<b>- Conductor</b>	Constantan
<b>Screen</b>	No
<b>Standards Met</b>	Colour code (cores & jacket) to IEC-584-3
<b>Thermocouple Type</b>	T
<b>Tolerance</b>	Class 2

## Ordering Information

Type	Style	Material	Core/Strands	Length	Manufacturers Number
T	Flat Pair	PVC	13/0.2mm	10m (32.8ft)	XE-2303-010