


P1: M-004

P2: M-044

Customer No.: No.1



MARKING:

(UL) SJT 3/C 14AWG(2.08MM²) VW-1 105°C 300V E204978C(UL) SJT 3/C 2.08MM²(14AWG) FT2 105°C 300V E204978


P1,P2: cULus E210037-VN

*NOTE: All relevant materials are complied with RoHS directive .
THE CABLE MARKING IS CONCAVE LETTERING MOULD

106121B2F14A(FP218-00)

P1	P2	
L	L	BLACK
N	N	WHITE
E	E	GREEN

PACKING:



MSL-VN- ⚠ ⚠	3	UL SJT 14AWG x 3C, OD 9.3mm, JACKET LIST, DRAWING No. EPSVT011403C-147		H5TC21-0304	L-40mm	M304	
	2	MOLDED PVC 35P, JACKET LIST		H1BC02-0304		M304	
		BRACKET:9745C, JACKET LIST		A1QC42-0767	1	M767	
		TERMINAL:98745L		A1QB43-0257	3	M257	
	1	MOLDED PVC 35P, JACKET LIST		H1BC02-0304		M304	
		BRACKET: YS-014, JACKET LIST		A1QC10-0767	1	M767	
		TERMINAL: 2x4mm 98672BS-1		A1QB07-0257	3	M257	
	No.	DESCRIPTION				Q'TY	Supplier
	APPROVED		CompuCableUSA			Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm	
	CHECKED	HU					
DESIGNER	XJW						
DRAWING	DAI						
Y PRINTING							
Y MODEL LOGO							
LOGO & CABLE							
LOGO							
±50mm							
	DATE	11/OCT/23	ITEM NO.	AC-C1514-XX		UNIT:mm	

REV.9 2023.10.11	ADD COLOR	REV.8 2023.10.07	MODIFY PRINTING
REV.7 2023.07.19	MODIFY CABLE LETTERING CONTENT	REV.6 2023.06.30	MODIFY MODEL LOGO
REV.5 2021.12.13	MODIFY CABLE LETTERING CONTENT	REV.4 2017.09.04	MODIFY MODEL LOGO & CABLE
REV.3 2015.11.03	MODIFY P2 MODEL LOGO	REV.2 2015.02.04	MODIFY MODEL LOGO
REV.1 2013.06.17	MODIFY P2 MODEL LOGO		

NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm