



PRODUCT NR:	DIM A	DIM M	P.C.B. THK
88981-001	13.80	2.80 REF	1.6mm
88981-002	14.80	3.80 REF	2.4mm
88981-003	13.20	2.20 REF	1.6mm



NOTES:

- 1 PULL OUT FORCE WITH SHAFT $\varnothing 0.30\text{mm}$ 0.1N MIN./ 0.8N MAX.
- 2 FOR P.C. BOARD LAYOUT SEE CUSTOMER DRAWING 88974.

PLATING ON CONTACT AREA
POSITIONS 1&2
1.27u Au MIN.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		BERG ELECTRONICS	
lir	ech no	dr	date	linear		projection		title	
A	H10346	DAN	920424					3 ROW RA RCP	
B	H20350	DAN	920426					STB MINICOAX INSERT	
C	H20665	DAN	921014	angles				product family	METRAL (tm)
D	H20755	DAN	921124	dr	D. ANDREWS	920424		size	dwg no
E	H30454	DAN	930622	engr	M. MEIJER	960618		scale	213
F	H60311	MME	960618	chr	P. SCHALK	920424		1 of 1	
				appd	D. ANDREWS	920424			
sheet index	revision	F							
	sheet	1							

PDM: Rev:F

STATUS: Released

Printed: Oct 01, 2010