








ISS.	AMEND	DATE
1	ISSUED	12/08/25




2x HOLE VARIANTS
Ø3.5mm CSK 82° x Ø5.85
'X' VERSION HAS Ø2.5 HOLES



SPECIFICATION

Impedance:	50 Ohm
Frequency:	10MHz - 18GHz
Operating Temp:	-30°C to 80°C
Plug A:	Female SMA
Plug B:	Female SMA

VARIANTS	
PART NO.	HOLE DETAILS
CP30260	HOLE Ø3.50 X CSK 82° X Ø5.85
CP30260X	PLAIN HOLE Ø2.50



RoHS
COMPLIANT

TOLERANCE

NO DEC. PLACE ±
1 DEC. PLACE ±
2 DEC. PLACE ±
HOLE Ø ±
ANGLES ±
UNLESS OTHERWISE STATED

Cliff Electronic Components Ltd.

76 Holmethorpe Avenue, Holmethorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2025

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

MATERIAL: SEE TABLE

FINISH: SEE TABLE

DRAWN: T.J.O.

APPROVED: D.P.J.

3rd ANGLE PROJECTION:

TITLE: FEED THROUGH SMA (F-F)

DRWG. No. CP30260

DO NOT SCALE

FORM: A4DRWGH