

INP3.6-12x310



DESCRIPTION

WHERE TO BUY

RESOURCES

This thin-film amorphous silicon flexible indoor solar module is laminated with standard duty PET and foil tape contact terminals. It's well suited to collect artificial lighting in indoor settings such as warehouses, offices, and retail spaces.

Electrical Specifications:

Max Voc all light levels = 5.5V

200 Lux

- Power: 0.150mW
- Operating Voltage: 2.4V

- Current: 0.062mA
- Average Voc: 3.6V
- Isc: 0.08mA


1000 Lux

- Power: 0.982mW
- Operating Voltage: 3.2V
- Current: 0.307mA
- Average Voc: 4.0V
- Isc: 0.40mA

Physical Specifications:

- Dimensions: 310.0 x 11.86 (mm) / 12.204 x 0.466 (in)
- Weight: 0.01oz / 0.84g
- Thickness: 0.22mm

IV Curve



CONNECT WITH US

NAVIGATION

Products

Markets

PowerFilm Solar, Inc.

1287 XE Place

Ames, Iowa 50014

Custom Solutions

515-292-7606

Technology

Contact Us

Education

Explore

© 2025 PowerFilm Solar, Inc. All rights reserved

Privacy

Back to Top