


LL200-3.6-75



DESCRIPTION

WHERE TO BUY

RESOURCES

This thin-film amorphous silicon flexible indoor solar module is laminated with standard duty PET and foil tape contact terminals. It's well suited to collect artificial lighting in indoor settings such as warehouses, offices, and retail spaces.

Electrical Specifications:

Max Voc all light levels = 5.5V

200 Lux

- Power: 0.206mW
- Operating Voltage: 2.4V
- Current: 0.086mA
- Average Voc: 3.6V
- Isc: 0.1mA

1000 Lux


- Power: 1.354mW
- Operating Voltage: 3.2V
- Current: 0.423mA
- Average Voc: 4.0V
- Isc: 0.6mA

Physical Specifications:

- Dimensions: 73.0 x 74.0 (mm) / 2.87 x 2.91 (in)
- Weight: 0.05oz / 1.42g

- Thickness: 0.22mm

IV Curve



CONNECT WITH US

Products
Markets
Custom Solutions
Technology
Education
Explore

1287 XE Place
Ames, Iowa 50014

515-292-7606

Contact Us