

20V/6A N-Channel MOSFET

Features




- Trench Power LV MOSFET technology
- High Power and current handling capability

Product Summary

V_{DS}	$R_{DS(ON)}$ MAX	I_D MAX
20V	18mΩ@4.5V	6A
	22mΩ@2.5V	

Application







- PWM application
- Load switch






Absolute Maximum Ratings (TA=25°C unless otherwise noted)				
Symbol	Parameter		Rating	Unit
Common Ratings (TC=25°C Unless Otherwise Noted)				
V _{DS}	Drain-Source Breakdown Voltage		20	V
V _{GS}	Gate-Source Voltage		±10	V
T _J	Maximum Junction Temperature		150	°C
T _{STG}	Storage Temperature Range		-50 to 155	°C
I _S	Diode Continuous Forward Current	Tc=25°C	6	A
Mounted on Large Heat Sink				
I _{DM}	Pulse Drain Current Tested	Tc=25°C	25	A
I _D	Continuous Drain Current	Tc=25°C	6	A
P _D	Maximum Power Dissipation	Tc=25°C	1.25	W
R _{θJA}	Thermal Resistance Junction-to-Ambient		100	°C/ W

Electrical Characteristics (T _J =25°C unless otherwise noted)						
Symbol	Parameter	Condition	Min	Typ	Max	Unit
Static Electrical Characteristics @ T _J = 25°C (unless otherwise stated)						
BV _{(BR)DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =250μA	20	--	--	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =20V, V _{GS} =0V	--	--	1	μA
I _{GSS}	Gate-Body Leakage Current	V _{GS} =±10V, V _{DS} =0V	--	--	±100	nA
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =250μA	0.45	0.7	1.0	V
R _{DS(on)}	Drain-Source On-State Resistance	V _{GS} =4.5V, I _D =5A	--	12	18	mΩ
		V _{GS} =2.5V, I _D =4A	--	15	22	mΩ
Dynamic Electrical Characteristics @ T _J = 25°C (unless otherwise stated)						
C _{ISS}	Input Capacitance	V _{DS} =10V, V _{GS} =0V, f=1MHz	--	885	--	pF
C _{OSS}	Output Capacitance		--	135	--	pF
C _{RSS}	Reverse Transfer Capacitance		--	120	--	pF
Switching Characteristics						
Q _g	Total Gate Charge	V _{DS} =10V, I _D =6A, V _{GS} =4.5V	--	11	--	nC
Q _{gs}	Gate Source Charge		--	1.75	--	nC
Q _{gd}	Gate Drain Charge		--	3	--	nC
t _{d(on)}	Turn-on Delay Time	V _{DD} =10V, R _L =1.5Ω, V _{GS} =4.5V, R _G =3Ω	--	7	--	nS
t _r	Turn-on Rise Time		--	45	--	nS
t _{d(off)}	Turn-Off Delay Time		--	30	--	nS
t _f	Turn-Off Fall Time		--	50	--	nS
Source- Drain Diode Characteristics						
V _{SD}	Forward on voltage	T _J =25°C, I _S =6A	--	--	1.2	V

Typical Operating Characteristics



SOT-23-3L Package information



Symbol	Dimensions in Millimeters(mm)		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.042	0.050
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.042	0.046
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.112	0.120
E	1.500	1.700	0.060	0.068
E1	2.650	2.950	0.106	0.118
e	0.950TYP		0.037TYP	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°