


EBW Series

Manganin/Aluchrom Alloy Current Sense

The EBW Series are manufactured using electron beam welding technology. This allows the joining of different alloys with great accuracy and tolerance. The EBW Series have heavy copper connectors, excellent long term stability and low inductance. These components can tolerate soldering temperatures of 350C for 30 seconds or 250C for 10min. These can be mounted using re-flow soldering or welding on copper. The EBWA can handle a power of 5W up to 100A at 0.5mΩ. The EBWB can handle a constant power of 7W at 0.2mΩ and a continuous load of 180A at 0.2mΩ.



CERTIFICATIONS

BN ES ISO 9001: 2008

ISO/TS 16949: 2009

APPLICATIONS

- Current sensors for hybrid power sources
- Frequency converters
- High current automotive applications.

SERIES SPECIFICATION

Model	Power (W)	Resistance (m Ω)	Material	TCR (20°C - 60°C)	Weight (g)
EBWA-M	5	0.5	Manganin	±70ppm/°C	0.4081
	4	1	Manganin	±50ppm/°C	0.1994
EBWA-N	4	2	Aluchrom Alloy	±50ppm/°C	0.2726
	3	3	Aluchrom Alloy	±50ppm/°C	0.1832
	2.5	4	Aluchrom Alloy	±50ppm/°C	0.1363
EBWB-M	7	0.2	Manganin	±100ppm/°C	1.5138
	6	0.5	Manganin	±75ppm/°C	0.5652
EBWB-N	6	1	Aluchrom Alloy	±50ppm/°C	0.8573
	4	2	Aluchrom Alloy	±50ppm/°C	0.4287
	3.5	3	Aluchrom Alloy	±50ppm/°C	0.2858


CHARACTERISTICS

Tolerance	±1% (F), ±5% (J)
TCR	20°C-60°C Max. ±200ppm/°C
Operating Temperature	-55°C to 170°C

PERFORMANCE DATA

Thermal Shock	-65°C, 25°C, 125°C, 25°C 25cycles	±0.1%
Short Time Overload	Rated Power X 5 for 5 secs.	±0.2%
Resistance to Soldering Heat	350°C 30 sec. or 250°C 10 min.	±0.2%
Moisture Resistance	90~98%RH, +25°C, +65°C, -10°C 10 cycles	±0.2%
High Temperature Exposure	140°C for 250 hours	±0.2%
Vibration High Frequency	15g 10 to 2000Hz 36 cycles	±0.2%
Inductance		<3nH
Load Life	90 min "ON" 30 min "OFF" for 2000 hours	±1.0%


Derating



EBW Series

Manganin/Aluchrom Alloy Current Sense


PULSE ENERGY/POWER FOR CONTINUOUS OPERATION



EBWA: Max. curve is only valid for the resistance value 0.5m. The min. curve is only valid for the resistance value 4m. For other resistance values the area in between the max. and the min. curve is valid


EBWB: Max. curve is only valid for the resistance value 0.2m. The min. curve is only valid for the resistance value 2m. For other resistance values the area in between the max. and the min. curve is valid

DIMENSIONS




	L	W	A	T
EBWA	10mm $\pm 3/-2$ 0.394"	5.2mm $\pm 3/-2$ 0.205"	2mm $\pm 0/-5$ 0.079"	0.6 max. 0.024"
EBWB	15mm ± 2 0.591"	7.75mm $\pm 3/-2$ 0.305"	4.2mm $\pm 1/-7$ 0.165"	1.0 max. 0.039"

Land Pattern




Tape and Reel

EBWA



EBWB



Reel: ~12.95" (329mm)

Qty. per reel: EBWA: 3000pcs
EBWB: 2000pcs

ORDERING INFORMATION

Standard Part Numbers

EBWA-MR0005FE
EBWA-MR0010FE
EBWA-MR0020FE
EBWA-MR0030FE
EBWA-MR0040FE
EBWB-MR0002FE
EBWB-MR0005FE
EBWB-MR0010FE
EBWB-MR0020FE
EBWB-MR0030FE

EBWA - MR0020FE T

Series
Electron
Beam Weld

Size

Alloy

M = Manganin
N = NiCr

Resistance

RoHS Compliant

Tolerance

F = 1%
J = 5%

Tape and reel

EBWA: 3000 pc/reel
EBWB: 2000 pc/reel