






- SPECIFICATIONS:
- MATERIAL:
 - A. SCREW: M2.5 STEEL, ZINC PLATED
 - B. BODY : PA66, UL94 V-0
 - C. BLOCK: BRASS, NI PLATED
 - D. COVER: PA66, UL94 V-0
 - E. CONTACT : COPPER ALLOY
 - F. MTG. SCREW: M2.5 STEEL, ZINC PLATED
 - WIRE SIZE: 30 TO 12AWG
 - ELECTRICAL RATING : 300V, 18A
 - MAX TORQUE : 5.0LBF. IN
 - WIRE STRIP LENGTH: .24 IN. (6.00mm)
 - OPERATING TEMPERATURE:-40°C TO +115°C



ENGINEERING NUMBER LEGEND

M750B - 14 - 2 - XX - X

SERIES STYLE PITCH POLES COLOR
1- BLACK
3- GREEN

CONTACT FACTORY FOR OPTIONAL COLORS

TOLERANCES			
MM	TOL	INCH	TOL
0-6	±0.25	0-.24	±.010
>6-30	±0.40	>.24-1.18	±.016
>30-120	±0.50	>1.18-4.76	±.020
>120	±0.80	>4.76	±.031

FUNCTIONAL SYMBOLS $\frac{F}{A} = 0$ $\frac{F}{C} = 0$ $\frac{F}{P} = 0$ DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																				
	DIMENSION UNITS		SCALE		CURRENT REV DESC: ADDED PNS 397141003, 397141005, 397141007 AND 397141009			molex TERMINAL PLUG 5.08MM 45 DEGREE WIRE ENTRY WITH MOUNTING ENDS													
	INCH/MM		3:1																		
	GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 760931 DRWN: ABENJAMINLW 2023/07/06 CHK'D: DNGUYEN62 2023/08/29 APPR: WLEUNG 2023/08/30			PRODUCT CUSTOMER DRAWING													
		MM	INCH																		
4 PLACES ± --- ± ---				INITIAL REVISION:			DOCUMENT NUMBER			DOC TYPE			DOC PART			REVISION					
3 PLACES ± --- ± SEE CHART																					
2 PLACES ± SEE CHART ± SEE CHART				DRWN: RSTONE 2014/04/11 APPR: JFMURPHY 2014/10/16			SD-39714-001			PSD			001			B					
1 PLACE ± SEE CHART ± ---																					
0 PLACES ± --- ± ---				THIRD ANGLE PROJECTION			DRAWING			SERIES			MATERIAL NUMBER			CUSTOMER			SHEET NUMBER		
ANGULAR TOL ± ---																					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							C-SIZE			39714			SEE SHEET-2			GENERAL MARKET			1 OF 2		

[illegible]