


RWS Series

Precision Power Wirewound SMD Resistor



A compact and precision power resistor, manufactured to the highest standards; reliable and robust but still achieving drift of less than 1% and TCR of 10-90ppm/°C when under rated conditions

FEATURES

- High overload capability for surge and pulse applications
- Precision High Power wirewound Resistor
- Low inductance available
- RoHS Compliant

ELECTRICAL SPECIFICATIONS

Type	Wattage	Tolerance	Resistance Range		Resistance Range - Non-inductive	
			Min	Max	Min	Max
RWS05	0.5	D (0.5%) F (1%) J (5%)	R005	1K2	R1	200R
RWS1	1		R005	5K	R1	1K
RWS2	2		R005	12K	R1	2K4
RWS3	3		R01	20K	R1	4K
RWS5	5		R05	50K	R1	10K

CHARACTERISTICS

Tolerance (Code): $\pm 0.5\%$ (D), $\pm 1\%$ (F), $\pm 5\%$ (J)

Operating Temperature: -55°C to $+155^{\circ}\text{C}$

Temperature coefficients: $\pm 90\text{ppm}/^{\circ}\text{C}$ R1-R99, $\pm 50\text{ppm}/^{\circ}\text{C}$ 1R-10R, $\pm 20\text{ppm}/^{\circ}\text{C}$ >10R

Max. working voltage: $(P \times R)^{1/2}$

Short time overload: 5 times rated wattage for 5 seconds $\pm (1.0\% + 0.05\Omega)\Delta R$


Solderability: Bath temperature $235 \pm 5^{\circ}\text{C}$, immersion time 2 ± 0.5 seconds JIS C 5201 4.17 >95% of contact face covered new solder

Resistance to solder heat: Bath temperature $260 \pm 5^{\circ}\text{C}$, immersion time 10 ± 1 seconds JIS C 5201 4.18 $\pm (0.5\% + 0.05\Omega)\Delta R$


Dielectric withstanding voltage: Test voltage >500V, duration 1 minute JIS C 5201 4.7

Load life: $70^{\circ}\text{C} \pm 2^{\circ}\text{C}$, rated DC working voltage applied 1.5 hours on and 0.5 hours off, 1000 hours, $\pm (2.0\% + 0.05\Omega)\Delta R$

Temperature Rise



Derating Curve



(continued)



RWS Series

Precision Power Wirewound SMD Resistor

DIMENSIONS

(mm±0.5)

Type	L ₁	L ₂	H ₁	W ₁	W ₂
RWS05	5.08	1.28	3.25	2.54	1.663
RWS1	7.50	1.75	4.64	3.50	2.405
RWS2	11.00	2.00	4.65	4.50	3.59
RWS3	13.50	2.50	5.65	5.50	4.20
RWS5	20.30	3.00	7.87	7.62	4.90



Recommended Solder Pad Dimensions

Type	L ₄	W ₃
RWS05	2.0	2.2
RWS1	2.5	3.0
RWS2	2.8	4.2
RWS3	3.5	4.8
RWS5	4.0	5.5

ORDERING INFORMATION

Non-Inductive

N R W S 1 F T R

Series

Tolerance
F = 1%
J = 5%
K = 10%

Tape
& Reel