




RECOMMENDED PCB LAYOUT

N = Number of poles
Dim L=Nx5.08
Dim P=(N-1)x5.08

	Dim L	Dim P
2-6p	±0.20	±0.15
7-12p	±0.25	±0.20
13-18p	±0.30	±0.25
19-24p	±0.40	±0.30

SIGN	DATE	DESCRIPTION	APPROVER
△	02.08'06	Standard spec is changed.	Marivn
△	10.15'09	The Safety Approval cULus Passed	Kind
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- ⑩ Terminal body: Brass(CuZn) Tin plated
- ⑪ Terminal screw: Steel Zinc plating "-" slot type
- ⑫ Wire guard: Stainless steel
- ⑬ Terminal housing: Thermoplastic (UL94V-0)

△ Electrical cULus

- Voltage rating: 300VAC
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 14-22
- Stranded wire(AWG): 14-22
- Torque(Lb-In): 3.5
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec

△ Safety Approval:



TA xx 41 x x 0000 G

02 2 CONTACTS	0 Black	Dim A	RoHS
03 3 CONTACTS	5 Green	1 3.8mm	Pb<40,000ppm
... ..	6 Blue	2 3.5mm	
24 24 CONTACTS	8 Grey	3 4.0mm	

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TA - 5.08mm series one interlock							
PART NO.	TAXx41xx0000G			DWG NO.	8TA0205			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				
		Kind 2009.10.15	Marvin 2006.02.08				UNIT: mm	X. ±0.50
							SCALE: NONE	X.X ±0.30
					SHEET: 01/01	REV.: D	X.XX ±0.10	
							X° ±1°	