


P1: M-084A

Customer No.: No.1

MARKING: (UL) SJT 3/C 14AWG(2.08MM²) VW-1 105°C 300V E204978C(UL) SJT 3/C 2.08MM²(14AWG) FT2 105°C 300V E204978 MSL-VN-

P1: dUs E210037-VN

* NOTE: All relevant materials are complied with RoHS directive .
THE CABLE MARKING IS CONCAVE LETTERING MOULD

158BB2F14A(FP465-00)

P1 STRIPPED JACKET 51mm

L ——— SEMI-STRIPPED 12.7mm BLACK
N ——— SEMI-STRIPPED 12.7mm WHITE
E ——— SEMI-STRIPPED 12.7mm GREEN

REV.1 2024.07.12 MODIFY PLUG MODEL AND BRACKET SUPPLIER

NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm

2	UL SJT 14AWG*3C OD 9.3mm, JACKET BLACK, DRAWING No.EPSVT011403C-147		H5TC21-0304K09	1830mm	M304	
1	MOLDED PVC 35P, JACKET BLACK		H1BC02-0304K09		M304	
	⚠️ TERMINAL WITH BRACKET: LP-31M内架-9		A1QC82-1035K09	1	M1035	
No.	DESCRIPTION				Q'TY	Supplier
APPROVED		CompuCableUSA			Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm	
CHECKED	HU					
DESIGNER	XJW					
DRAWING	MuMu					
DATE	12/JUL/24	ITEM NO.	AC-PT14515-XX		UNIT:mm	