





CUSTOMER DRAWING

REVISIONS			
ZONE	REV.	DESCRIPTION	DATE
	PA1	INITIAL RELEASE	2025-01-08
	PA2	NOTE UPDATE	2025-01-14
	PA3	NOTE UPDATE	2025-03-10



STAMP LOGO & SERIES & QR CODE,
SEE NOTE 1.

MOUNTING CUT-OUT




SPECIFICATIONS

Shell Material	Stainless Steel
Sping Material	Corrosion Resistant Stainless Steel
Sealing Material	EPDM
Working Pressure	0~0.6MPa
Safety Pressure	2.0MPa
Operating Temperature	-40~+105 °C
Sealing	Dry Break Sealing, No Leakage
Applicable Fluid	Deionized Water, Glycol, Propylene Glycol
Adapted Hose Inner Dia.	/

1. STAMP LOGO & SERIES & QR CODE.

STAMP EXAMPLE:

Amphenol UQDB06



READING: UQDBP-06TMU03-N000-20250103-00001

CODE NUMBER


DATE IN 8 DIGIT, YYYYMMDD


SEQUENTIAL NUMBER, FROM 00001 TO 99999

NOTES

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM THE AMPHENOL CORP.

Next Assembly

UNLESS OTHERWISE SPECIFIED						APPROVALS			DATE		
LINEAR DIMENSIONS ARE IN MILLIMETERS						PREPARED BY:		Michael Zeng		2025-03-10	
TOLERANCES:						LEAD/PRODUCT ENGINEER:		Jerry Pu			
DIM. RANGE		0.5-3	>3-6	>6-30	>30-120	>120-400		ENGINEERING MANAGER:			
TOLERANCE		±0.1	±0.1	±0.2	±0.3	±0.5		Ran Xiao			
ANGLES = ±2°						PRODUCT GROUP:		C&I			
DIM. & TOL. PER ASME Y14.5M-1994;						AIPG DIVISION:		AIO			
DRM PER MIL-DTL-31000;						MATERIAL SPEC			PROCESS SPEC		
OTHER AMPHENOL STANDARDS: 9-9318						N/A			N/A		
THIRD ANGLE PROJECTION											
											



AMPHENOL CORPORATION

Amphenol Technology (Zhuhai) Co. Ltd.
No. 63 Xingnan Road, Sanzao Town, Jinwan, Zhuhai, PRC

UQDB06 PLUG TM UNF3/4"-16

SIZE	CAGE CODE	DOCUMENT NUMBER	REV
C	90MJ5	UQDBP-06TMU03-000	PA3
SCALE: 2.5:1		REF:	SHEET 1 OF 1