

## iID® TELIDstation

### Smart programming and charging station for TELID®300.pro/eco series

iID®TELIDstation is one of microsensys's desktop RFID-HF devices for wireless data capture. iID® TELIDstation is designed for communication with the family of TELID®300 dataloggers. Device supports programming, data read out and charging of up to six dataloggers simultaneously.

iID® TELIDstation comes with USB-C power supply and several communication interfaces like Bluetooth™ Low Energy 5.1, WiFi\*\* and LAN\*\*.

microsensys offers an attractive component of sensor components for high performance process monitoring.



microsensys GmbH  
In der Hochstedter Ecke 2  
D 99098 Erfurt

TEL +49-361-59874 0  
E-MAIL info@microsensys.de  
FAX +49-361-59874 17  
WEB www.microsensys.de

This data sheet is subject to change. Please contact microsensys for latest technical information. Picture may differ from original product.  
TELIDSTATION 001.DOCX

<b>Basics:</b>	HF RFID read / write / charge unit for up to 6 TELID®300 pro/eco series loggers
<b>Display:</b>	power LED (orange), interface LED (RGB), 6x RF state LEDs (RGB)
<b>RFID Air Interface:</b>	RFID system iID®3000, HF (13,56 MHz)
<b>Standards:</b>	based on ISO15693, ISO14443
<b>Chip support:</b>	TELID®300
<b>Field Direction:</b>	field distributed in TELID nest
<b>Operating Distance:</b>	0...10mm
<b>HOST Interface:</b>	Bluetooth™ 5.1, WiFi, LAN (Ethernet)
<b>Wireless host interface:</b>	Bluetooth direct communication, RESTful API*, TELIDstation website
<b>Communication Modes:</b>	user interface, website operated
<b>Operation Modes:</b>	stand alone
<b>Connectors:</b>	RJ45, communication
	USB-C, device power
<b>Power Supply:</b>	5V±5% (stabilized low noise), max. 1,5A
<b>Interface:</b>	
<b>Software Interface:</b>	iID® interface protocol for TELID®station (GATT characteristics) TELID® library* / TELID® service*
<b>Supported Commands:</b>	Configure_Telid, Read_Telid_Status, Read_Telid_Protocol
<b>Configuration / Operation:</b>	TELID®station internal website
<b>Device Size:</b>	approx. 145 mm x 100 mm x 35 mm
<b>Casing Material:</b>	plastic, black body, clear-sighted cover
<b>Environmental:</b>	
<b>Operating Temperature:</b>	-5°C ... +60°C
<b>Storage Temperature:</b>	-10°C ... +65°C
<b>Protection Class:</b>	IP44
<b>Accessories included:</b>	TELID®station power adapter
<b>Accessories excluded:</b>	adapters for different TELID®300 loggers TELID®station application software (separate ordering)

<b>Type :</b>	<b>38.29.768.00</b>
<b>Downloaded OP System:</b>	iID-3000
<b>Region, Certification:</b>	EU (CE/ETSI), NA/CA*
<b>Emmissions:</b>	EN 300 330, FCC Part 15*

\*) in development / on request / pending \*\*) options may vary by device type