

High-Q, High-Power Multilayer Ceramic Chip Capacitors

P0805C0G8R2C251NTE (0805,C0G,8.2 pF,DC 250 V)

1. Scope

This specification applies to High-Q, High-Power Multilayer Ceramic Chip Capacitors (MLCCs).

Application Scope: High-power RF signal transmission/reception in: Telecommunications base station power amplifiers,Low Earth Orbit (LEO) satellite transceiver systems

2. Part Number System

P	0805	C0G	8R2	C	251	N	T	E
①	②	③	④	⑤	⑥	⑦	⑧	⑨
Series Code	Size Code	Temperature Characteristics	Nominal Capacitance	Capacitance Tolerance	Rated Voltage	Termination Type	Packaging Code	Thickness Code

① Series Code P - High-Q, High-Power MLCC (Internal Electrodes : Cu)

② Size Code (Unit: mm)




Fig.1 Structure & Dimension

Size Code	L	W	L1,L2	g	T	⑨ Thickness Code
0805	2.00 ± 0.10	1.25 ± 0.10	0.20-0.70	0.70 min	0.85 ± 0.10	E

③ Temperature Characteristics

Temperature Characteristics	Operating Temp. Range	Temperature Characteristics		
		Temp. coeff. or Cap. Change	Temp. Range	Ref. Temp.
C0G	-55 °C-125 °C	0±30 ppm/°C	25 °C-125 °C	25 °C

④ Nominal Capacitance

Code	Nominal Capacitance
8R2	8.2 pF

⑤ Capacitance Tolerance

Code	Capacitance Tolerance
C	±0.25 pF

⑥ Rated Voltage

Code	Voltage Values
251	DC 250 V

⑦ Termination Type

Code	Terminal Electrodes	Plating Material
N	Cu	Ni/Sn

⑧ Packaging Code

Code	Square Hole Spacing	Disc Size	Carrier Tape	QTY (Kpcs)
T	4 mm	7 //	Paper	4

3. Technical Specifications and Test Methods

1. Operating Environment

Temp. Characteristics	Temp. Range	Relative Humidity	Atmospheric Pressure
COG	-55 °C-125 °C	≤95% (25 °C)	86 kPa-106 kPa

3.2 Reliability Test Specifications and Methods

Unless otherwise specified, the test methods in Table 1 are based on: GB/T 21041 and GB/T 21042 (IDT IEC 6038)

Table 1: Specifications and Methods

No.	Item	Specification	Test Method
1	Appearance	No obvious defects on ceramic body and termination.	Visual examination under a microscope
2	Size Code	See Fig.1 and ② Size Code	Measuring by gages which precision is not less than 0.01 mm.
3	Capacitance	Within the specified tolerance	Measurement Temperature 18 °C-28 °C Relative Humidity ≤ 80% RH
4	Q	$C \geq 30 \text{ pF}; Q \geq 1400, C < 30 \text{ pF}; Q \geq 800 + 20 \text{ C}$ C: Nominal Capacitance (pF)	Measurement Frequency $C \leq 1 \text{ nF}, f = 1.0 \pm 0.1 \text{ MHz}$ $C > 1 \text{ nF}, f = 1.0 \pm 0.1 \text{ KHz}$ Measurement Voltage $1.0 \pm 0.2 \text{ Vrms}$
5	Insulation Resistance (IR)	$\geq 10,000 \text{ M}\Omega$	Measurement Temperature 18 °C-28 °C Relative Humidity ≤ 80% RH Measurement Voltage Rated Voltage Charging Time 1 min Charge/discharge current ≤ 50 mA
6	Voltage proof	No defects or abnormalities.	Test Voltage $\geq 2.5 \times U_R$ Applied Time $t = 1 - 5 \text{ s}$ Charge/discharge current ≤ 50 mA
7	Temperature characteristic of capacitance	$\text{COG}; \alpha_c \leq \pm 30 \text{ ppm}/^\circ\text{C}(125^\circ\text{C}); -72 \leq \alpha_c \leq \pm 30 \text{ ppm}/^\circ\text{C}(-55^\circ\text{C})$	Pre-drying 16-24 hours Measure the capacitance separately in 25 °C, θ_1 , 25 °C, θ_2 , 25 °C, should satisfied related Temperature Coefficient of Capacitance (α_c) . COG $\theta_1 = -55^\circ\text{C}, \theta_2 = 125^\circ\text{C}$ T.C. Measurement Voltage $1.0 \pm 0.2 \text{ Vrms}$
8	Resistance to soldering heat	Appearance No visible damage and terminations uncovered shall be less than 25%. Cap. Change $\Delta C/C \leq \pm 2.5\%$ or $\pm 0.25 \text{ pF}$, (Whichever is larger) IR Initial specification Q Initial specification Voltage proof No defects or abnormalities.	Pre-heating Temp. : 120 °C-150 °C, Time: 60 s Test Method Solder bath Solder alloy Sn-Ag-Cu(Lead Free Solder) Temperature $(270 \pm 5)^\circ\text{C}$ Duration of immersion $(10 \pm 1) \text{ s}$ Depth of immersion 10 mm Post-treatment Let sit for $(24 \pm 2) \text{ h}$ at room temperature, then measure.

Table 1: Specifications and Methods






No.	Item	Specification	Test Method
9	Solderability	Appearance 95% of the terminations is to be soldered evenly and continuously.	Pre-heating Temp. : 80 °C-120 °C, Time: 10-30 s Test Method Solder bath Flux Solution of rosin ethanol Solder alloy Sn-Ag-Cu (Lead Free Solder) Temperature (245 ± 5) °C Duration of immersion (2.0 ± 0.5) s Depth of immersion 10 mm
10	Substrate bending test	Appearance No defects or abnormalities Cap. Change $\Delta C/C \leq \pm 5\%$ or ± 0.5 pF, (Whichever is larger)	Mounting method Solder the capacitor to the test substrate as shown in Fig 2 Pressurization Method Shown in Fig 3 Flexure 1 mm Holding Time (5 ± 1) s then measure the capacitance  Fig. 2  Fig. 3
11	Adhesive strength of termination	Appearance No defects or abnormalities	Subjected to 3 cycles of lead-free reflow at 260 °C (standard profile) for thermal shock testing, with ~30 minutes between cycles. Mounting method Solder the capacitor to the test substrate and apply the normal force F indicated in Fig. 4 Holding Time $t = (10 \pm 1)$ s Pushing force 0805: F = 10 N  Fig. 4
12	Vibration	Appearance No defects or abnormalities Cap. Change Initial specification IR Initial specification Q Initial specification	Mounting method Solder the capacitor to the test substrate Amplitude 1.5 mm Kind of Vibration A simple harmonic motion Frequency 10 Hz-55 Hz-10 Hz Vibration Time 1 min Repeat this for 2 hours each in 3 perpendicular directions X, Y, Z, total 6 hours.

Table 1: Specifications and Methods

No.	Item	Specification		Test Method																
13	Rapid change of temperature	Appearance	No defects or abnormalities	Subjected to 3 cycles of lead-free reflow at 260 °C (standard profile) for thermal shock testing, with ~30 minutes between cycles.																
		Cap. Change	$\Delta C/C \leq \pm 2.5\%$ or ± 0.25 pF, (Whichever is larger)	Mounting method	Solder the capacitor to the test substrate															
		IR	Initial specification	The number of cycles	100 cycles															
		Q	Initial specification	Temperature Step	<table><tr><td>Step</td><td>Temp.(°C)</td><td>Time (min)</td></tr><tr><td>1</td><td>-55</td><td>30 ± 3</td></tr><tr><td>2</td><td>25</td><td>2-5</td></tr><tr><td>3</td><td>125</td><td>30 ± 3</td></tr><tr><td>4</td><td>25</td><td>2-5</td></tr></table>	Step	Temp.(°C)	Time (min)	1	-55	30 ± 3	2	25	2-5	3	125	30 ± 3	4	25	2-5
		Step	Temp.(°C)	Time (min)																
		1	-55	30 ± 3																
2	25	2-5																		
3	125	30 ± 3																		
4	25	2-5																		
Voltage proof	No defects or abnormalities.																			
		Post-treatment	Let sit for (24 ± 2) h at room temperature, then measure.																	
14	Damp heat, steady state	Appearance	No defects or abnormalities	Subjected to 3 cycles of lead-free reflow at 260 °C (standard profile) for thermal shock testing, with ~30 minutes between cycles.																
		Cap. Change	$\Delta C/C \leq \pm 7.5\%$ or 0.75 pF, (Whichever is larger)	Mounting method	Solder the capacitor to the test substrate															
		IR	≥ 500 Mfi	Test Temperature	(60 ± 2) °C															
		Q	C ≥ 30 pF, Q ≥ 200	Test Humidity	90%–95% RH															
			C < 30 pF, Q $\geq 100 + 10 C/3$	Test Time	(500 ± 12) h															
			C: Nominal Capacitance (pF)	Post-treatment	Let sit for (24 ± 2) h at room temperature, then measure.															
15	High temperature high humidity (steady)	Appearance	No defects or abnormalities	Subjected to 3 cycles of lead-free reflow at 260 °C (standard profile) for thermal shock testing, with ~30 minutes between cycles.																
		Cap. Change	$\Delta C/C \leq \pm 7.5\%$ or 0.75 pF, (Whichever is larger)	Mounting method	Solder the capacitor to the test substrate															
		IR	≥ 500 Mfi	Test Temperature	(60 ± 2) °C															
		Q	C ≥ 30 pF, Q ≥ 200	Test Humidity	90%–95% RH															
			C < 30 pF, Q $\geq 100 + 10 C/3$	Test Voltage	1.0 × U _R															
			C: Nominal Capacitance (pF)	Test Time	(500 ± 12) h															
				Charge/discharge curren	≤ 50 mA															
				Post-treatment	Let sit for (24 ± 2) h at room temperature, then measure.															
16	Endurance	Appearance	No defects or abnormalities	Subjected to 3 cycles of lead-free reflow at 260 °C (standard profile) for thermal shock testing, with ~30 minutes between cycles.																
		Cap. Change	$\Delta C/C \leq \pm 2\%$ or ± 0.2 pF, (Whichever is larger)	Mounting method	Solder the capacitor to the test substrate															
		IR	≥ 1000 Mfi	Test Temperature	125 °C ± 3 °C															
		Q	C ≥ 30 pF, Q ≥ 350	Test Voltage	2.0 × U _R															
			10 pF < C < 30 pF, Q $\geq 275 + 5 C/2$	Test Time	(1000 ± 12) h															
			C ≤ 10 pF, Q $\geq 200 + 10 C$	Charge/discharge curren	≤ 50 mA															
			C: Nominal Capacitance (pF)	Post-treatment	Let sit for (24 ± 2) h at room temperature, then measure.															

Table 1: Specifications and Methods

No.	Item	Specification	Test Method	
17	Beam Load Test	Destruction value Destruction value should be exceed following one 0805 ≥ 4 N	Mounting method Speed supplied the Stress Load < Size Code:0805 max >  Fig. 5	Place the capacitor in the beam load fixture as Fig 5/6 0402min : 0.5 mm/s , 0201: 0.1 mm/s < Size Code:1206 min >  Fig. 6
18	ESR	See test report	Measurement Frequency Measurement Temperature Measurement Instrument	500MHz-3GHz Room Temperature Keysight 4991B
19	SRF	See test report	Measurement Temperature Measurement Instrument	Room Temperature Keysight 4991B/5080B

4. Packaging, Shipment and storage

4.1 Packaging

4.1.1 packaging type

Reel Packaging (standard carrier tape disc packaging), single disc smallest package see ⑧ Packaging Code

First packaging: Each multi-disc material is packed into a box.

The second packaging: the first packaged packaging box is loaded into the paper packaging box, and the remaining space in the box is filled with light auxiliary materials.

The above packaging forms can also be packaged according to user needs.

4.1.2 Carrier Tape size




Fig. 7-1 0402 (Paper tape/ 2 mm pitch)




Fig. 7-2 0201 (Paper tape/ 2 mm pitch)




Fig. 7-3 0201 (Paper tape/ 1 mm pitch)

Table 2-1: Carrier size (Size Code: 0402 max)

(Unit:mm)

Size Code	Thickness code	Carrier Tape Type	Packaging Code	A	B	F	P1	E	D0	P2	K	W	P0	t
0201	A	Paper	T	0.38 ± 0.03	0.68 ± 0.03	3.50 ± 0.05	2.00 ± 0.05	1.75 ± 0.10	1.55 ± 0.05	2.00 ± 0.05	0.36 ± 0.02	8.00 ± 0.10	4.00 ± 0.10	0.5 max
0201	A	Paper	J	0.38 ± 0.03	0.68 ± 0.03	3.50 ± 0.05	2.00 ± 0.05	1.75 ± 0.10	1.55 ± 0.05	2.00 ± 0.05	0.36 ± 0.02	8.00 ± 0.10	4.00 ± 0.10	0.5 max
0201	A	Paper	D	0.38 ± 0.03	0.68 ± 0.03	3.50 ± 0.05	1.00 ± 0.05	1.75 ± 0.10	1.55 ± 0.05	1.00 ± 0.05	0.36 ± 0.02	8.00 ± 0.10	4.00 ± 0.10	0.5 max
0201	A	Paper	L	0.38 ± 0.03	0.68 ± 0.03	3.50 ± 0.05	1.00 ± 0.05	1.75 ± 0.10	1.55 ± 0.05	1.00 ± 0.05	0.36 ± 0.02	8.00 ± 0.10	4.00 ± 0.10	0.5 max
0402	B	Paper	T	0.63 ± 0.05	1.13 ± 0.05	3.50 ± 0.05	2.00 ± 0.05	1.75 ± 0.10	1.55 ± 0.05	2.00 ± 0.05	/	8.00 ± 0.10	4.00 ± 0.10	0.8 max
0402	B	Paper	J	0.63 ± 0.05	1.13 ± 0.05	3.50 ± 0.05	2.00 ± 0.05	1.75 ± 0.10	1.55 ± 0.05	2.00 ± 0.05	/	8.00 ± 0.10	4.00 ± 0.10	0.8 max




Fig. 7-4 0603 (Paper tape)




Fig. 7-5 0603 (Plastic tape)

Table 2-2: Carrier size (Size Code:0603 min)

(Unit:mm)

Size Code	Thickness code	Carrier Tape Type	Packaging Code	A	B	F	P	E	D0	P2	K	W	P0	t
0603	U	Paper	T	1.00 ± 0.10	1.80 ± 0.10	3.50 ± 0.05	4.00 ± 0.10	1.75 ± 0.10	1.55 ± 0.05	2.00 ± 0.05	/	8.00 ± 0.20	4.00 ± 0.10	0.95 max
0805	E	Paper	T	1.45 ± 0.20	2.20 ± 0.20	3.50 ± 0.05	4.00 ± 0.10	1.75 ± 0.10	1.55 ± 0.05	2.00 ± 0.05	/	8.00 ± 0.20	4.00 ± 0.10	1.15 max

4.1.3 Disc size




Fig. 8 Disc (Width of carrier-8 mm)

Table 3: Disc size

(Unit:mm)

Disc size	Width of carrier	A	B	C	D	E	F	F1	Size Code
7"	8.00 ± 0.10	$\Phi 178 \pm 2.0$	$\Phi 13 \pm 1.0$	$\Phi 4.0 \pm 0.5$	$\Phi 60 \pm 2.0$	4.0 ± 1.0	11.5 ± 1.0	10.0 ± 2.0	All
13"	8.00 ± 0.10	$\Phi 330 \pm 2.0$	$\Phi 13 \pm 1.0$	$\Phi 4.0 \pm 0.5$	$\Phi 108 \pm 2.0$	4.0 ± 1.0	13.5 ± 2.0	10.0 ± 2.0	All

4.1.4 Carrier Tape specifications




Fig. 9 Carrier

Packaging	The minimum length of the reserved spaces		
Carrier	Trailer	Empty	Unseal
	60 mm	200 mm	160 mm

4.1.5 Performance of Carrier Taping

4.1.5.1 Strength of Carrier Tape and Top Cover Tape

a. Carrier Tape

When a tensile force 1.02 kgf is applied in the direction to unreel the tape, the tape shall withstand this force.

b. Top cover Tape

When a tensile force 1.02 kgf is applied to the tape, the tape shall withstand this force.

4.1.5.2 Peeling Strength of Top Cover Tape

Unless otherwise specified, the peeling strength of top cover tape shall be within 10.2 gf to 71.4 gf when the top cover tape is pulled at a speed of 300 mm/min with the angle of 0° to 15° (see Fig.10).




Fig.10 Cover tape peel-off force

2. Shipment

Transport packaging products to adapt to the modern means of transport, but the product in the process of transport to prevent rain and acid and alkali corrosion, shall not be whipped extrusion casting and gravity.

3. Storage

1. Storage conditions:

The recommended temperature is less than 30 °C.

A temperature is 5 °C to 40 °C and a relative humidity is 20% to 70% as a standard condition.(MSL Level 1)

MLCC may be affected by the storage conditions. Please use them promptly after delivery.

High temperature and humidity conditions and/or prolonged storage may cause deterioration of the packaging materials.

If more than one year has elapsed since delivery, also check the solderability before use.

2. Corrosive gas can react with the termination (external) electrodes or lead wires of capacitors, and result in poor solderability.

Do not store the capacitors in an atmosphere consisting of corrosive gas (e.g.,hydrogen sulfide, sulfur dioxide, chlorine, ammonia gas etc.)

5. MLCC Application of Technical Requirements

5.1 Circuit Design

5.1.1 Operating Temperature

- Do not use capacitor above the maximum allowable operating temperature.
- Surface temperature including self-heating should be below maximum operating temperature.

5.1.2 Operating Voltage

The operating voltage for capacitors must always be lower than their rated voltage.


5.2 PCB Design

5.2.1 Design of Land-patterns

When the capacitors are mounted on a PCB, the amount of solder at the terminations has a direct effect on the performance of the capacitors.

The greater the amount of solder, the higher the stress on the capacitor. Therefore, when designing land-patterns, it is necessary to consider the appropriate size and configuration of the solder pads.

Size and recommended land dimensions are shown in the following figure and table.




Recommended land dimensions for reflow-soldering

(unit: mm)

Size Code	Length	Width	Tolerance	A	B	C
0201	0.6	0.3	± 0.03	0.20-0.25	0.20-0.30	0.20-0.35
0201	0.6	0.3	± 0.05	0.20-0.25	0.25-0.35	0.30-0.40
0201	0.6	0.3	$\pm 0.09, \pm 0.1$	0.23-0.30	0.25-0.35	0.30-0.40
0402	1.0	0.5	± 0.05	0.30-0.50	0.35-0.45	0.40-0.60
0402	1.0	0.5	$\pm 0.15, \pm 0.20$	0.40-0.60	0.40-0.50	0.50-0.70
0402	1.0	0.5	± 0.30	0.40-0.60	0.40-0.50	0.50-0.80
0603	1.6	0.8	± 0.10	0.60-0.80	0.60-0.70	0.60-0.80
0603	1.6	0.8	± 0.20	0.70-0.90	0.70-0.80	0.80-1.00
0603	1.6	0.8	$\pm 0.25, \pm 0.30$	0.70-0.90	0.70-0.90	0.80-1.10
0805	2.0	1.25	$\pm 0.10, \pm 0.15, \pm 0.20$	1.00-1.40	0.60-0.80	1.20-1.40
0805	2.0	1.25	± 0.25	1.00-1.40	0.70-0.90	1.35-1.55

5.2.2 Capacitor Layout on PC Board

Mechanical stress varies according to the location of capacitors on PC board. The recommendation for better design is as follows




The stress in capacitors is in the following order: $A > B = C > D > E$


Pay attention not to bend or distort the PC board otherwise the capacitor may crack.

Please refer to the following examples of good and bad capacitors layout.

a. Not recommended




b. Recommended




5.2.3 Solder Buildup and Soldering

a. Examples of soldering method not recommended



b. Examples of soldering method recommended







5.3 Consideration for Automatic Placement

If the mounting head is adjusted too low, it may induce excessive stress in the chip capacitor to result in cracking. Please take following precautions

- a.Adjust the bottom dead center of the mounting head to reach on the PC board surface and not press it ;
- b.Adjust the mounting head pressure to be 1N to 3N of static weight ;
- c.To minimize the impact energy from mounting head, it is important to provide support from the bottom side of the PC board.

Please refer to the following samples


Mounting	Not recommended	Recommended
Singel-sided Mounting	 Cracks	 Support pin
Double-sided Mounting	 Solder peeling Cracks	 Support pin

5.4 Soldering

5.4.1 Flux Selection

- a.It is recommended to use a mildly activated rosin flux (less than 0.1wt% chlorine). Strong flux is not recommended.
- b.Please provide proper amount of flux. Excessive flux must be avoided.
- c.When water-soluble flux is used, enough washing is necessary.

5.4.2 Recommended Soldering Profile




5.4.2.1 Reflow Soldering Condition

NO.	Reflow Soldering zone	Reflow Soldering Condition
①	Preheating 1	$\leq 3\text{ }^{\circ}\text{C/s}$, $\geq 60\text{ s}$
②	Constant temperature	$150^{\circ}\text{C} - 200^{\circ}\text{C}$, $60\text{ s} - 120\text{ s}$, $\leq 1\text{ }^{\circ}\text{C/s}$
③	Preheating 1	$1 - 5\text{ }^{\circ}\text{C/s}$
④	Soldering 1	Above $217\text{ }^{\circ}\text{C}$, $60 - 150\text{ s}$
⑤	Soldering 1	Above $260\text{ }^{\circ}\text{C}$, over 10 s
⑥	Natural cooling	$\leq 6\text{ }^{\circ}\text{C/s}$

Caution

a.Excessive solder will induce higher tensile force in chip capacitor when temperature changes and result in cracking. Insufficient solder may detach the capacitor from the PC board.

The ideal condition is to have solder mass controlled to 1/2 to 1/3 of the thickness of the capacitors.



b.Soldering duration should be kept as close to recommended times as possible, because excessive duration can detrimentally affect solderability.

c.The peak temperature of reflow soldering is $245\text{ }^{\circ}\text{C} \pm 15\text{ }^{\circ}\text{C}$.

6. All products in this specification comply with the EU RoHS directive


The EU RoHS Directive refers to the "Directive 2011/65/EU on the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment" stipulated by the European Union.

ORIGINAL MFG PART No.: **P0805C0G8R2C251NTE**

PRODUCT NAME:	High-Q, High-Power MLCC P Series SMD 0805 C0G 8.2pF ± 0.25 pF 250V
REVISION:	A3
NEXTGEN ORDER PART CODE*:	P0805N8R2C251E
CROSS REF. PART NO.:	
ORIGINAL MFG PART NO.:	P0805C0G8R2C251NTE
ORIGINAL MANUFACTURER:	EYang Technology/Eyang MLCC

*Image shown is a representation only.
Exact specifications should be obtained
from the product dimension*

*: Please Indicate this Part Code For RFQ/Order Support

**AUTHORIZED DISTRIBUTOR**

NextGen Components, Inc.

US Warehouse Location: 9 Orchard Road, Suit 106, Lake Forest, CA 92630, USA

RFQ/Order Support: sales@NextGenComponent.com

Note: This page was created by NextGen Components, Inc. ("NextGen"). The attached last document was created by the part manufacturer, not NextGen, and is provided strictly 'as is.' NextGen, its subsidiaries, affiliates, employees, and agents make no representations or warranties regarding the attached last document and disclaim any liability for the consequences of relying on the information therein. All referenced brands, product names, service names, and trademarks are the property of their respective owners.

HOW TO ORDER

Please Follow Up Part Code Guide And Indicate NextGen Part Code P0805N8R2C251E For RFQ and new Order.**RFQ**[Request For Quotation](#)

CODE	NAME	KEY SPECIFICATION OPTION
P	Series Code	P: High-Q, High-Power Multilayer Ceramic Chip Capacitors
0805	Case Size	0105 : L0.40*W0.20mm; 0201 : L0.60*W0.30mm; 0402 : L1.00*W0.50mm; 0603 : L1.60*W0.80mm 0805 : L2.00*W1.25mm; 1206 : L3.20*W1.60mm; 1210 : L3.20*W2.50mm
N	Temperature Characteristics	N: NP0 (COG); B: X7R; G: X8G; W: X5R; S: X6S; Y: Y5V; T: X7S; R: X7T
8R2	Capacitance	Two significant digits followed by number of Zero, The 3rd digit signifies the multiplying factor, and letter R is decimal point. 8R2: 8.2pF; 101: 100pF; 102: 1nF; 150: 15pF; 180: 18pF; 475: 4.7μF
C	Capacitance Tolerance	A: ±0.05pF; B: ±0.1pF; C: ±0.25pF; D: ±0.5pF; F: ±1%; G: ±2%; J: ±5%; K: ±10% L: ±15%; M: ±20%; N: ±30%; P: ±0.02pF; X: ±40%; S: 50%/-20%; Y: 150%/-20% Z: 80%/-20%
251	Rated Voltage	Two significant digits followed by No. of zeros. "R" is in place of decimal point. 6R3: 6.3 VDC; 160: 16 VDC; 250: 25 VDC; 100: 10 VDC; 500: 50 VDC; 101: 100 VDC; 201: 200 VDC; 251: 250 VDC
E	Case Thickness	E: 1.15mm Max, See Page 7 (T's Symbol) for Different part code
XX	Internal Control Code	Blank: N/A; XX: Letter A~Z, a~z or digits (0~9) for Special/Custom Parameters

IMPORTANT NOTES AND DISCLAIMER

1. **ROHS COMPLIANCE:** The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU RoHS Directive (EU) 2015/863 EC (RoHS3). RoHS Test Report for this product can be obtained can be obtained at Download Center.
2. **REACH COMPLIANCE:** REACH substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, REACH Test Report for this product can be obtained can be obtained at Download Center.
3. All Product parametric performance is indicated in the Electrical Characteristics for the listed herein test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.
4. NextGen Component, Inc (*NextGen*) reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.
5. *NextGen* makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, not does *NextGen* assume any liability for application assistance or customer product design.
6. *NextGen* does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application. No license is granted by implication or otherwise under any intellectual property rights of NextGen.
7. *NextGen* products are not authorized for use as critical components in life support devices or systems without express written approval by *NextGen*.
8. *NextGen* requires that customers first obtain an RMA (Returned Merchandise Authorization) number prior to returning any products. Returns must be made within 30 days of the date of invoice, be in the original packaging, unused and like-new condition. At the time of quoting or purchasing, a product may say that it is Non-Cancelable/ Non-Returnable (NCNR). These products are not returnable and not refundable.