


Mechanical Specifications

D	29.0 ±2.0mm
T	5.0 ±1.0mm
Lead Diameter	1.0 ±0.1mm
S	9.5 ±1.0mm
L	38.0 ±9.0 mm
B	7.8 ±1.0mm
C	3.50 ±1.0mm



Electrical Specifications

Resistance @ 25°C	5.0Ω ± 20%
Max Steady State Current Up to 65°C	20.0 A
Max recommended energy rating (Joules)	200.0 J
Max Capacitance @ 120 VAC	13,893μF
Max Capacitance @ 240 VAC	3,473μF
Resistance @ 100% of Max Current	0.034 Ω
Resistance @ 50% of Max Current	0.082 Ω
Body Temperature @ 100% Current rating	206°C
Dissipation Constant	45.4mW/°C
Thermal Time Constant	194 seconds
Material Type	“H”

Rev.	Date:	Change
1	4/15/18	Issue

Ametherm, Inc
961 Fairview Drive
Carson City, NV 89701
Telephone: **800-808-2434**
Fax: 775 884-0670
www.Ametherm.com

Reliability Delivered On Time