








ISS.	AMEND	DATE
1	ISSUED	29/08/25




SUPPLIED WITH 4x DUST COVERS (NOT SHOWN)

ITEM	MATERIAL	FINISH
MMC BODY	PEI UL94-V0	GREEN
DUST CAPS	PC UL94-V0	GREY
INNER FRAME	PC/ABS UL94-V0	BLACK
FT FRAME	ZINC DIECAST	NICKEL

PART NO.	HOLE DETAILS
CP30244M	HOLE Ø3.50 X CSK 82° X Ø5.85
CP30244M3	M3 THREAD



SPECIFICATION
Operating Temp: -30°C to 80°C



RoHS COMPLIANT
TOLERANCE NO DEC. PLACE ± 1 DEC. PLACE ± 2 DEC. PLACE ± HOLE Ø ± ANGLES ± UNLESS OTHERWISE STATED
DO NOT SCALE

Cliff Electronic Components Ltd.
76 Holmethorpe Avenue, Holmethorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

3rd ANGLE PROJECTION:

MATERIAL: SEE TABLE

FINISH: SEE TABLE

DRAWN: T.J.O.

APPROVED: D.P.J.

TITLE: FT METAL MMC (2 PORT) USCONEC

DRWG. No. CP30244M

FORM: A4DRWGH

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED
TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2025