

Industrial Ethernet IE-SW-VL08MT-6TX-2SC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Product image



The Value Line from Weidmüller consists of unmanaged and managed switches in a high-quality IP 30 protected metal housing. The equipment can be delivered with Fast Ethernet and Gigabit Ethernet ports. Value Line managed switches support a variety of helpful management functions, such as fast ring redundancy, port-based VLAN, QoS, RMON, bandwidth management, port mirroring and error notification via e-mail or a relay. The ring redundancy can be simply set via the web based management interface, or with a dip switch found on the top of the switch.

- Unmanaged Plug & Play switches in a high-quality metal housing (IP 30)
- Price-conscious middle-range
- Managed switches for the entry into a configurable network infrastructure
- Unmanaged full Gigabit switch with 8 ports
- Approvals: CE, FCC, cULus, Class I Div. 2 / ATEX, DNV / GL

General ordering data

Type	IE-SW-VL08MT-6TX-2SC
Order No.	1344770000
Version	Network switch, managed, Fast Ethernet, Number of ports: 6x RJ45, 2 * SC Multi-mode, IP30, -40 °C...75 °C
GTIN (EAN)	4050118147001
Qty.	1 pc(s).

**Industrial Ethernet
IE-SW-VL08MT-6TX-2SC**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Width	53.6 mm	Width (inches)	2.11 inch
Height	135 mm	Height (inches)	5.315 inch
Depth	105 mm	Depth (inches)	4.134 inch
Net weight	890 g		

EMC conformity and approvals

EMC standards	EN 55032, EN 55024, CISPR 32, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 1 GHz: 20 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 1 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 2 kV, IEC 61000-4-6 CS: 10 V, IEC 61000-4-8	Explosive risk zone	UL/cUL, Class I, Division 2, Groups A, B, C and D, ATEX Zone 2 Ex nA nC IIC T4 Gc
Free fall	according to IEC 60068-2-32	Security	UL508, UL60950-1, CSA C22.2 No. 60950-1, EN60950-1
Shock	according to IEC 60068-2-27	Vibration	according to IEC 60068-2-6

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	75 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Fibre optic 100BaseFX

Link budget multimode	12 dB	Max. TX multi-mode	-10 dBm
Min. TX multi-mode	-20 dBm	Receive sensitivity multi-mode	-32 dBm
System reserve multi-mode	-6 dBm	Typical distances multi-mode	5 km (50/125 µm multi-mode cable), 4 km (62.5/125 µm multi-mode cable)
Wavelength multi-mode	1,300 nm		

Guarantee

Time interval	5 years
---------------	---------

**Industrial Ethernet
IE-SW-VL08MT-6TX-2SC**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Interfaces**

Alarm contact	1 relay output with a current capacity of 1 A at 24 V DC	Console port interface	RS-232
DIP switch	Turbo-Ring, Master, Coupler, Reserve	LED indicator	PWR1, PWR2, FAULT, MSTR/HEAD, CPLR/TAIL, 10/100M (TP-Port), 100M (fibre-optic port).
Number of ports	6x RJ45, 2 * SC Multi-mode	RJ45 ports	10/100BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port

MTBF

MTBF	1,102,845 hrs	MTBF	Telcordia (Bellcore), GB
------	---------------	------	--------------------------

Power supply

Connection type	1 removable 6-pin terminal block	Current consumption	0.35 A bei 24 V
Overload current protection	Existing	Reverse polarity protection	Available
Supply voltage	24 V DC, 2 redundant inputs	Supply voltage, max	45 V DC
Supply voltage, min.	12 V DC		

Switch characteristics

IGMP-Groups	256	MAC table size	8 K
Max. number of available VLANs	64	Packet buffer size	1 Mbit
Priority queues	4	VLAN-ID max	4,094
VLAN-ID min	1		

Technical data

Housing main material	metal	Protection degree	IP30
Type of mounting	Mounting rail		

Technology

Flow control	IEEE 802.3x flow control, Back pressure flow control	MIB	MIB-II, Ethernet-Like MIB, P-BRIDGE MIB, Bridge MIB, RSTP MIB, RMON MIB Group 1, 2, 3, 9
Protocol	IGMPv1/v2, GMRP, GVRP, SNMPv1/v2c/v3, DHCP Server/Client, TFTP, SNTP, SMTP, RARP, RMON, HTTP, Telnet, Syslog, DHCP option 66/67/82, BootP, LLDP, PROFINET, EtherNet/IP, Modbus/TCP, IPv6	Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X) und 100BaseFX, IEEE 802.3x for flow control, IEEE 802.1D-2004 for the Spanning Tree protocol, IEEE 802.1w for Rapid STP, IEEE 802.1p for Class of Service, IEEE 802.1Q for VLAN tagging

**Industrial Ethernet
IE-SW-VL08MT-6TX-2SC**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Classifications**

ETIM 5.0	EC000734	ETIM 6.0	EC000734
eClass 6.2	19-17-01-06	eClass 7.1	19-17-01-06
eClass 8.1	19-17-01-06	eClass 9.0	19-17-01-06
eClass 9.1	19-17-01-06		

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	ODVA Certificate DE_PN4800_160418_004.pdf
Brochure/Catalogue	CAT 9 IETH 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Product Change Notification	Release Notes Product Change Notification IE-SW-VL08MT-series
Software	SNMP MIB file GSDML IE-SW-VL08M-series EDS IE-SW-VL08M-series Managed Switch Configuration Utility Version 3.5.2
User Documentation	Hardware Installation Guide Manual