





PERCAGE PANNEAU
MOUNTING HOLE



	MM		INCH	
	maxi	mini	maxi	mini
A	6.5	6.4	0.256	0.25
B	6.14	6	0.242	0.236

CABLES :

CHARACTERISTICS

NOMINAL IMPEDANCE	50 Ω
FREQUENCY RANGE	NA GHz
TEMPERATURE RATING	-65/+165 °C
VSWR	NA + 0 x F(GHz)Maxi
RF INSERTION LOSS	NA $\sqrt{F}$ (GHz) dB Maxi
VOLTAGE RATING	335 Vrms Max
DIELECTRIC WITHSTANDING VOLTAGE	1000 Vrms min
INSULATION RESISTANCE	5000 M Ω min
HERMETIC SEAL	- cc/s NA Atm.cm3/s
LEAKAGE (pressurized only)	- psi NA MPa
WEIGHT	0 Oz - g

STANDARDISATION

CABLE RETENTION

CENTER CONTACT RETENTION

Axial force - mating end	6.06 ₂₇	lb min N
Axial force - opposite end	6.06 ₂₇	lb min N
Torque (Min)	3.96 _{2.8}	Inch.oz cm.N

RECOMMENDED TORQUES

Mating	0 _{NA}	Inch.lb cm.N
Panel nut	13.27 ₁₅₀	Inch.lb cm.N
Clamp nut	0 _{NA}	Inch.lb cm.N

CONSTRUCTION

CONNECTOR PARTS	MATERIALS	FINISH
BODY	STAINLESS STEEL	PASSIVATED
OUTER CONTACT	STAINLESS STEEL	PASSIVATED
CENTER CONTACT	BERYLLIUM COPPER	GOLD OVER NICKEL
INSULATOR	PTFE	-
-	-	-
-	-	-
-	-	-
-	-	-
-	-	-

ISSUE	REVISION No	DESCRIPTION	BY	DATE
-	-	-	-	-
9519	12-05-95	Change rear of c. contact	TRIGUES	12-05-95
9504	94.12.018	Epoxy resin version -> Indent version	BERTHET	25-01-95

Initiated on 01/09/88

The information given here is subject to change without notice. Design changes may be in order to improve the product.



Approval by leleu

GUILLOMIN