

SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Insulator(housing): Thermoplastic (UL94V-0)
- Item ② Spring clamp: Stainless steel
- Item ③ Terminal Body(contact pin): Brass.
- Item ④ Insulator(Cover): Thermoplastic (UL94V-0)

Electrical: cULus



- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus

H3 xx 1 0 x 0 xxxx G

No. OF POLES
02: 2 POLES
:
16: 16 POLES

COLOR
0: BLACK
5: GREEN
6: BLUE
8: GREY

G: Pb<40000ppm
0000: Standard
Any special item by
customer request.
please contact sales
department.



PCB Layout

POLE		2	3	4	5	6	7	8
A		14.00	21.50	29.00	36.50	44.00	51.50	59.00
B		7.50	15.00	22.50	30.00	37.50	45.00	52.50
Tol.	±0.15				±0.20			
POLE	9	10	11	12	13	14	15	16
A	66.50	74.00	81.50	89.00	96.50	104.50	111.50	119.00
B	60.00	67.50	75.00	82.50	90.00	97.50	105.00	112.50
Tol.	±0.25				±0.30			

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	H3 7.5mm Series						
PART NO.	H3xx10x0xxxxG			DWG NO.	8H30002		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Tony 2008.05.29	Tony 2008.05.29				
					UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
					SHEET: 01/01	X.XX ±0.10	
					REV.: B	X° ±1°	