FAIRCHILD

SEMICONDUCTOR

CD4503BC Hex Non-Inverting 3-STATE Buffer

General Description

The CD4503BC is a hex non-inverting 3-STATE buffer with high output current sink and source capability. 3-STATE outputs make it useful in bus-oriented applications. Two separate disable inputs are provided. Buffers 1 through 4 are controlled by the disable 4 input. Buffers 5 and 6 are controlled by the disable 2 input. A high level on either disable input will cause those gates on its control line to go into a high impedance state.

October 1987 Revised January 2004

CD4503BC Hex Non-Inverting 3-STATE Buffer


Ordering Code:

| Order Number | Package Number | Package Description | |
|--------------|----------------|--|---|
| CD4503BCM | M16A | 16-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-012, 0.150" Narrow | 1 |
| CD4503BCN | N16E | 16-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide | |

Features

■ 3-STATE outputs

Connection Diagram



 \blacksquare Wide supply voltage range: 3.0 V_{DC} to 18 V_{DC}

■ Pin-for-pin replacement for MM80C97 and MC14503

Symmetrical turn on/turn off delays

Schematic Diagram

Symmetrical output rise and fall times

Truth Table

| | In | Disable Input | Out |
|-------------|-----|------------------|---------|
| | 0 | 0 | 0 |
| | 1 | 0 | 1 |
| | Х | 1 | 3-STATE |
| X = Don't C | are | | |

© 2004 Fairchild Semiconductor Corporation DS005989

CD4503BC

Absolute Maximum Ratings(Note 1) (Note 2)

| () | |
|---|-----------------------------------|
| Supply Voltage (V _{DD}) | -0.5V to +18V |
| Input Voltage (V _{IN}) | -0.5V to +0.5V |
| Storage Temperature Range (T _S) | $-65^{\circ}C$ to $+150^{\circ}C$ |
| Power Dissipation (P _D) | |
| Dual-In-Line | 700 mW |
| Small Outline | 500 mW |
| Lead Temperature (TL) | |
| (Soldering, 10 seconds) | 260°C |
| | |

Recommended Operating Conditions (Note 2)

Supply Voltage (V_{DD}) Operating Temperature Range (T_A) +3V to +15V $-55^\circ C$ to $+125^\circ C$

Note 1: "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. They are not meant to imply that the devices should be operated at these limits. The tables of "Recommended Operating Conditions" and "Electrical Characteristics" provide conditions for actual device operation.

Note 2: $V_{SS} = 0V$ unless otherwise specified.

DC Electrical Characteristics (Note 2)

| Symbol | Parameter | Conditions | -55 | _55°C | | +25°C | | | +125°C | |
|-----------------|-------------------------|--|-------|-------|-------|-------------------|------|-------|--------|-------|
| Symbol | Faialletei | Conditions | Min | Max | | Тур | Max | Min | Max | Units |
| I _{DD} | Quiescent Device | $V_{DD} = 5V,$ | | 1 | | | 1 | | 30 | |
| | Current | $V_{IN} = V_{DD} \text{ or } V_{SS}$ | | | | | | | | |
| | | $V_{DD} = 10V,$ | | 2 | | | 2 | | 60 | μA |
| | | $V_{IN} = V_{DD} \text{ or } V_{SS}$ | | | | | | | | μΑ |
| | | V _{DD} = 15V, | | 4 | | | 4 | | 120 | |
| | | $V_{IN} = V_{DD} \text{ or } V_{SS}$ | | | | | | | | |
| V _{OL} | LOW Level | $V_{IN} = V_{DD}$ or 0 | | | | | | | | |
| | Output Voltage | $V_{DD} = 5V$ | | 0.05 | | 0 | 0.05 | | 0.05 | |
| | | $V_{DD} = 10V$ | | 0.05 | | 0 | 0.05 | | 0.05 | V |
| | | $V_{DD} = 15V$ | | 0.05 | | 0 | 0.05 | | 0.05 | |
| V _{OH} | HIGH Level | $V_{IN} = V_{DD} \text{ or } 0$ | | | | | | | | |
| | Output Voltage | $V_{DD} = 5V$ | 4.95 | | 4.95 | 5 | | 4.95 | | |
| | | $V_{DD} = 10V$ | 9.95 | | 9.95 | 10 | | 9.95 | | V |
| | | $V_{DD} = 15V$ | 14.95 | | 14.95 | 15 | | 14.95 | | |
| VIL | LOW Level | $V_{DD} = 5V,$ | | 1.5 | | 2.25 | 1.5 | | 1.5 | |
| | Input Voltage | $V_{O} = 4.5V \text{ or } 0.5V$ | | | | | | | | |
| | | $V_{DD} = 10V,$ | | 3.0 | | 4.50 | 3.0 | | 3.0 | v |
| | | $V_0 = 9.0V \text{ or } 1.0V$ | | | | | | | | v |
| | | V _{DD} = 15V, | | 4.0 | | 6.75 | 4.0 | | 4.0 | |
| | | V _O = 13.5V or 1.5V | | | | | | | | |
| VIH | HIGH Level | $V_{DD} = 5V,$ | 3.5 | | 3.5 | 2.75 | | 3.5 | | |
| | Input Voltage | $V_{O} = 0.5V \text{ or } 4.5V$ | | | | | | | | |
| | | $V_{DD} = 10V,$ | 7.0 | | 7.0 | 5.5 | | 7.0 | | v |
| | | $V_0 = 1.0V \text{ or } 9.0V$ | | | | | | | | v |
| | | V _{DD} = 15V, | 11.0 | | 11.0 | 8.25 | | 11.0 | | |
| | | V _O = 1.5V or 13.5V | | | | | | | | |
| I _{OL} | LOW Level Output | $V_{DD} = 4.5V, V_{OL} = 0.4V$ | 2.8 | | 2.3 | 2.55 | | 1.60 | | |
| | Current | $V_{DD} = 5.0V, V_{OL} = 0.4V$ | 3.0 | | 2.4 | 2.75 | | 1.75 | | mA |
| | | $V_{DD} = 10V, V_{OL} = 0.5V$ | 7.85 | | 6.35 | 7.00 | | 4.45 | | mA |
| | | $V_{DD} = 15V, V_{OL} = 1.5V$ | 19.95 | | 16.10 | 25.00 | | 11.30 | | |
| I _{OH} | HIGH Level Output | $V_{DD} = 5V, V_{OH} = 4.6V$ | -1.28 | | -1.02 | -1.76 | | -0.7 | | |
| | Current | $V_{DD} = 10V, V_{OH} = 9.5V$ | -3.20 | | -2.60 | -4.5 | | -1.8 | | mA |
| | | V _{DD} = 15V, V _{OH} = 13.5V | -8.20 | | -6.80 | -17.6 | | -4.8 | | |
| I _{OZ} | 3-STATE Leakage Current | V _{DD} = 15V | | ±0.1 | 1 | ±10 ⁻⁴ | ±0.1 | 1 | ±1.0 | μA |
| IIN | Input Current | V _{DD} = 15V | | ±0.1 | İ 👘 | ±10 ⁻⁴ | ±0.1 | İ 👘 | ±1.0 | μA |

Note 3: $I_{\mbox{OH}}$ and $I_{\mbox{OL}}$ are tested one output at a time.

| AC Electrical | Characteristics | (Note 4) |
|---------------|-----------------|----------|
|---------------|-----------------|----------|

| $T_A = 25^{\circ}C$, $C_L = 50$ pF, $R_L = 200$ k Ω , Input $t_r = t_f = 20$ ns, unless otherwise specified | | | | | | |
|---|-------------------------|----------------|-----|-----|-----|-------|
| Symbol | Parameter | Conditions | Min | Тур | Max | Units |
| t _{PHL} , t _{PLH} | Propagation Delay Time | $V_{DD} = 5V$ | | 75 | 100 | |
| | | $V_{DD} = 10V$ | | 35 | 40 | ns |
| | | $V_{DD} = 15V$ | | 25 | 30 | |
| t _{PLZ} , t _{PHZ} | Propagation Delay Time, | $V_{DD} = 5V$ | | 80 | 125 | |
| | Logical Level to HIGH | $V_{DD} = 10V$ | | 40 | 90 | ns |
| | Impedance State | $V_{DD} = 15V$ | | 35 | 70 | |
| t _{PZL} , t _{PZH} | Propagation Delay Time, | $V_{DD} = 5V$ | | 95 | 175 | |
| | High Impedance State to | $V_{DD} = 10V$ | | 40 | 80 | ns |
| | Logical Level | $V_{DD} = 15V$ | | 35 | 70 | |
| t _{TLH} | Output Rise Time | $V_{DD} = 5V$ | | 45 | 80 | |
| | | $V_{DD} = 10V$ | | 23 | 40 | ns |
| | | $V_{DD} = 15V$ | | 18 | 35 | |
| t _{THL} | Output Fall Time | $V_{DD} = 5V$ | | 45 | 80 | |
| | | $V_{DD} = 10V$ | | 23 | 40 | ns |
| | | $V_{DD} = 15V$ | | 18 | 35 | |

Note 4: AC Parameters are guaranteed by DC correlated testing.

