


## Continental Dynamics 10" Direct Drive Exhaust Fan, 1 Speed, 1500 CFM, 1/30 HP

Part Number: 246506



The guard mount exhaust fan is designed for low-pressure exhausting and cooling applications. Steel spiral wire guards enclose 3 aluminum fan blades for safety. Wire guards feature built-in mounting holes for easy installation. The 120V, single phase totally enclosed motor is permanently lubricated for long life. It is UL, cUL listed and conforms to UL507 standard.

### Specification:

Manufacturers Part Number	246506
Brand	Continental Dynamics
Certifications	UL, cUL listed, OSHA, UL507
Mounting Location	Guard or Wall
RPM	1500 rpm
CFM	1500 CFM
Amperage	0.38 A
Max Temperature	104° F °F
Decibels	59
CFM High	1500 CFM
Power Cord Type	Hard Wire
Cord Length	Not Included ft
Drive Type	Direct Drive
Length	11-1/2 in

Number of Speeds	1
Wattage	45 W
Voltage	120 V
Indoor/Outdoor	Indoor
Width	11-1/2 in
Horsepower	1/30 HP
Fan Diameter	10 in
Motor Type	Totally Enclosed
MPN	246506
UNSPSC	40101502