

RUK Series

Features


- 125°C, 3,000 ~ 5,000 hours assured
- For automobile modules and other high temperature applications
- RoHS compliant



Specifications

Items	Performance																																		
Category Temperature Range	-40°C ~ +125°C																																		
Capacitance Tolerance	± 20% (at 120 Hz, 20°C)																																		
Leakage Current (at 20°C)	I = 0.01CV or 3 (μA) whichever is greater (after 2 minutes) Where, C = rated capacitance in μF, V = rated DC working voltage in V																																		
Tanδ (at 120 Hz, 20°C)	<table><tr><td>Rated Voltage</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td></tr><tr><td>Tanδ (max.)</td><td>0.15</td><td>0.12</td><td>0.10</td><td>0.10</td><td>0.08</td><td>0.08</td></tr></table>							Rated Voltage	10	16	25	35	50	63	Tanδ (max.)	0.15	0.12	0.10	0.10	0.08	0.08														
Rated Voltage	10	16	25	35	50	63																													
Tanδ (max.)	0.15	0.12	0.10	0.10	0.08	0.08																													
Low Temperature Characteristics (at 120 Hz)	Impedance ratio shall not exceed the values given in the table below. <table><tr><td>Rated Voltage</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td></tr><tr><td rowspan="2">Impedance Ratio</td><td>Z(-25°C) / Z(+20°C)</td><td>3</td><td>2</td><td>2</td><td>2</td><td>2</td></tr><tr><td>Z(-40°C) / Z(+20°C)</td><td>6</td><td>4</td><td>4</td><td>4</td><td>4</td></tr></table>							Rated Voltage	10	16	25	35	50	63	Impedance Ratio	Z(-25°C) / Z(+20°C)	3	2	2	2	2	Z(-40°C) / Z(+20°C)	6	4	4	4	4								
Rated Voltage	10	16	25	35	50	63																													
Impedance Ratio	Z(-25°C) / Z(+20°C)	3	2	2	2	2																													
	Z(-40°C) / Z(+20°C)	6	4	4	4	4																													
Endurance	<table><tr><td>Test Time</td><td colspan="6">3,000 Hrs for ϕ D = 8mm; 5,000 Hrs for ϕ D ≥ 10mm</td></tr><tr><td>Capacitance Change</td><td colspan="6">Within ± 20% of initial value</td></tr><tr><td>Tanδ</td><td colspan="6">Less than 200% of specified value</td></tr><tr><td>Leakage Current</td><td colspan="6">Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20°C after applied with rated subjected to DC voltage with the rated ripple current is applied for 3,000 / 5,000 hours at 125°C.							Test Time	3,000 Hrs for ϕ D = 8mm; 5,000 Hrs for ϕ D ≥ 10mm						Capacitance Change	Within ± 20% of initial value						Tanδ	Less than 200% of specified value						Leakage Current	Within specified value					
Test Time	3,000 Hrs for ϕ D = 8mm; 5,000 Hrs for ϕ D ≥ 10mm																																		
Capacitance Change	Within ± 20% of initial value																																		
Tanδ	Less than 200% of specified value																																		
Leakage Current	Within specified value																																		
Shelf Life Test	<table><tr><td>Test Time</td><td colspan="6">1,000 Hrs</td></tr><tr><td>Capacitance Change</td><td colspan="6">Within ± 20% of initial value</td></tr><tr><td>Tanδ</td><td colspan="6">Less than 200% of specified value</td></tr><tr><td>Leakage Current</td><td colspan="6">Less than 500% of specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 hours at 125°C without voltage applied.							Test Time	1,000 Hrs						Capacitance Change	Within ± 20% of initial value						Tanδ	Less than 200% of specified value						Leakage Current	Less than 500% of specified value					
Test Time	1,000 Hrs																																		
Capacitance Change	Within ± 20% of initial value																																		
Tanδ	Less than 200% of specified value																																		
Leakage Current	Less than 500% of specified value																																		
Ripple Current and Frequency Multipliers	<table><tr><td> Freq.(Hz) Cap.(μF) </td><td>120</td><td>1k</td><td>10k</td><td colspan="3">100k up</td></tr><tr><td>0.47 ~ 100</td><td>1.00</td><td>1.70</td><td>1.88</td><td colspan="3">2.00</td></tr><tr><td>150 ~ 470</td><td>1.00</td><td>1.45</td><td>1.58</td><td colspan="3">1.65</td></tr><tr><td>1,000</td><td>1.00</td><td>1.20</td><td>1.25</td><td colspan="3">1.33</td></tr></table>							Freq.(Hz) Cap.(μF)	120	1k	10k	100k up			0.47 ~ 100	1.00	1.70	1.88	2.00			150 ~ 470	1.00	1.45	1.58	1.65			1,000	1.00	1.20	1.25	1.33		
Freq.(Hz) Cap.(μF)	120	1k	10k	100k up																															
0.47 ~ 100	1.00	1.70	1.88	2.00																															
150 ~ 470	1.00	1.45	1.58	1.65																															
1,000	1.00	1.20	1.25	1.33																															


Diagram of Dimensions



Lead Spacing and Diameter Unit: mm

ϕ D	8	10	12.5	16
P	3.5	5.0	5.0	7.5
ϕ d	0.6			0.8
α	L<20: 1.5, L≥20: 2.0			
β	0.5			

The case size of 16×20 is suitable for below diagram:



All product specifications in the catalog are subject to change without notice. (Cat. 2025E3)

Dimension and Permissible Ripple Current

Dimension: $\phi D \times L$ (mm)
Ripple Current: mA/rms at 120 Hz, 125°C

Cap. (μF)	Contents	10V (1A)		16V (1C)		25V (1E)		35V (1V)		50V (1H)		63V (1J)	
		$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA
10	100									8×11.5	56	8×11.5	56
22	220							8×11.5	75	10×12.5	99	10×12.5	99
33	330					8×11.5	92	10×12.5	108	10×16	133	10×16	133
47	470			8×11.5	100	10×12.5	129	10×16	142	10×16	159	10×20	173
100	101	10×12.5	154	10×16	190	10×16	208	10×20	225				
220	221	10×16	252	10×20	305	12.5×20	371	12.5×25	403	12.5×20	279	12.5×20	279
330	331	10×16	308	12.5×20	414	12.5×25	493	16×20	503				
470	471	10×20	399	12.5×25	537	16×20	601			16×20	459		
1,000	102	16×20	715										

Part Numbering System

RUK Series	470μF	± 20%	16V	Bulk Package	Gas Type	12.5 ϕ × 25L	Regional Tracking Purpose
RUK	471	M	1C	BK	-	1325	S
Series Name	Capacitance	Capacitance Tolerance	Rated Voltage	Lead Configuration and Package	Rubber Type	Case Size	

Note: For more details, please refer to "Part Numbering System - Radial Type" on page 139.

All product specifications in the catalog are subject to change without notice. (Cat. 2025E3)