

VEU Series

Features

- 4φ ~ 18φ, 105°C, 3,000 ~ 5,000 hours assured
- Long life assured
- Designed for surface mounting on high density PC board
- RoHS compliant
- AEC-Q200 compliant parts available (replace "S" Suffix with "KS")



Marking color: Black

Specifications

Items	Performance																																																																									
Category	6.3 ~ 100V				160 ~ 400V				450V																																																																	
Temperature Range	-55°C ~ +105°C				-40°C ~ +105°C				-25°C ~ +105°C																																																																	
Capacitance Tolerance	± 20% (at 120 Hz, 20°C)																																																																									
Leakage Current (at 20°C)	Rated Voltage		6.3 ~ 100V				160 ~ 450V																																																																			
	Time		after 2 minutes				after 5 minutes																																																																			
	Leakage Current		I = 0.01CV or 3 (μA), whichever is greater				I = 0.04CV + 100 (μA)																																																																			
	Where, C = rated capacitance in μF, V = rated DC working voltage in V																																																																									
Tanδ (at 120 Hz, 20°C)	<table><tr><td>Rated Voltage</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td><td>80</td><td>100</td><td>160</td><td>200</td><td>250</td><td>400</td><td>450</td></tr><tr><td>Tanδ (max.)</td><td>0.30</td><td>0.24</td><td>0.20</td><td>0.16</td><td>0.13</td><td>0.12</td><td>0.09</td><td>0.08</td><td>0.07</td><td>0.15</td><td>0.15</td><td>0.15</td><td>0.20</td><td>0.20</td></tr></table>														Rated Voltage	6.3	10	16	25	35	50	63	80	100	160	200	250	400	450	Tanδ (max.)	0.30	0.24	0.20	0.16	0.13	0.12	0.09	0.08	0.07	0.15	0.15	0.15	0.20	0.20																														
Rated Voltage	6.3	10	16	25	35	50	63	80	100	160	200	250	400	450																																																												
Tanδ (max.)	0.30	0.24	0.20	0.16	0.13	0.12	0.09	0.08	0.07	0.15	0.15	0.15	0.20	0.20																																																												
Low Temperature Characteristics (at 120 Hz)	Impedance ratio shall not exceed the values given in the table below. <table><tr><td colspan="2">Rated Voltage</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td><td>80</td><td>100</td><td>160</td><td>200</td><td>250</td><td>400</td><td>450</td></tr><tr><td rowspan="2">Impedance Ratio</td><td>Z(-25°C) / Z(+20°C)</td><td>4</td><td>3</td><td>2</td><td>2</td><td>2</td><td>2</td><td>2</td><td>2</td><td>2</td><td>3</td><td>3</td><td>3</td><td>6</td><td>6</td></tr><tr><td>Z(-55/-40°C) / Z(+20°C)</td><td>10</td><td>7</td><td>5</td><td>3</td><td>3</td><td>3</td><td>3</td><td>3</td><td>3</td><td>6</td><td>6</td><td>6</td><td>10</td><td>-</td></tr></table>														Rated Voltage		6.3	10	16	25	35	50	63	80	100	160	200	250	400	450	Impedance Ratio	Z(-25°C) / Z(+20°C)	4	3	2	2	2	2	2	2	2	3	3	3	6	6	Z(-55/-40°C) / Z(+20°C)	10	7	5	3	3	3	3	3	3	6	6	6	10	-													
Rated Voltage		6.3	10	16	25	35	50	63	80	100	160	200	250	400	450																																																											
Impedance Ratio	Z(-25°C) / Z(+20°C)	4	3	2	2	2	2	2	2	2	3	3	3	6	6																																																											
	Z(-55/-40°C) / Z(+20°C)	10	7	5	3	3	3	3	3	3	6	6	6	10	-																																																											
Endurance	<table><tr><td>Test Time</td><td colspan="14">3,000 Hrs for ϕ D ≤ 10 mm; 5,000 Hrs for ϕ D ≥ 12.5 mm</td></tr><tr><td>Capacitance Change</td><td colspan="14">Within ± 30% of initial value</td></tr><tr><td>Tanδ</td><td colspan="14">Less than 300% of specified value</td></tr><tr><td>Leakage Current</td><td colspan="14">Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage applied for 3,000 ~ 5,000 hours at 105°C.														Test Time	3,000 Hrs for ϕ D ≤ 10 mm; 5,000 Hrs for ϕ D ≥ 12.5 mm														Capacitance Change	Within ± 30% of initial value														Tanδ	Less than 300% of specified value														Leakage Current	Within specified value													
Test Time	3,000 Hrs for ϕ D ≤ 10 mm; 5,000 Hrs for ϕ D ≥ 12.5 mm																																																																									
Capacitance Change	Within ± 30% of initial value																																																																									
Tanδ	Less than 300% of specified value																																																																									
Leakage Current	Within specified value																																																																									
Shelf Life Test	<table><tr><td>Test Time</td><td colspan="14">1,000 Hrs</td></tr><tr><td>Capacitance Change</td><td colspan="14">Within ± 30% of initial value</td></tr><tr><td>Tanδ</td><td colspan="14">Less than 300% of specified value</td></tr><tr><td>Leakage Current</td><td colspan="14">Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 hours at 105°C without voltage applied.														Test Time	1,000 Hrs														Capacitance Change	Within ± 30% of initial value														Tanδ	Less than 300% of specified value														Leakage Current	Within specified value													
Test Time	1,000 Hrs																																																																									
Capacitance Change	Within ± 30% of initial value																																																																									
Tanδ	Less than 300% of specified value																																																																									
Leakage Current	Within specified value																																																																									
Ripple Current and Frequency Multipliers	<table><tr><td colspan="2">Frequency (Hz)</td><td>50</td><td>120</td><td>1k</td><td>10k up</td></tr><tr><td rowspan="2">Cap.(μF)</td><td>≤ 1,000</td><td>0.70</td><td>1.00</td><td>1.30</td><td>1.40</td></tr><tr><td>1,000 < C ≤ 1,500</td><td>0.85</td><td>1.00</td><td>1.13</td><td>1.15</td></tr></table>														Frequency (Hz)		50	120	1k	10k up	Cap.(μF)	≤ 1,000	0.70	1.00	1.30	1.40	1,000 < C ≤ 1,500	0.85	1.00	1.13	1.15																																											
Frequency (Hz)		50	120	1k	10k up																																																																					
Cap.(μF)	≤ 1,000	0.70	1.00	1.30	1.40																																																																					
	1,000 < C ≤ 1,500	0.85	1.00	1.13	1.15																																																																					

Diagram of Dimensions

Fig. 1





Fig. 2



Lead Spacing and Diameter

Unit: mm


φD	L	A	B	C	W	P	Fig. No.
4	5.7 ± 0.3	4.3	4.3	5.1	0.5 ~ 0.8	1.0	1
5	5.7 ± 0.3	5.3	5.3	5.9	0.5 ~ 0.8	1.5	1
6.3	5.7 ± 0.3	6.6	6.6	7.2	0.5 ~ 0.8	2.0	1
6.3	7.7 ± 0.3	6.6	6.6	7.2	0.5 ~ 0.8	2.0	1
8	10 ± 0.5	8.3	8.3	9.0	0.7 ~ 1.1	3.1	1
10	10 ± 0.5	10.3	10.3	11.0	0.7 ~ 1.1	4.7	1
12.5	13.5 ± 0.5	13.0	13.0	13.7	1.1 ~ 1.4	4.4	2
12.5	16 ± 0.5	13.0	13.0	13.7	1.1 ~ 1.4	4.4	2
16	16.5 ± 0.5	17.0	17.0	18.0	1.1 ~ 1.4	6.4	2
16	21.5 ± 0.5	17.0	17.0	18.0	1.1 ~ 1.4	6.4	2
18	16.5 ± 0.5	19.0	19.0	20.0	1.1 ~ 1.4	6.4	2
18	21.5 ± 0.5	19.0	19.0	20.0	1.1 ~ 1.4	6.4	2

The diagram is marking " () " for reference dimension.


All product specifications in the catalog are subject to change without notice. (Cat. 2025E3)

Marking


$\phi D \leq 6.3 \text{ mm}$



$\phi D = 8 \sim 10 \text{ mm}$



$\phi D \geq 12.5 \text{ mm}$



Dimension and Permissible Ripple Current

Dimension: $\phi D \times L(\text{mm})$

Ripple Current: mA/rms at 120 Hz, 105°C

Rated Volt. (Voc)		6.3V (0J)		10V (1A)		16V (1C)		25V (1E)		35V (1V)		50V (1H)		63V (1J)		80V (1K)	
Cap. (μF)	Contents	φ D×L	mA	φ D×L	mA	φ D×L	mA	φ D×L	mA	φ D×L	mA	φ D×L	mA	φ D×L	mA	φ D×L	mA
1	010											4×5.7	8				
2.2	2R2											4×5.7	12				
3.3	3R3											4×5.7	17				
4.7	4R7									4×5.7	16	5×5.7	22				
10	100					4×5.7	18	5×5.7	27	5×5.7	27	6.3×5.7	32				
22	220	4×5.7	22	4×5.7	22	5×5.7	30	6.3×5.7	44	6.3×5.7	44	6.3×7.7	58				
33	330	5×5.7	35	5×5.7	35	6.3×5.7	48	6.3×5.7	50	6.3×7.7	57	8×10	130				
47	470	5×5.7	38	6.3×5.7	50	6.3×5.7	50	6.3×7.7	63	8×10	92	8×10	141				
100	101	6.3×5.7	69	6.3×7.7	81	6.3×7.7	81	8×10	116	10×10	151	10×10	160			12.5×13.5	220
150	151													12.5×13.5	240	12.5×16	290
220	221	6.3×7.7	120	8×10	141	8×10	141	10×10	290	10×10	320	12.5×13.5	280	12.5×16	320	16×16.5	410
330	331	8×10	141	10×10	290	10×10	290	10×10	320	12.5×13.5	320	12.5×16	360	16×16.5	450	16×16.5	510
470	471	10×10	320	10×10	320	10×10	320			12.5×16	410	16×16.5	510	16×16.5	540	18×16.5	650
1,000	102	10×10	410							16×16.5	690	18×16.5	780				
1,500	152									18×16.5	900						

Rated Volt. (Voc)		100V (2A)		160V (2C)		200V (2D)		250V (2E)		400V (2G)		450V (2W)	
Cap. (μF)	Contents	φ D×L	mA	φ D×L	mA	φ D×L	mA	φ D×L	mA	φ D×L	mA	φ D×L	mA
3.3	3R3											12.5×13.5	40
4.7	4R7							12.5×13.5	65	12.5×16	50	12.5×16	50
10	100					12.5×13.5	80	12.5×16	105	16×16.5	85	16×16.5	85
22	220					12.5×16	105	16×16.5	180	18×21.5	130	18×21.5	130
33	330			12.5×13.5	95	16×16.5	220	18×16.5	230				
47	470			16×16.5	260	18×16.5	270	18×21.5	280				
68	680	12.5×13.5	180	18×16.5	320	18×21.5	330						
100	101	12.5×16	240	16×21.5	380								
150	151	16×16.5	340										
220	221	16×16.5	410										
330	331	18×16.5	540										

Part Numbering System

VEU Series	470μF	± 20%	6.3V	Carrier Tape	10 ϕ × 10L	Regional Tracking Purpose
VEU	471	M	0J	TR	-	1010
Series Name	Capacitance	Capacitance Tolerance	Rated Voltage	Package Type	Terminal Type	Case Size
						S

Note: For more details, please refer to "Part Numbering System - SMD Type" on page 106.

All product specifications in the catalog are subject to change without notice. (Cat. 2025E3)