

VUK Series

Features

- 8φ ~ 18φ, 125°C, 3,000 ~ 5,000 hours assured
- Chip type high temperature range, for +125°C use
- For automobile modules and other high temperature applications
- RoHS compliant
- AEC-Q200 compliant parts available (replace "S" Suffix with "KS")



Marking color: Black

Specifications

Items	Performance																												
Category Temperature Range	-40°C ~ +125°C																												
Capacitance Tolerance	± 20% (at 120 Hz, 20°C)																												
Leakage Current (at 20°C)	I = 0.03CV or 4 (μA) whichever is greater (after 1 minutes) Where, C = rated capacitance in μF, V = rated DC working voltage in V																												
Tanδ (at 120 Hz, 20°C)	<table><tr><td>Rated Voltage</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td></tr><tr><td>Tanδ (max.)</td><td>0.22</td><td>0.18</td><td>0.16</td><td>0.14</td><td>0.12</td><td>0.12</td></tr></table> When the capacitance exceeds 1,000μF, 0.02 shall be added every 1,000μF increase.						Rated Voltage	10	16	25	35	50	63	Tanδ (max.)	0.22	0.18	0.16	0.14	0.12	0.12									
Rated Voltage	10	16	25	35	50	63																							
Tanδ (max.)	0.22	0.18	0.16	0.14	0.12	0.12																							
Low Temperature Characteristics (at 120 Hz)	Impedance ratio shall not exceed the values given in the table below. <table><tr><td colspan="2">Rated Voltage</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td></tr><tr><td rowspan="2">Impedance Ratio</td><td>Z(-25°C) / Z(+20°C)</td><td>6</td><td>5</td><td>4</td><td>3</td><td>3</td><td>3</td></tr><tr><td>Z(-40°C) / Z(+20°C)</td><td>12</td><td>8</td><td>6</td><td>4</td><td>4</td><td>4</td></tr></table>						Rated Voltage		10	16	25	35	50	63	Impedance Ratio	Z(-25°C) / Z(+20°C)	6	5	4	3	3	3	Z(-40°C) / Z(+20°C)	12	8	6	4	4	4
Rated Voltage		10	16	25	35	50	63																						
Impedance Ratio	Z(-25°C) / Z(+20°C)	6	5	4	3	3	3																						
	Z(-40°C) / Z(+20°C)	12	8	6	4	4	4																						
Endurance	<table><tr><td>Test Time</td><td>3,000 Hrs for ϕ D ≤ 10 mm; 5,000 Hrs for ϕ D ≥ 12.5 mm</td></tr><tr><td>Capacitance Change</td><td>Within ± 30% of initial value</td></tr><tr><td>Tanδ</td><td>Less than 300% of specified value</td></tr><tr><td>Leakage Current</td><td>Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage applied for 3,000 / 5,000 hours at 125°C.						Test Time	3,000 Hrs for ϕ D ≤ 10 mm; 5,000 Hrs for ϕ D ≥ 12.5 mm	Capacitance Change	Within ± 30% of initial value	Tanδ	Less than 300% of specified value	Leakage Current	Within specified value															
Test Time	3,000 Hrs for ϕ D ≤ 10 mm; 5,000 Hrs for ϕ D ≥ 12.5 mm																												
Capacitance Change	Within ± 30% of initial value																												
Tanδ	Less than 300% of specified value																												
Leakage Current	Within specified value																												
Shelf Life Test	<table><tr><td>Test Time</td><td>1,000 Hrs</td></tr><tr><td>Capacitance Change</td><td>Within ± 30% of initial value</td></tr><tr><td>Tanδ</td><td>Less than 300% of specified value</td></tr><tr><td>Leakage Current</td><td>Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 hours at 125°C without voltage applied.						Test Time	1,000 Hrs	Capacitance Change	Within ± 30% of initial value	Tanδ	Less than 300% of specified value	Leakage Current	Within specified value															
Test Time	1,000 Hrs																												
Capacitance Change	Within ± 30% of initial value																												
Tanδ	Less than 300% of specified value																												
Leakage Current	Within specified value																												
Ripple Current and Frequency Multipliers	<table><tr><td rowspan="3">Cap.(μF) ≤ 330 330 < C ≤ 3,300</td><td>Freq.(Hz)</td><td>50</td><td>120</td><td>1k</td><td>10k up</td></tr><tr><td></td><td>0.80</td><td>1.0</td><td>1.25</td><td>1.40</td></tr><tr><td></td><td>0.85</td><td>1.0</td><td>1.20</td><td>1.30</td></tr></table>						Cap.(μF) ≤ 330 330 < C ≤ 3,300	Freq.(Hz)	50	120	1k	10k up		0.80	1.0	1.25	1.40		0.85	1.0	1.20	1.30							
Cap.(μF) ≤ 330 330 < C ≤ 3,300	Freq.(Hz)	50	120	1k	10k up																								
		0.80	1.0	1.25	1.40																								
		0.85	1.0	1.20	1.30																								

Diagram of Dimensions

Fig. 1





Fig. 2



Lead Spacing and Diameter

Unit: mm


φD	L	A	B	C	W	P	Fig. No.
8	10 ± 0.5	8.3	8.3	9.0	0.7 ~ 1.1	3.1	1
10	10 ± 0.5	10.3	10.3	11.0	0.7 ~ 1.1	4.7	1
12.5	13.5 ± 0.5	13.0	13.0	13.7	1.1 ~ 1.4	4.4	2
12.5	16 ± 0.5	13.0	13.0	13.7	1.1 ~ 1.4	4.4	2
16	16.5 ± 0.5	17.0	17.0	18.0	1.1 ~ 1.4	6.4	2
18	16.5 ± 0.5	19.0	19.0	20.0	1.1 ~ 1.4	6.4	2
18	21.5 ± 0.5	19.0	19.0	20.0	1.1 ~ 1.4	6.4	2

The diagram is marking " () " for reference dimension.


All product specifications in the catalog are subject to change without notice. (Cat. 2025E3)

Marking

$\phi D = 8 \sim 10 \text{ mm}$



$\phi D \geq 12.5 \text{ mm}$



Dimension and Permissible Ripple Current

Dimension: $\phi D \times L(\text{mm})$

Ripple Current: mA/rms at 120 Hz, 125°C

Cap. (μF)	Contents	10V (1A)		16V (1C)		25V (1E)		35V (1V)		50V (1H)		63V (1J)	
		$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA
100	101			8×10	85	8×10	85	10×10	110	12.5×13.5	170	12.5×13.5	150
220	221	8×10	85	10×10	150	10×10	150	12.5×13.5	200	16×16.5	250	16×16.5	230
330	331	10×10	150	12.5×13.5	230	12.5×13.5	230	16×16.5	280	18×16.5	340	18×16.5	320
470	471	12.5×13.5	230	12.5×13.5	250	16×16.5	310	18×16.5	380	18×21.5	430	18×21.5	410
680	681	12.5×13.5	250	12.5×13.5	280	16×16.5	350	18×16.5	450				
1,000	102	12.5×16	350	16×16.5	440	18×21.5	540						
1,500	152	12.5×16	350	16×16.5	460								
2,200	222	18×16.5	620	18×21.5	710								
3,300	332	18×21.5	770										

Part Numbering System

VUK Series	330μF	± 20%	16V	Carrier Tape	12.5 ϕ × 13.5L	Regional Tracking Purpose
VUK	331	M	1C	TR	-	1313
Series Name	Capacitance	Capacitance Tolerance	Rated Voltage	Package Type	Terminal Type	Case Size
						S

Note: For more details, please refer to "Part Numbering System - SMD Type" on page 106.

All product specifications in the catalog are subject to change without notice. (Cat. 2025E3)