

VZR Series

Features

- 5φ ~ 18φ, 105°C, 7,000 ~ 8,000 hours assured
- Low Impedance temperature range up to +105°C
- For automobile modules and high temperature applications
- RoHS compliant
- AEC-Q200 compliant parts available (replace "S" Suffix with "KS")



Marking color: Black

Specifications

Items	Performance														
Category Temperature Range	-25°C ~ +105°C														
Capacitance Tolerance	± 20% (at 120 Hz, 20°C)														
Leakage Current (at 20°C)	I = 0.01CV or 3 (μA) whichever is greater (after 2 minutes) Where, C = rated capacitance in μF, V = rated DC working voltage in V														
Tanδ (at 120 Hz, 20°C)	<table><tr><td>Rated Voltage</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr><tr><td>Tanδ (max.)</td><td>0.32</td><td>0.28</td><td>0.26</td><td>0.16</td><td>0.14</td><td>0.14</td></tr></table> When the capacitance exceeds 1,000 μ F, 0.02 shall be added every 1,000 μ F increase.	Rated Voltage	6.3	10	16	25	35	50	Tanδ (max.)	0.32	0.28	0.26	0.16	0.14	0.14
Rated Voltage	6.3	10	16	25	35	50									
Tanδ (max.)	0.32	0.28	0.26	0.16	0.14	0.14									
Low Temperature Characteristics (at 120 Hz)	Impedance ratio shall not exceed the values given in the table below. <table><tr><td>Rated Voltage</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr><tr><td>Impedance Ratio</td><td>Z(-25°C) / Z(+20°C)</td><td>4</td><td>3</td><td>2</td><td>2</td><td>2</td></tr></table>	Rated Voltage	6.3	10	16	25	35	50	Impedance Ratio	Z(-25°C) / Z(+20°C)	4	3	2	2	2
Rated Voltage	6.3	10	16	25	35	50									
Impedance Ratio	Z(-25°C) / Z(+20°C)	4	3	2	2	2									
Endurance	<table><tr><td>Test Time</td><td>7,000 Hrs for ϕ D ≤ 10 mm; 8,000 Hrs for ϕ D ≥ 12.5 mm</td></tr><tr><td>Capacitance Change</td><td>Within ± 30% of initial value</td></tr><tr><td>Tanδ</td><td>Less than 300% of specified value</td></tr><tr><td>Leakage Current</td><td>Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage applied for 7,000 ~ 8,000 hours at 105°C.	Test Time	7,000 Hrs for ϕ D ≤ 10 mm; 8,000 Hrs for ϕ D ≥ 12.5 mm	Capacitance Change	Within ± 30% of initial value	Tanδ	Less than 300% of specified value	Leakage Current	Within specified value						
Test Time	7,000 Hrs for ϕ D ≤ 10 mm; 8,000 Hrs for ϕ D ≥ 12.5 mm														
Capacitance Change	Within ± 30% of initial value														
Tanδ	Less than 300% of specified value														
Leakage Current	Within specified value														
Shelf Life Test	<table><tr><td>Test Time</td><td>1,000 Hrs</td></tr><tr><td>Capacitance Change</td><td>Within ± 30% of initial value</td></tr><tr><td>Tanδ</td><td>Less than 300% of specified value</td></tr><tr><td>Leakage Current</td><td>Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 hours at 105°C without voltage applied.	Test Time	1,000 Hrs	Capacitance Change	Within ± 30% of initial value	Tanδ	Less than 300% of specified value	Leakage Current	Within specified value						
Test Time	1,000 Hrs														
Capacitance Change	Within ± 30% of initial value														
Tanδ	Less than 300% of specified value														
Leakage Current	Within specified value														
Ripple Current and Frequency Multipliers	<table><tr><td>Frequency (Hz)</td><td>50</td><td>120</td><td>1k</td><td>10k up</td></tr><tr><td>Multiplier</td><td>0.35</td><td>0.50</td><td>0.83</td><td>1.0</td></tr></table>	Frequency (Hz)	50	120	1k	10k up	Multiplier	0.35	0.50	0.83	1.0				
Frequency (Hz)	50	120	1k	10k up											
Multiplier	0.35	0.50	0.83	1.0											

Diagram of Dimensions

Fig. 1





Fig. 2



Lead Spacing and Diameter

Unit: mm


φ D	L	A	B	C	W	P	Fig. No.
5	7 ± 0.3	5.3	5.3	5.9	0.5 ~ 0.8	1.5	1
6.3	7 ± 0.3	6.6	6.6	7.2	0.5 ~ 0.8	2.0	1
6.3	8.7 ± 0.5	6.6	6.6	7.2	0.5 ~ 0.8	2.0	1
8	10 ± 0.5	8.3	8.3	9.0	0.7 ~ 1.1	3.1	1
10	10 ± 0.5	10.3	10.3	11.0	0.7 ~ 1.1	4.7	1
12.5	13.5 ± 0.5	13.0	13.0	13.7	1.1 ~ 1.4	4.4	2
12.5	16 ± 0.5	13.0	13.0	13.7	1.1 ~ 1.4	4.4	2
16	16.5 ± 0.5	17.0	17.0	18.0	1.1 ~ 1.4	6.4	2
16	21.5 ± 0.5	17.0	17.0	18.0	1.1 ~ 1.4	6.4	2
18	16.5 ± 0.5	19.0	19.0	20.0	1.1 ~ 1.4	6.4	2
18	21.5 ± 0.5	19.0	19.0	20.0	1.1 ~ 1.4	6.4	2

The diagram is marking " () " for reference dimension.


All product specifications in the catalog are subject to change without notice. (Cat. 2025E3)

Marking


$\phi D \leq 6.3 \text{ mm}$



$\phi D = 8 \sim 10 \text{ mm}$



$\phi D \geq 12.5 \text{ mm}$



Dimension: $\phi D \times L(\text{mm})$

Ripple Current: mA/rms at 100k Hz, 105°C

Impedance: Ω / at 100k Hz, 20°C

Dimension and Permissible Ripple Current

Rated Volt. (Vdc)		6.3V (0J)				10V (1A)				16V (1C)				25V (1E)				35V (1V)				50V (1H)			
Cap. (μF)	Contents	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA
10	100																5×7	2.2	95						
22	220							5×7	2.2	95	5×7	2.2	95	5×7	2.2	95	5×7	2.2	95						
33	330				5×7	2.2	95				6.3×7	1.1	140	6.3×7	1.1	140	6.3×8.7	1.0	230						
47	470	5×7	2.2	95				6.3×7	1.1	140	6.3×7	1.1	140	6.3×7	1.1	140	6.3×8.7	1.0	230	8×10	0.53	350			
100	101	6.3×7	1.1	140				6.3×7	1.1	140	6.3×8.7	1.0	230							8×10	0.53	350			
150	151				6.3×7	1.1	140	6.3×8.7	1.0	230															
220	221	6.3×8.7	1.0	230				6.3×8.7	1.0	230	8×10	0.22	600	8×10	0.22	600	8×10	0.22	600	10×10	0.35	670			
330	331	6.3×8.7	1.0	230				8×10	0.22	600	8×10	0.22	600	8×10	0.22	600	10×10	0.16	850	12.5×13.5	0.18	850			
390	391																			12.5×16	0.15	950			
470	471	8×10	0.22	600				8×10	0.22	600	10×10	0.16	850				12.5×13.5	0.092	950	16×16.5	0.12	1,200			
680	681				10×10	0.16	850										12.5×16	0.074	1,200						
820	821	10×10	0.16	850																18×16.5	0.12	1,300			
1,000	102													12.5×13.5	0.092	950	16×16.5	0.066	1,450	16×21.5	0.08	1,600			
1,200	122													12.5×16	0.074	1,200									
1,500	152							12.5×13.5	0.092	950	16×16.5	0.066	1,450	16×16.5	0.066	1,450	18×16.5	0.064	1,550	18×21.5	0.072	1,650			
1,800	182				12.5×13.5	0.092	950	12.5×16	0.074	1,200	16×16.5	0.066	1,450	18×16.5	0.064	1,550	16×21.5	0.041	2,000						
2,200	222	12.5×13.5	0.092	950	12.5×16	0.074	1,200	16×16.5	0.066	1,450	18×16.5	0.064	1,550	18×16.5	0.064	1,550	16×21.5	0.041	2,000						
2,700	272	12.5×16	0.074	1,200										16×21.5	0.041	2,000	18×21.5	0.039	2,150						
3,300	332				16×16.5	0.066	1,450	18×16.5	0.064	1,550	18×21.5	0.039	2,150												
3,900	392	16×16.5	0.066	1,450																					
4,700	472				18×16.5	0.064	1,550	16×21.5	0.041	2,000															
5,600	562	18×16.5	0.064	1,550	16×21.5	0.041	2,000	18×21.5	0.039	2,150															
6,800	682	16×21.5	0.041	2,000	18×21.5	0.039	2,150																		
8,200	822	18×21.5	0.039	2,150																					

Part Numbering System

VZR Series 470 μF

$\pm 20\%$

6.3V

Carrier Tape

8 ϕ × 10L

Regional Tracking Purpose

VZR

471

M

0J

TR

-

0810

S

Series Name

Capacitance

Capacitance Tolerance

Rated Voltage

Package Type

Terminal Type

Case Size

Note: For more details, please refer to "Part Numbering System - SMD Type" on page 106.