

DATA SHEET

WIRELESS COMPONENTS

PCB type antenna
ANTX150P118B09153
890~925MHz



FEATURES & BENEFITS

- The smallest PCB antenna in the market
- Miniature design allows users to save required space
- Double-side adhesive tape makes it easy to install in device
- Ranges of types of connector and cable provide a flexible design options
- Halogen free and RoHS compliant

APPLICATIONS

- Tablet / Desktop PC
- Internet TV / STB / Game console / Camera
- WiFi network devices (IEEE 802.11b/g/n)
- Bluetooth / ZigBee devices
- Car Infotainment
- Smart meter
- Lighting control
- POS terminal
- Wireless Industrial Control

ORDERING INFORMATION-GLOBAL PART NUMBER, PHYCOMP CTC & 12NC

All part numbers are identified by the series, packing type, material, size, antenna type, working frequency and packing quantity.

YAGEO BRAND ordering code**GLOBAL PART NUMBER (PREFERRED)****ANT X150 P 118 B 0915 3****(1) (2) (3) (4) (5) (6) (7)****(1) FAMILY**

ANT = Antenna products

(2) CONNECTOR & CABLE LENGTH (MM)

X = I-PEX

150 = 150mm

(3) ANTENNA TYPE

P=PCB

(4) SERIAL NUMBER

118 = SERIAL NUMBER 118

(5) PACKAGE TYPE

B = Bulk

(6) WORKING FREQUENCY

915 = 890~925MHz

(7) CABLE TYPE

3 = 1.13mm diameter Mini-Coaxial Cable

SPECIFICATIONS

Table 1


DESCRIPTION	VALUE
Working Frequency	890~925MHz
VSWR	2.5:1 max
Peak Gain	1.9dBi
Polarization	Linear
Radiation Pattern	Omni-directional
Impedance	50 Ω Nominal
Operating Temperature	-40 °C to 85 °C
Maximum Power	1 W
Dimension	34mm x 7mm x 0.95mm
Radio Connector	I-PEX (20278-112R-13)
Cable Diameter / Length / Color	1.13mm / 150mm / Black
Mounting	Adhesive Tape (HF-DS)

DIMENSIONS

Table 2 Mechanical


DIMENSION	VALUE
L (mm)	150+-3.00
W (mm)	34+-0.30
H (mm)	7+-0.30
T (mm)	0.95+-0.15
A (mm)	2.30 Max

OUTLINES



RETURN LOSS & VSWR

Return Loss (dB)



VSWR




Fig. 2 Return loss & VSWR Measurement


ANTENNA GAIN & EFFICIENCY

Table 3

FREQUENCY (GHz)	AVERAGE GAIN (dBi)	EFFICIENCY (%)	PEAK GAIN (dBi)
890	-3.1	49.1	1.6
894	-2.8	52.1	1.7
900	-2.5	56.7	1.9
915	-2.6	55.0	1.5
925	-3.2	48.3	0.6

ANTENNA RADIATION PATTERNS

Scale: 5 dBi / div Max : 5 dBi Min : -20 dBi



REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 0	Jan. 15, 2018	-	- New data sheet for PCB type antenna, 890~925MHz application