

VZS Series

Features

- 5φ ~ 10φ, 105°C, 2,000 hours assured
- Low impedance 30 ~ 50% less than VZH series
- Large capacitance with ultra low impedance capacitors
- Designed for surface mounting on high density PC board
- RoHS compliant
- AEC-Q200 compliant parts available (replace "S" Suffix with "KS")




Marking color: Black

Specifications

Items	Performance																													
Category Temperature Range	-55°C ~ +105°C																													
Capacitance Tolerance	± 20% (at 120 Hz, 20°C)																													
Leakage Current (at 20°C)	I = 0.01CV or 3 (μA) whichever is greater (after 2 minutes) Where, C = rated capacitance in μF, V = rated DC working voltage in V																													
Tanδ (at 120 Hz, 20°C)	<table><tr><td>Rated Voltage</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr><tr><td>Tanδ (max.)</td><td>0.30</td><td>0.26</td><td>0.22</td><td>0.16</td><td>0.13</td><td>0.10</td></tr></table> When the capacitance exceeds 1,000μF, 0.02 shall be added every 1,000μF increase.							Rated Voltage	6.3	10	16	25	35	50	Tanδ (max.)	0.30	0.26	0.22	0.16	0.13	0.10									
Rated Voltage	6.3	10	16	25	35	50																								
Tanδ (max.)	0.30	0.26	0.22	0.16	0.13	0.10																								
Low Temperature Characteristics (at 120 Hz)	Impedance ratio shall not exceed the values given in the table below. <table><tr><td colspan="2">Rated Voltage</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr><tr><td rowspan="2">Impedance Ratio</td><td>Z(-25°C) / Z(+20°C)</td><td>4</td><td>3</td><td>2</td><td>2</td><td>2</td><td>2</td></tr><tr><td>Z(-55°C) / Z(+20°C)</td><td>8</td><td>5</td><td>4</td><td>3</td><td>3</td><td>3</td></tr></table>							Rated Voltage		6.3	10	16	25	35	50	Impedance Ratio	Z(-25°C) / Z(+20°C)	4	3	2	2	2	2	Z(-55°C) / Z(+20°C)	8	5	4	3	3	3
Rated Voltage		6.3	10	16	25	35	50																							
Impedance Ratio	Z(-25°C) / Z(+20°C)	4	3	2	2	2	2																							
	Z(-55°C) / Z(+20°C)	8	5	4	3	3	3																							
Endurance	<table><tr><td>Test Time</td><td>2,000 Hrs</td></tr><tr><td>Capacitance Change</td><td>Within ± 30% of initial value</td></tr><tr><td>Tanδ</td><td>Less than 300% of specified value</td></tr><tr><td>Leakage Current</td><td>Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage applied for 2,000 hours at 105°C.							Test Time	2,000 Hrs	Capacitance Change	Within ± 30% of initial value	Tanδ	Less than 300% of specified value	Leakage Current	Within specified value															
Test Time	2,000 Hrs																													
Capacitance Change	Within ± 30% of initial value																													
Tanδ	Less than 300% of specified value																													
Leakage Current	Within specified value																													
Shelf Life Test	Test time: 1,000 hours; other items are the same as those for the Endurance.																													
Ripple Current and Frequency Multipliers	<table><tr><td>Frequency (Hz)</td><td>50, 60</td><td>120</td><td>1k</td><td>10k up</td></tr><tr><td>Multiplier</td><td>0.60</td><td>0.70</td><td>0.85</td><td>1.0</td></tr></table>							Frequency (Hz)	50, 60	120	1k	10k up	Multiplier	0.60	0.70	0.85	1.0													
Frequency (Hz)	50, 60	120	1k	10k up																										
Multiplier	0.60	0.70	0.85	1.0																										

Diagram of Dimensions



Lead Spacing and Diameter


Unit: mm

φ D	L	A	B	C	W	P
5	5.8 ± 0.3	5.3	5.3	5.9	0.5 ~ 0.8	1.5
6.3	5.8 ± 0.3	6.6	6.6	7.2	0.5 ~ 0.8	2.0
6.3	7.7 ± 0.3	6.6	6.6	7.2	0.5 ~ 0.8	2.0
8	6.5 ± 0.3	8.3	8.3	9.0	0.5 ~ 0.8	2.3
8	10 ± 0.5	8.3	8.3	9.0	0.7 ~ 1.1	3.1
10	10 ± 0.5	10.3	10.3	11	0.7 ~ 1.1	4.7
10	12.5 ± 0.5	10.3	10.3	11	0.7 ~ 1.1	4.7


The diagram is marking " () " for reference dimension.

Marking

φ D ≤ 6.3 mm



φ D = 8 ~ 10 mm



Dimension: $\phi D \times L$ (mm)
Ripple Current: mA/rms at 100k Hz, 105°C
Impedance: Ω / at 100k Hz, 20°C

Dimension and Permissible Ripple Current

Rated Volt. (Vdc)		6.3V (0J)			10V (1A)			16V (1C)			25V (1E)			35V (1V)			50V (1H)		
Cap. (μF)	Contents	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA
22	220							5×5.8	0.36	240	5×5.8	0.36	240	5×5.8	0.36	240			
33	330				5×5.8	0.36	240				5×5.8 6.3×5.8	0.36 0.26	240 300	6.3×5.8	0.26	300			
47	470	5×5.8	0.36	240				5×5.8 6.3×5.8	0.36 0.26	240 300	6.3×5.8	0.26	300	6.3×5.8	0.26	300			
68	680							6.3×5.8	0.26	300	6.3×5.8	0.26	300	6.3×7.7	0.16	600			
100	101	5×5.8 6.3×5.8	0.36 0.26	240 300	5×5.8	0.36	240	6.3×5.8 6.3×7.7	0.26 0.16	300 600	6.3×5.8 6.3×7.7 8×6.5	0.26 0.16 0.18	300 600 500	8×10	0.08	850	8×10	0.18	670
150	151				6.3×5.8	0.26	300	6.3×7.7	0.16	600	8×10	0.08	850	8×10	0.08	850			
220	221	6.3×5.8	0.26	300	6.3×7.7 8×6.5	0.16 0.18	600 500	6.3×7.7 8×6.5 8×10	0.16 0.18 0.08	600 500 850	8×10	0.08	850				10×10	0.15	900
330	331	6.3×7.7 8×6.5	0.16 0.18	600 500	8×10	0.08	850	8×10	0.08	850				10×10	0.06	1,190			
470	471	8×10	0.08	850	8×10	0.08	850	8×10	0.08	850	10×10	0.06	1,190	10×12.5	0.06	1,190			
680	681	8×10	0.08	850	8×10	0.08	850	10×10	0.06	1,190	10×12.5	0.06	1,190						
1,000	102				10×10	0.06	1,190	10×12.5	0.06	1,190									
1,500	152	10×10	0.06	1,190	10×12.5	0.06	1,190												
2,200	222	10×12.5	0.06	1,190															

Part Numbering System

VZS Series	470μF	± 20%	6.3V	Carrier Tape	8 ϕ × 10L	Regional Tracking Purpose
VZS	471	M	0J	TR	-	0810
Series Name	Capacitance	Capacitance Tolerance	Rated Voltage	Package Type	Terminal Type	Case Size

Note: For more details, please refer to "Part Numbering System - SMD Type" on page 106.