





CUSTOMER DRAWING

REVISIONS			
ZONE	REV.	DESCRIPTION	DATE
	PA1	INITIAL RELEASE	2025-01-20
	PA2	NOTE UPDATE	2025-03-10



MOUNTING CUT-OUT




SPECIFICATIONS

Shell Material	Stainless Steel
Sping Material	Corrosion Resistant Stainless Steel
Sealing Material	EPDM
Working Pressure	0~0.6MPa
Safety Pressure	2.0MPa
Operating Temperature	-40~+105℃
Sealing	Dry Break Sealing, No Leakage
Applicable Fluid	Deionized Water, Glycol, Propylene Glycol
Adapted Hose Inner Dia.	/

1. STAMP LOGO & SERIES & QR CODE.

STAMP EXAMPLE:

Amphenol UQDB02



LOGO & SERIES

READING: UQDBP-02TMU01-N000-20250103-00001

CODE NUMBER


DATE IN 8 DIGIT, YYYYMMDD


SEQUENTIAL NUMBER, FROM 00001 TO 99999

NOTES

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM THE AMPHENOL CORP.

Next Assembly

UNLESS OTHERWISE SPECIFIED							APPROVALS			DATE		
LINEAR DIMENSIONS ARE IN MILLIMETERS							PREPARED BY:		Michael Zeng		2025-03-10	
TOLERANCES:							LEAD/PRODUCT ENGINEER:		Jerry Pu			
DIM. RANGE		0.5-3	>3-6	>6-30	>30-120	>120-400	ENGINEERING MANAGER:		Ran Xiao			
TOLERANCE		±0.1	±0.1	±0.2	±0.3	±0.5	PRODUCT GROUP:		C&I			
ANGLES = ±2°							AIPG DIVISION:		AIO			
DIM. & TOL. PER ASME Y14.5M-1994;							MATERIAL SPEC			PROCESS SPEC		
DRM PER MIL-DTL-31000;							N/A			N/A		
OTHER AMPHENOL STANDARDS: 9-9318												
THIRD ANGLE PROJECTION												
												



AMPHENOL CORPORATION

Amphenol Technology (Zhuhai) Co. Ltd.
No. 63 Xingnan Road, Sanzao Town, Jinwan, Zhuhai, PRC

UQDB02 PLUG TM UNF7/16"-20

SIZE	CAGE CODE	DOCUMENT NUMBER	REV
C	90MJ5	UQDBP-02TMU01-000	PA2
SCALE: 2.5:1		REF:	SHEET 1 OF 1