





CUSTOMER DRAWING

REVISIONS			
ZONE	REV.	DESCRIPTION	DATE
	PA1	INITIAL RELEASE	2025-01-20
	PA2	NOTE UPDATE	2025-03-10



MOUNTING CUT-OUT




SPECIFICATIONS

Shell Material	Stainless Steel
Sping Material	Corrosion Resistant Stainless Steel
Sealing Material	EPDM
Working Pressure	0~0.6MPa
Safety Pressure	2.0MPa
Operating Temperature	-40~+105℃
Sealing	Dry Break Sealing, No Leakage
Applicable Fluid	Deionized Water, Glycol, Propylene Glycol
Adapted Hose Inner Dia.	/

1. STAMP LOGO & SERIES & QR CODE.

STAMP EXAMPLE:

Amphenol UQDB04



LOGO & SERIES

READING: UQDBP-04TMU02-N000-20250103-00001

CODE NUMBER


DATE IN 8 DIGIT, YYYYMMDD

SEQUENTIAL NUMBER, FROM 00001 TO 99999

NOTES

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM THE AMPHENOL CORP.

Next Assembly

UNLESS OTHERWISE SPECIFIED						APPROVALS				DATE			
LINEAR DIMENSIONS ARE IN MILLIMETERS TOLERANCES:						PREPARED BY:			Michael Zeng			2025-03-10	
						LEAD/PRODUCT ENGINEER:			Jerry Pu				
DIM. RANGE 0.5-3>3-6>6-30>30-120>120-400						ENGINEERING MANAGER:			Ran Xiao				
TOLERANCE ±0.1 ±0.1 ±0.2 ±0.3 ±0.5						PRODUCT GROUP:			C&I				
ANGLES = ±2°						AIPG DIVISION:			AIO				
DIM. & TOL. PER ASME Y14.5M-1994;						MATERIAL SPEC				PROCESS SPEC			
DRM PER MIL-DTL-31000;													
OTHER AMPHENOL STANDARDS: 9-9318						N/A				N/A			
THIRD ANGLE PROJECTION													
													

AMPHENOL CORPORATION

Amphenol Technology (Zhuhai) Co. Ltd.
No. 63 Xinghan Road, Sanzao Town, Jinwan, Zhuhai, PRC

UQDB04 PLUG TM UNF9/16"-18

SIZE	CAGE CODE	DOCUMENT NUMBER	REV
C	90MJ5	UQDBP-04TMU02-000	PA2
SCALE: 2.5:1		REF:	SHEET 1 OF 1