

FIRE ALARM MULTI CONDUCTOR SHIELDED RISER

Copper conductors with premium grade PVC used for Fire alarm systems.



GENERAL INFO

Fire alarm systems have expanded from a rather simple and unsophisticated business configured upon large, electro-mechanical devices to one relying upon the most modern technologies of microprocessor and chip technology. More and more end users— industrial, commercial as well as consumer—are relying upon these emerging systems to protect both property and life. These systems are only as good as their weakest component, whether that component be a processor or interconnecting wire and cable. It is General Cable's charter that all products supplied for use in these and any other systems shall be constructed of only the finest available materials, and provide the service and assurance that the end user not only needs, but requires. Aside from the quality materials used in these designs, specifiers and end users of Carol® Brand wire and cable products have come to expect that these cables are registered and certified with the leading regulatory agencies such as Underwriters Laboratories ... and we haven't let you down! These designs have proven themselves in the area of fire system security over time; all are fabricated with solid, bare copper conductors and insulations and jackets of premium-grade PVC. Offered both with and without shields, the former to protect these critical circuits from noise, these cables will provide the latest in available technology for the system installer and contractor. General Cable Carol Brand products are conveniently packaged in 1000' or 500' lengths to assist the installer.

CONSTRUCTION/DESIGN

Nominal outer diameter [inch]	Conductor strand count	Cable marking	Conductor category	AWG size
0.281		CAROL (R) 12 AWG -- E2062S -- 75C E60233-8 (UL) CL3R OR FPLR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT)	Class 2 = stranded	12
0.245		CAROL (R) 14 AWG -- E2052S -- 75C E60233-8 (UL) CL3R OR FPLR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT) (PRINT EVERY 2 FT)	Class 2 = stranded	14
0.245		CAROL (R) 14 AWG -- E2052S -- 75C E60233-8 (UL) CL3R OR FPLR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT) (PRINT EVERY 2 FT)	Class 2 = stranded	14
		PRYSMIAN GROUP (H) (YEAR) EASY GLIDER(R) MTW OR THHN/THWN-2 (UL) 12 AWG (3.31 MM2) GR I AND GR II 600V VW-1 OR AWM OR T90 NYLON / TWN75 C(UL) FT1 (-25C)		14
0.245		CAROL (R) 14 AWG -- E2052S -- 75C E60233-8 (UL) CL3R OR FPLR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT) (PRINT EVERY 2 FT)	Class 2 = stranded	14
0.2	19/.0117	CAROL (R) 16 AWG -- E2043S -- 75C E60233-8 (UL) CL3R OR FPLR --- (UL) C(UL)CMR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT) (PRINT EVERY 2 FT)	Class 2 = stranded	16
0.22	19/.0117	CAROL (R) 16 AWG -- E2044S -- 75C E60233-8 (UL) CL3R OR FPLR --- (UL) C(UL)CMR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT)	Class 2 = stranded	16
0.19	19/.0117	NA	Class 2 = stranded	16
0.16	7/26	CAROL (R) 18 AWG -- E2032S -- 75C E60233-8 (UL) CL3R OR FPLR --- (UL) C(UL)CMR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT)	Class 2 = stranded	18
0.16	7/26	CAROL (R) 18 AWG -- E2032S -- 75C E60233-8 (UL) CL3R OR FPLR --- (UL) C(UL)CMR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT)	Class 2 =	18
0.23	Solid	NA		
0.16	7/26	CAROL (R) 18 AWG -- E2032S -- 75C E60233-8 (UL) CL3R OR FPLR --- (UL) C(UL)CMR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT)	Class 2 = stranded	18

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
E2062S.41.10	12/2C STRANDED SHIELDED CMR/CL3R	CAROL (R) 12 AWG -- E2062S -- 75C E60233-8 (UL) CL3R OR FPLR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT)	12	Black/Red	2	Gray
E2062S.38.10	12/2C STRANDED SHIELDED CMR/CL3R	CAROL (R) 12 AWG -- E2062S -- 75C E60233-8 (UL) CL3R OR FPLR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT)	12	Black/Red	2	Gray
E2052S.41.03	14/2C STRANDED SHIELDED CMR/CL3R	CAROL (R) 14 AWG -- E2052S -- 75C E60233-8 (UL) CL3R OR FPLR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT) (PRINT EVERY 2 FT)	14	Black, Red	2	Red
E2052S.25.03	14/2C STRANDED SHIELDED CMR/CL3R	CAROL (R) 14 AWG -- E2052S -- 75C E60233-8 (UL) CL3R OR FPLR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT) (PRINT EVERY 2 FT)	14	Black, Red	2	Red
E2052S.30.10M	14/2C STRANDED SHIELDED CMR/CL3R	CAROL (R) 14 AWG -- E2052S -- 75C E60233-8 (UL) CL3R OR FPLR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT) (PRINT EVERY 2 FT)	14	Black, Red	2	Gray
92979A.41.10	14/2 BC SHIELDED CL3R	PRYSMIAN GROUP (H) (YEAR) EASY GLIDER(R) MTW OR THHN/THWN-2 (UL) 12 AWG (3.31 MM2) GR I AND GR II 600V VW-1 OR AWM OR T90 NYLON / TWN75 C(UL) FT1 (-25C)	14	NA	2	Gray
E2052S.30.10	14/2C STRANDED SHIELDED CMR/CL3R	CAROL (R) 14 AWG -- E2052S -- 75C E60233-8 (UL) CL3R OR FPLR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT) (PRINT EVERY 2 FT)	14	Black, Red	2	Gray
E2052S.41.10	14/2C STRANDED SHIELDED CMR/CL3R	CAROL (R) 14 AWG -- E2052S -- 75C E60233-8 (UL) CL3R OR FPLR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT) (PRINT EVERY 2 FT)	14	Black, Red	2	Gray
E2043S.41.10	16/3C STRANDED SHIELDED CMR/CL3R	CAROL (R) 16 AWG -- E2043S -- 75C E60233-8 (UL) CL3R OR FPLR --- (UL) C(UL)CMR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT) (PRINT EVERY 2 FT)	16	Black, Red, White	2	Gray
E2044S.41.10	16/4C STRANDED SHIELDED CMR/CL3R	CAROL (R) 16 AWG -- E2044S -- 75C E60233-8 (UL) CL3R OR FPLR --- (UL) C(UL)CMR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT)	16	Black, Red, White, Green	2	Gray

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
E2042S.30.10	16/2C STRANDED SHIELDED CMR/CL3R	NA	16	Black, Red	2	Gray
E2042S.41.10	16/2C STRANDED SHIELDED CMR/CL3R	NA	16	Black, Red	2	Gray
E2042S.18.10	16/2C STRANDED SHIELDED CMR/CL3R	NA	16	Black, Red	2	Gray
E2032S.41.03	18/2C STRANDED SHIELDED CMR/CL3R	CAROL (R) 18 AWG -- E2032S -- 75C E60233-8 (UL) CL3R OR FPLR --- (UL) C(UL)CMR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT)	18	Black, Red	2	Red
E2032S.30.10M	18/2C STRANDED SHIELDED CMR/CL3R	CAROL (R) 18 AWG -- E2032S -- 75C E60233-8 (UL) CL3R OR FPLR --- (UL) C(UL)CMR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT)	18	Black, Red	2	Gray
C4334A.41.03	18/2C STRANDED BC SHIELDED FPL/CSA	NA	18	Black, Red	2	Red
E2032S.43.19	18/2C STRANDED SHIELDED CMR/CL3R	CAROL (R) 18 AWG -- E2032S -- 75C E60233-8 (UL) CL3R OR FPLR --- (UL) C(UL)CMR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT)	18	Black, Red	2	Purple
E2032S.43.07	18/2C STRANDED SHIELDED CMR/CL3R	CAROL (R) 18 AWG -- E2032S -- 75C E60233-8 (UL) CL3R OR FPLR --- (UL) C(UL)CMR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT)	18	Black, Red	2	Blue
E2032S.30.10	18/2C STRANDED SHIELDED CMR/CL3R	CAROL (R) 18 AWG -- E2032S -- 75C E60233-8 (UL) CL3R OR FPLR --- (UL) C(UL)CMR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT)	18	Black, Red	2	Gray
E2032S.41.10	18/2C STRANDED SHIELDED CMR/CL3R	CAROL (R) 18 AWG -- E2032S -- 75C E60233-8 (UL) CL3R OR FPLR --- (UL) C(UL)CMR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT)	18	Black, Red	2	Gray

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
E2032S.46.10	18/2C STRANDED SHIELDED CMR/CL3R	CAROL (R) 18 AWG -- E2032S -- 75C E60233-8 (UL) CL3R OR FPLR --- (UL) C(UL)CMR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT)	18	Black, Red	2	Gray
E2032S.18.10	18/2C STRANDED SHIELDED CMR/CL3R	CAROL (R) 18 AWG -- E2032S -- 75C E60233-8 (UL) CL3R OR FPLR --- (UL) C(UL)CMR -- ROHS -- MADE IN USA (DATE CODE) (SEQ FT)	18	Black, Red	2	Gray
E2022S.30.10	20/2C STRANDED SHIELDED CMR/CL3R	NA	20	Black, Red	2	Gray
E2022S.41.10	20/2C STRANDED SHIELDED CMR/CL3R	NA	20	Black, Red	2	Gray
E2026S.41.10	20/6C STRANDED SHIELDED CMR/CL3R		20	NA	6	Black
E2003S.41.10	22/3C STRANDED SHIELDED CMR/CL3R	NA	22	Black, Red, White	2	Gray
E2002S.30.10	22/2C STRANDED SHIELDED CMR/CL3R	NA	22	Black, Red	2	Gray
E2002S.41.10	22/2C STRANDED SHIELDED CMR/CL3R	NA	22	Black, Red	2	Gray
E2002S.18.10	22/2C STRANDED SHIELDED CMR/CL3R	NA	22	Black, Red	2	Gray
E2000S.41.10	22/2C STRANDED SHIELDED CMR/CL3R	NA	22	Black, Red	2	Gray

PRODUCT DETAILS

Part number	Product name	Cable marking	AWG size	Core colors	Number of cores	Color outer jacket
E2002S.41.04SR	22/2C STRANDED SHIELDED CMR/CL3R	NA	22	Black, Red	2	Orange

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
E2062S.41.10	12/2C STRANDED SHIELDED CMR/CL3R		0.013	0.281			0.33	7.14
E2062S.38.10	12/2C STRANDED SHIELDED CMR/CL3R		0.013	0.281			0.33	7.14
E2052S.41.03	14/2C STRANDED SHIELDED CMR/CL3R		0.013	0.245			0.33	6.21
E2052S.25.03	14/2C STRANDED SHIELDED CMR/CL3R		0.013	0.245			0.33	6.21
E2052S.30.10M	14/2C STRANDED SHIELDED CMR/CL3R		0.013	0.245			0.33	6.21
92979A.41.10	14/2 BC SHIELDED CL3R							
E2052S.30.10	14/2C STRANDED SHIELDED CMR/CL3R		0.013	0.245			0.33	6.21
E2052S.41.10	14/2C STRANDED SHIELDED CMR/CL3R		0.013	0.245			0.33	6.21
E2043S.41.10	16/3C STRANDED SHIELDED CMR/CL3R		0.009	0.2			0.23	5.03
E2044S.41.10	16/4C STRANDED SHIELDED CMR/CL3R		0.009	0.22			0.23	5.56

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
E2042S.30.10	16/2C STRANDED SHIELDED CMR/CL3R		0.009	0.19			0.23	4.8
E2042S.41.10	16/2C STRANDED SHIELDED CMR/CL3R		0.009	0.19			0.23	4.8
E2042S.18.10	16/2C STRANDED SHIELDED CMR/CL3R		0.009	0.19			0.23	4.8
E2032S.41.03	18/2C STRANDED SHIELDED CMR/CL3R		0.008	0.16			0.2	4.04
E2032S.30.10M	18/2C STRANDED SHIELDED CMR/CL3R		0.008	0.16			0.2	4.04
C4334A.41.03	18/2C STRANDED BC SHIELDED FPL/CSA		0.015	0.23			0.38	5.84
E2032S.43.19	18/2C STRANDED SHIELDED CMR/CL3R		0.008	0.16			0.2	4.04
E2032S.43.07	18/2C STRANDED SHIELDED CMR/CL3R		0.008	0.16			0.2	4.04
E2032S.30.10	18/2C STRANDED SHIELDED CMR/CL3R		0.008	0.16			0.2	4.04
E2032S.41.10	18/2C STRANDED SHIELDED CMR/CL3R		0.008	0.16			0.2	4.04

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
E2032S.46.10	18/2C STRANDED SHIELDED CMR/CL3R		0.008	0.16			0.2	4.04
E2032S.18.10	18/2C STRANDED SHIELDED CMR/CL3R		0.008	0.16			0.2	4.04
E2022S.30.10	20/2C STRANDED SHIELDED CMR/CL3R		0.007	0.15			0.18	3.61
E2022S.41.10	20/2C STRANDED SHIELDED CMR/CL3R		0.007	0.15			0.18	3.61
E2026S.41.10	20/6C STRANDED SHIELDED CMR/CL3R							
E2003S.41.10	22/3C STRANDED SHIELDED CMR/CL3R		0.008	0.14			0.2	3.43
E2002S.30.10	22/2C STRANDED SHIELDED CMR/CL3R		0.008	0.14			0.2	3.35
E2002S.41.10	22/2C STRANDED SHIELDED CMR/CL3R		0.008	0.14			0.2	3.35
E2002S.18.10	22/2C STRANDED SHIELDED CMR/CL3R		0.008	0.14			0.2	3.35
E2000S.41.10	22/2C STRANDED SHIELDED CMR/CL3R		0.008	0.12			0.2	2.97

APPLICATION PROPERTIES

Part number	Product name	Conductor resistance at operation temperature [mOhm/ft]	Nominal insulation thickness [inch]	Nominal outer diameter [inch]	Nominal operation capacitance [pF/ft]	Shield DC resistance [mOhm/ft]	Nominal insulation thickness [mm]	Nominal outer diameter [mm]
E2002S.41.04SR	22/2C STRANDED SHIELDED CMR/CL3R		0.008	0.14			0.2	3.35

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	E2062S.41.10	12/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTS	1	LBS
	E2062S.38.10	12/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTO	32	LBS
	E2052S.41.03	14/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTO	1	LBS
	E2052S.25.03	14/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTO	20	LBS
	E2052S.30.10M	14/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTO	60	LBS
	92979A.41.10	14/2 BC SHIELDED CL3R	US	Distribution products	MTO	1	LBS
	E2052S.30.10	14/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTO	40	LBS
	E2052S.41.10	14/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTS	1	LBS
	E2043S.41.10	16/3C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTS	1	LBS
	E2044S.41.10	16/4C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTS	1	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	E2042S.30.10	16/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTS	26	LBS
	E2042S.41.10	16/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTS	1	LBS
	E2042S.18.10	16/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTO	14	LBS
	E2032S.41.03	18/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTO	1	LBS
	E2032S.30.10M	18/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTO	277,000	LBS
	C4334A.41.03	18/2C STRANDED BC SHIELDED FPL/CSA	US	Distribution products	MTS	1	LBS
	E2032S.43.19	18/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTO	1	LBS
	E2032S.43.07	18/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTO	39	LBS
	E2032S.30.10	18/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTS	18	LBS
	E2032S.41.10	18/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTS	1	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	E2032S.46.10	18/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTO	96	LBS
	E2032S.18.10	18/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTS	10	LBS
	E2022S.30.10	20/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTO	14	LBS
	E2022S.41.10	20/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTS	1	LBS
	E2026S.41.10	20/6C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTO	1	LBS
	E2003S.41.10	22/3C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTS	1	LBS
	E2002S.30.10	22/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTS	10	LBS
	E2002S.41.10	22/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTS	1	LBS
	E2002S.18.10	22/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTO	5	LBS
	E2000S.41.10	22/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTO	1	LBS

PRODUCT DETAILS

SPEC number	Part number	Product name	Country of origin	Distribution type	Stock item	Net weight	Weight unit
	E2002S.41.04SR	22/2C STRANDED SHIELDED CMR/CL3R	US	Distribution products	MTO	1	LBS

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
E2062S.41.10	12/2C STRANDED SHIELDED CMR/CL3R	FOOT	12	12	7	1000 FT Reel
E2062S.38.10	12/2C STRANDED SHIELDED CMR/CL3R	FOOT	12	12	11	500 FT Reel
E2052S.41.03	14/2C STRANDED SHIELDED CMR/CL3R	FOOT	12	12	7	1000 FT Reel
E2052S.25.03	14/2C STRANDED SHIELDED CMR/CL3R	FOOT	14	9	14	500 FT Pull-Pac
E2052S.30.10M	14/2C STRANDED SHIELDED CMR/CL3R	FOOT	0	0	0	1000 FT Pull-Pac
92979A.41.10	14/2 BC SHIELDED CL3R	INCH	12	12	10	1000 FT Reel
E2052S.30.10	14/2C STRANDED SHIELDED CMR/CL3R	FOOT	16	10	16	1000 FT Pull-Pac
E2052S.41.10	14/2C STRANDED SHIELDED CMR/CL3R	FOOT	12	12	11	1000 FT Reel
E2043S.41.10	16/3C STRANDED SHIELDED CMR/CL3R	FOOT	12	12	7	1000 FT Reel
E2044S.41.10	16/4C STRANDED SHIELDED CMR/CL3R	FOOT	12	12	11	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
E2042S.30.10	16/2C STRANDED SHIELDED CMR/CL3R	FOOT	14	9	14	1000 FT Pull-Pac
E2042S.41.10	16/2C STRANDED SHIELDED CMR/CL3R	FOOT	12	12	7	1000 FT Reel
E2042S.18.10	16/2C STRANDED SHIELDED CMR/CL3R	FOOT	7	7	11	500 FT Spool
E2032S.41.03	18/2C STRANDED SHIELDED CMR/CL3R	FOOT	12	12	6	1000 FT Reel
E2032S.30.10M	18/2C STRANDED SHIELDED CMR/CL3R	FOOT	13	8	13	1000 FT Pull-Pac
C4334A.41.03	18/2C STRANDED BC SHIELDED FPL/CSA	FOOT	12	12	7	1000 FT Reel
E2032S.43.19	18/2C STRANDED SHIELDED CMR/CL3R	FOOT	99	99	99	2000 FT Reel
E2032S.43.07	18/2C STRANDED SHIELDED CMR/CL3R	FOOT	99	99	99	2000 FT Reel
E2032S.30.10	18/2C STRANDED SHIELDED CMR/CL3R	FOOT	14	8	14	1000 FT Pull-Pac
E2032S.41.10	18/2C STRANDED SHIELDED CMR/CL3R	FOOT	12	12	7	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
E2032S.46.10	18/2C STRANDED SHIELDED CMR/CL3R	FOOT	16	16	12	5000 FT Reel
E2032S.18.10	18/2C STRANDED SHIELDED CMR/CL3R	FOOT	7	7	7	500 FT Spool
E2022S.30.10	20/2C STRANDED SHIELDED CMR/CL3R	FOOT	14	9	14	1000 FT Pull-Pac
E2022S.41.10	20/2C STRANDED SHIELDED CMR/CL3R	FOOT	12	12	7	1000 FT Reel
E2026S.41.10	20/6C STRANDED SHIELDED CMR/CL3R	INCH	99	99	99	1000 FT Reel
E2003S.41.10	22/3C STRANDED SHIELDED CMR/CL3R	FOOT	12	12	7	1000 FT Reel
E2002S.30.10	22/2C STRANDED SHIELDED CMR/CL3R	FOOT	14	8	14	1000 FT Pull-Pac
E2002S.41.10	22/2C STRANDED SHIELDED CMR/CL3R	FOOT	12	12	7	1000 FT Reel
E2002S.18.10	22/2C STRANDED SHIELDED CMR/CL3R	FOOT	7	7	5	500 FT Spool
E2000S.41.10	22/2C STRANDED SHIELDED CMR/CL3R	FOOT	12	12	8	1000 FT Reel

PRODUCT PACKAGING

Part number	Product name	Packaging unit	Packaging length	Packaging width	Packaging height	Put up
E2002S.41.04SR	22/2C STRANDED SHIELDED CMR/CL3R	FOOT	12	12	7	1000 FT Reel