MC3011 Series

1 cell lithium-ion/lithium-polymer battery protection IC

Outline

MC3011 series are protection IC with integrated MOS-FET for protection of the rechargeable lithium-ion or lithium-polymer battery. The overcharge, overdischarge and discharging and

charging overcurrent protection of the rechargeable one-cell lithium-ion or lithium-polymer battery can be detected.

Features	(Unless otherwise specified, Ta=25°C)
1) Range and accuracy of detection/release vol	Itage
	4.15V to 4.50V, 5mV steps Accuracy±22mV
	Accuracy±27mV (Topr=-5°C to +60°C)
Overcharge release voltage	4.00V to 4.35V *1 Accuracy±50mV
	2.00V to 3.00V *2 Accuracy±100mV
	2.00V to 3.00V *2 Accuracy±100mV
	Selection from 30mV to 130mV, 1mV Accuracy±6mV
	Selection from -130mV to -30mV, 1mV Accuracy±9mV
	Selection from 0.36V, 0.56V, 0.90V Accuracy±100mV
	nd release voltage is selectable from 0.10V/0.15V/0.20V/0.25V. Overdischarge detection and release voltage.
2) Range of detection delay time	
Overcharge detection delay time	Selection from 1.0s, 4.5s, 6.25s
Overdischarge detection delay time	Selection from 100ms, 256ms
 Discharging overcurrent detection delay tire 	me Selection from 8ms, 12ms, 16ms, 20ms, 34ms
 Charging overcurrent detection delay time 	Selection from 8.5ms, 25ms, 32.5ms
Short detection delay time	Selection from 0.50ms, 0.75ms
3) 0V battery charge function	Selection from "Permission" or "Prohibition"
4) The overcharge detection delay timer reset ti	ime function (function for the pulse charge) is provided. fixed
5) Low current consumption	
Normal mode	Тур. 3.0µA, Max. 5.2µA
Stand-by mode	Max. 0.1µA
	(For "Charger connection release" the overdischarge release condition.)
	Max. 0.5μA
	(For "Voltage release" the overdischarge release condition.)
S) MOS-FET	
Source to Source on state resistance	Τyp. 13.4mΩ (@VDD=3.7V)
7) Absolute maximum ratings	
● VCC pin	0.3V to +12V
• V- pin	
Drain-source voltage	Max. 24V
Drain current	
Total Power Dissipation	Max. 1.0W
Storage temperature	
Operation temperature	

Pin assignment

■ PLP-4D

(Top view)	Pin no.	Symbol	Function
S2 V-	1	S1	S1 is a source pin of Discharge MOS-FET and a negative power supply, which is connected to the negative terminal of the battery.
	2	VDD	VCC is a positive power supply pin, which is connected to the positive terminal of the battery through Rvcc (330 to 470 ohm).
	3	V-	V- is an input pin that detects overcurrent. This pin is connected to the source terminal of Charge MOS-FET through Ridt (2.7 kohm).
1 2 S1 V ₀₀	4	S2	S2 is a source pin of Charge MOS-FET, which is connected to a negative power supply terminal of chargers.
	-	D	D is a common pin of two drains of Charge MOS-FET and Discharge MOS-FET. D must be open electrically.

LINE UP

			ional ction	Detection / Release voltage							Detection delay time					Optional function	
Product name	Package	0V battery charge function	Dicharge overcuttent detection voltage becomes dependent on VDD	Overcharge detection voltage	Overcharge release voltage	Overdischarge detection voltage	Overdischarge release voltage	Discharging overcurrent detection voltage	Charging overcurrent detection voltage	Short detection voltage	Overcharge detection delay time	Overdischarge detection delay time	Discharging overcurrent detection delay time	Charging overcurrent detection delay time	Short detection delay time	Discharge current limit (@VCC=3.5V)	Charge current limit (@VCC=3.5V)
		*1	*2	Vdet1	Vrel1	Vdet2	Vrel2	Vdet3-1	Vdet4	Vshort	tVdet1	tVdet2	tVdet3	tVdet4	tshort	Idischg	Icharge
				V	V	V	V	V	V	V	S	ms	ms	ms	μs	Α	Α
MC3011CL1GAM	PLP-4D	0		4.425	4.225	2.500	2.900	0.064	-0.073	0.36	1.0	100	12.0	8.50	500	4.50	5.40


PLP-4D ... 5,000pcs/Reel

Please inquire to us, if you request a rank other than the above.

^{*1 0}V battery charge function Permission × Prohibition 2 Optional functions Provide × Not provided

MC3011 Series

Typical application circuit



- R1 and C1 stabilize a supply voltage ripple. However, the detection voltage rises by the current of penetration in IC of the voltage detection when R1 is enlarged, and the value of R1 is adjusted to 1KΩ or less. Moreover, adjust the value of C1 to 0.01µF or more to do the stability operation, please.
- R1 and R2 resistors are current limit resistance if a charger is connected reversibly or a high–voltage charger that exceeds the absolute maximum rating is connected. R1 and R2 may cause a power consumption will be over rating of power dissipation, therefore the "R1+R2" should be more than 1KΩ. Moreover, if R2 is too enlarged, the charger connection release cannot be occasionally done after the overdischarge is detected, so adjust the value of R2 to 10KΩ or less, please.
- C2 and C3 capacitors have effect that the system stability about voltage ripple or imported noise. After check characteristics, decide that these capacitors should be inserted or not, where should be inserted, and capacitance value, please.