

# **VSC3308**

### 11.5 Gbps 8 × 8 Crosspoint Switch

Microsemi's multichannel 11.5 Gbps crosspoint switch provides a cost-effective solution for high-speed copper interconnects.

The VSC3308 is an advanced signal conditioning crosspoint switch solution uniquely capable of addressing a wide array of asynchronous, physical layer switching, and routing applications across storage, server, video, communications, and other industries. Featuring an  $8\times 8$  non-blocking, multicasting switch core with ports running at any rate up to 11.5 Gbps, the VSC3308 architecture provides protocol-transparent operation, allowing each channel to run independently.

The device supports virtually all standard and proprietary data protocols up to the maximum data rate. VSC3308 incorporates Microsemi's fourth-generation input equalization and pre-emphasis I/O capability engineered to overcome channel impairments experienced in today's high-density systems at multi-gigabit data rates. The device can perform signal fanout, loopback, and protection switching. It can also regenerate signals compromised by losses in the transmission medium. Microsemi's equalization works independently of the data rate, providing highly effective compensation for deterministic jitter across a wide range of high-speed interconnect applications.


## **Highlights**

- DC to 11.5 Gbps operation
- 8 × 8 fully non-blocking switch capability
- Protocol-transparent operation
- Advanced input equalization and output preemphasis

## **Applications**

- Servers
- Storage
- Telecom
- Broadcast video switching/routing
- HDMI/DVI/DisplayPort switching/routing
- Test and measurement

#### **VSC3308 Line Card Application**



Microsemi makes no warranty, representation, or guarantee regarding the information contained herein or the suitability of its products and services for any particular purpose, nor does Microsemi assume any liability whatsoever arising out of the application or use of any product or circuit. The products sold hereunder and any other products sold by Microsemi have been subject to limited testing and should not be used in conjunction with mission-critical equipment or applications. Any performance specifications are believed to be reliable but are not verified, and Buyer must conduct and complete all performance and other testing of the products, alone and together with, or installed in, any end-products. Buyer shall not rely on any data and performance specifications or parameters provided by Microsemi. It is the Buyer's responsibility to independently determine suitability of any products and to test and verify the same. The information provided by Microsemi hereunder is provided "as is, where is" and with all faults, and the entire risk associated with such information is entirely with the Buyer. Microsemi does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other IP rights, whether with regard to such information is entirely by information. Information provided in this document is proprietary to Microsemi, and Microsemi reserves the right to make any changes to the information in this document or to any products and services at any time without notice.



# **VSC3308**

## 11.5 Gbps 8 × 8 Crosspoint Switch

## **Speed and Protocol Support**

- 11.5 Gbps non-return-to-zero (NRZ) data bandwidth
- Protocol-transparent

### **Architecture**

- Fully non-blocking and multicasting switch core
- LOS detection and forwarding (supports out-of-band signaling)
- Fully asynchronous operation with <1 ns latency
- 8 x 8 switch core enables signal fanout, loopback, and protection switching

## Signal Integrity

- Multiple time-constant programmable input and output equalization
- Wide equalization adjustment range
- Input EQ up to 26 dB
- 9 dB of pre-emphasis


## **Key Specifications**

- 11.5 Gbps NRZ per channel data rate
- 2.5 V power supply
- 10 mm × 10 mm flip chip ball grid array package

#### **Related Products**

Visit <u>www.microsemi.com</u> for information about these related products:

- Crosspoint switches
- Ethernet MACs
- · Mux, demux, and transceivers
- Electronic dispersion compensation CDRs



Two-Wire Interface or Four-Wire Interface



Microsemi Corporate Headquarters
One Enterprise, Aliso Viejo, CA 92656 USA
Within the USA: +1 (800) 713-4113
Outside the USA: +1 (949) 380-6100
Fax: +1 (949) 215-4996
Email: sales.support@microsemi.com
www.microsemi.com

Microsemi Corporation (Nasdaq: MSCC) offers a comprehensive portfolio of semiconductor and system solutions for aerospace & defense, communications, data center and industrial markets. Products include high-performance and radiation-hardened analog mixed-signal integrated circuits, FPGAs, SoCs and ASICs; power management products; timing and synchronization devices and precise time solutions, setting the world's standard for time; voice processing devices; RF solutions; discrete components; enterprise storage and communication solutions, security technologies and scalable anti-tamper products; Ethernet solutions; Power-over-Ethernet ICs and midspans; as well as custom design capabilities and services. Microsemi is headquartered in Aliso Viejo, California and has approximately 4,800 employees globally. Learn more at www.microsemi.com.