

Material:

Insulator: PBT UL 94V-0

Contact: Brass

Front Shell: SPCC, Nickel plated over Cu

Rear Shell: SPCC, Tin plated over Cu

Ordering Code

CD51 50 P * 1 ** -A
① ② ③ ④ ⑤ ⑥

① Series No.

② No. of Circuits:

③ Contact type: P= Plug(Male)

④ Plating option:

2= Gold flash plated over Nickel

A= Selective Gold flash plated over Nickel

⑤ Color: 1= Black




⑥ Other Option:

00-A= With $\phi 3.10$ mm holes on shell(Standard)





A0-A= Riveted #4-40 UNC close nuts on front shell

C0-A= Riveted #4-40 UNC open nuts on rear shell

G1-A= Riveted #4-40 UNC open nuts on rear shell & With #4-40 Hexagon Screw



Mounting Style

Code	00—A	Code	A0—A	Code	C0—A	Code	G1—A
		DIM. L= 5.8mm		DIM. L= 4.0mm		DIM. L1= 4.0mm DIM. L2= 4.8mm	
							

RoHS Compliant

4					DATE	UNIT: mm / inch	TITLE: D-SUB MALE 50P SOLDER CUP TYPE	瀚荃股份有限公司 CviLux Corporation			
3				DRAWN BY: Wayne	2/24-25'	TOLERANCE UNLESS OTHERWISE SPECIFIED	MATERIAL:				
2				ENGINEER: Sun	2/24-25'	.X ±0.35/.014 X' ±	FINISH:	DRAWING NO. CD5157S1	PART NO. CD5150P*1**-A		
1				CHECKED BY: Eisley	2/24-25'	.XX ±0.25/.010 X' ±		SCALE 2 / 1	SHEET 1 OF 1		
SYM	NAME	DATE	REVISIONS	APPROVED BY: Eisley	2/24-25'	.XXX ±0.15/.006 X' ±					